

Datasheet


RS PRO M12 Female Rear Panel Mount 8 Pin Shielded Connector


Part No: 2017203




Technical Specifications:

Rated Operational Voltage	30 V
Current Rating	2 A
Insulation Resistance	≥100 MΩ
Temperature Range	-25° ... +75°C
Coding	A-Coded
Degree of Protection	IP67
Housing Material	Brass Ni Plated
Contact	Cu-Zn
Contact Plating	Gold Flash
Contact Carrier	Nylon 66
O-ring	Neoprene
Pole	8
Clamp Nut	M16 x 1.5





PCB Layout:



Quality Standard: IEC 61076-2-101

 <p>TÜVRheinland CERTIFIED</p>	<p>Type Approved Safety Regular Production Surveillance</p>	
	<p>www.tuv.com ID 1111210483</p>	

