


Deep groove ball bearings, single row, seal on both sides

Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
35	62	14	16,8	10,2	0,44	-	7000	0,16	6007-2RS1 *



Calculation factors

k_r 0,025
 f_0 15