



Order Code	TCK-102
Inductance	3.3 μ H \pm 20% (at 100 kHz / 250 mV)
Impedance (DCR)	18 mOhm max.
Rated Current	10 A max.
Operating Temperature	-40°C to +125°C



Impedance Curve



Outline Dimensions



Dimensions [mm]

Dimension	Value [mm]
A	6.5 \pm 0.3
B	6.5 \pm 0.3
C	4.2 max.
D	7.6 max.
E	1.5 \pm 0.3
F	1.2 \pm 0.3
G	3.0
H	8.5
I	2.5