

ZK10-PE

ABB contact for United
Kingdom

General Information

Extended Product Type:	ZK10-PE
Product ID:	1SNK710150R0000
EAN:	3472597101502
Catalog Description:	ZK10-PE PI-Spring clamp Terminal Block - Ground - Green Yellow
Long Description:	ZK10-PE PI-Spring clamp Terminal Block - Ground - Green Yellow - 10 mm ² - 10 mm 0.394 in spacing - Flat marking area

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » PI-Spring Terminal Blocks

Ordering

EAN:	3472597101502
Minimum Order Quantity:	20 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Width:	10 mm
Product Net Height:	87.7 mm
Product Net Length:	47.6 mm
Product Net Depth:	47.6 mm
Product Net Weight:	36.20 g

Container Information

Package Level 1 Units:	20 piece
Package Level 1 Width:	86 mm
Package Level 1 Height:	50 mm
Package Level 1 Length:	200 mm
Package Level 1 Gross Weight:	0.744 kg
Package Level 1 EAN:	3472597101502
Package Level 2 Units:	240 piece
Package Level 2 Width:	300 mm
Package Level 2 Height:	200 mm
Package Level 2 Length:	400 mm
Package Level 2 Gross Weight:	8.928 kg
Package Level 3 Units:	11520 piece

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Technical UL/CSA

Connecting Capacity-Main Circuit UL/CSA:	Spring Clamp / Rigid 1x 20 ... 6 AWG Spring Clamp / With Insulated Ferrule 1x 20 ... 8 AWG
---	---

Spring Clamp / Without Insulated Ferrule 1x 20 ... 8 AWG

Flammability According to UL94: V0**Additional Information**

Ambient Temperature:	-5 ... +40 °C
Color:	Green-Yellow
Connecting Capacity-Main Circuit:	Spring Clamp / Flexible 1x 0.5 ... 10 mm ² Spring Clamp / Rigid 1x 0.5 ... 16 mm ² Spring Clamp / With Insulated Ferrule 1x 0.5 ... 10 mm ² Spring Clamp / Without Insulated Ferrule 1x 0.5 ... 10 mm ²
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Dielectric Test Voltage:	2200 V
Function:	Ground
IIT Publishing Status:	Level 0 - Information enabled
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Pollution Degree:	3
Product Main Type:	ZK10-PE
Product Name:	Terminal Block
Rated Cross-Section:	10 mm ²
Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Rated Short-time Withstand Current (I_{cw}):	for 1.0s 1200 A
Recommended Screw Driver:	4 mm
Spacing:	10 mm
Sub-Function:	2 connections
Sub-Function 2:	Profile aligned with ZK10
Wire Stripping Length:	15.0 mm

Certificates and Declarations (Document Number)

BV Certificate:	1SND162013A0200
CB Certificate:	1SND162018A0200
CSA Certificate:	1SND162014A0201
cUL Certificate:	1SND162012A0200
Declaration of Conformity - CE:	1SND225151C1000
GOST Certificate:	1SND161005A1104
RoHS Information:	1SND230535F0200
UL Certificate:	1SND162012A0200

Classifications

ETIM 4.0:	EC000901 - Ground terminal block
ETIM 5.0:	EC000901 - Ground terminal block
Object Classification Code:	X

