



## SAS-87 HORN SIREN SAS-88



This ceiling mountable piezoceramic siren is used for very loud immediate attention-getting functions. The sound output level reaches 122 dB(A). Combined with a visual eye-catching flashlight, the siren gets immediate attention. This siren is especially suited for use in applications such as fire alarms, automation equipment, security devices, emergency warnings and as safe guards. The SAS-87 is available in 2 versions: 12Vdc ~~and 24Vdc.~~

### ADVANTAGES & APPLICATIONS

#### ADVANTAGES :

- Audiovisual alarm: eye-catching flashlight
- Loud siren output with solid-state flash light and high sound pressure
- Ceiling mounting type; disk mounting bracket
- Dust tight and waterproof

#### APPLICATIONS :

- Smoke alarms
- Fire alarms
- Car/burglar alarms


### SPECIFICATIONS

Operating voltage:	SAS-87-12V: 6-14Vdc <del>SAS-87-24V: 16-28Vdc</del>
Operating current: (with reverse polarity protection)	SAS-87-12V: 250mA <del>SAS-87-24V: 160mA</del>
Operation frequency:	1.5-3.5kHz (±30%)
Alarm tones:	frequency sweep during 1 second
Sound output:	122dB(A) (±dB(A) @30cm
Flash light flux:	20 candle
Color:	Ivory
Power cord:	length of 30cm (±3 cm; AWG24)
Case material:	ABS plastic <b>Sounder &amp; Plastic Case</b> <span style="border: 1px solid red; padding: 2px;">Lens cover: PC</span>
Weight:	128g/pc 1pc/box; 50 pcs/inner box; 100 pcs/box Net weight/Gross weight/Measurement: 18kg/19kg/0.10m3

**122 dB(A)  
@ 30cm**



## ELECTRICAL PARAMETERS



Note : All measurements are made in free air @1 meter @21°C @35% RH.

## DIMENSIONS (all dimensions are in mm)

