

Thrust ball bearings, single direction

Principal dimensions			Basic load ratings		Fatigue load limit P_u	Minimum load factor A	Speed ratings		Mass kg	Designation
d	D	H	dynamic	static			Reference speed	Limiting speed		
mm			kN		kN	-	r/min			-
10	24	9	9,95	15,3	0,56	0,0012	9500	13000	0,020	51100

