































- Standard housing
- Corrosion-resistant hoods (series K)



Side bayonet on hood

| Style | Ordering number | Cable entry | | | Description | Outline drawing dimensions in mm | |
|---|--|--|--|--|--|---|---|
| | |  PG |  PG |  PG | |  |  |
| Hood side entry standard construction | 41.32.10.05 41.32.10.79 41.32.10.69 | 16 | 16 | 16 | HA.10.STS.1.16 HA.10.STS.1.16.Z HA.10.STS.1.16.G |  |  |
| | 51.41.32.10.05 51.41.32.10.79 51.41.32.10.69 | 16 | 16 | 16 | HA-K.10.STS.1.16 HA-K.10.STS.1.16.Z HA-K.10.STS.1.16.G |  |  |
| high construction | 49.32.15.05 49.32.15.79 49.32.15.69 | 16 | 16 | 16 | HD.15.STS.1.16 HD.15.STS.1.16.Z HD.15.STS.1.16.G |  |  |
| | 49.32.15.07 49.32.15.80 49.32.15.70 | 21 | 21 | 21 | HD.15.STS.1.21 HD.15.STS.1.21.Z HD.15.STS.1.21.G |  |  |
| high construction | 51.49.32.15.05 51.49.32.15.79 51.49.32.15.69 | 16 | 16 | 16 | HD-K.15.STS.1.16 HD-K.15.STS.1.16.Z HD-K.15.STS.1.16.G |  |  |
| | 51.49.32.15.07 51.49.32.15.80 51.49.32.15.70 | 21 | 21 | 21 | HD-K.15.STS.1.21 HD-K.15.STS.1.21.Z HD-K.15.STS.1.21.G |  |  |
| top entry standard construction | 41.30.10.05 41.30.10.79 41.30.10.69 | 16 | 16 | 16 | HA.10.STO.1.16 HA.10.STO.1.16.Z HA.10.STO.1.16.G |  |  |
| | 51.41.30.10.05 51.41.30.10.79 51.41.30.10.69 | 16 | 16 | 16 | HA-K.10.STO.1.16 HA-K.10.STO.1.16.Z HA-K.10.STO.1.16.G |  |  |
| high construction | 49.30.15.05 49.30.15.79 49.30.15.69 | 16 | 16 | 16 | HD.15.STO.1.16 HD.15.STO.1.16.Z HD.15.STO.1.16.G |  |  |
| | 49.30.15.07 49.30.15.80 49.30.15.70 | 21 | 21 | 21 | HD.15.STO.1.21 HD.15.STO.1.21.Z HD.15.STO.1.21.G |  |  |
| high construction | 51.49.30.15.05 51.49.30.15.79 51.49.30.15.69 | 16 | 16 | 16 | HD-K.15.STO.1.16 HD-K.15.STO.1.16.Z HD-K.15.STO.1.16.G |  |  |
| | 51.49.30.15.07 51.49.30.15.80 51.49.30.15.70 | 21 | 21 | 21 | HD-K.15.STO.1.21 HD-K.15.STO.1.21.Z HD-K.15.STO.1.21.G |  |  |