



Fuse-link, high speed, 20 A, AC 690 V, 90 kA, BS88, 9 x 75 mm, aR, BS, 64.3 mm fixing centres



Powering Business Worldwide™

Part no. **Sicherung 20A IEC269-4**
 Catalog No. **20FC**

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			high speed
Rated current	I	A	20
Rated voltage			AC 690 V
Construction size			BS88
Size			9 x 75 mm
Utilization category			aR
Description			64.3 mm fixing centres
Breaking Capacity		kA	90
usable for size/applications			semiconductor protection
Standard/Approval			BS
Shape			offset bolted tags
Standards/Regulations			BS88-4 IEC 60269-4

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	20
Rated voltage		V	690
Voltage type			AC
Rated switching capacity		kA	90
Utilization category			aR (accompanied semiconductor protection)
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No