


**SEE PAGE 2 FOR CONNECTOR DETAILS

WIRING SCHEMATIC 1 PIN 1 = BROWN 2 = WHITE 3 = BLUE 4 = BLACK WIRING SCHEMATIC 2 PIN 2 = GRED 3 = BLACK 4 = WHITE



NOTE: PACKAGED 10 PER BAG

Full stainless steel variant successfully passes 96-hour salt spray testing per ASTM B117

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF A SHARE OF SALE OF SALE

DRAWN:

G. BROWN

DATE: 01/23/2019

NorComp


UNITS = "as indicated"


DO NOT SCALE FROM DRAWING

SCALE: SHEET OF REV 4


DWG NO. MPM12A04IYYDF0Y

DESCRIPTION: M12 4 POSITION STAINLESS STEEL MALE PIGTAIL





RECOMMENDED PANEL CUT-OUT



SPECIFICATIONS:

MATERIALS:

HOUSING: PBT, UL94 V-0, BLACK CONTACTS: 10μ"GOLD PLATED BRASS NUT: 316 STAINLESS STEEL

SHELL: 316 STAINLESS STEEL ORING:

EPDM, BLACK

ELECTRICAL:

RATED CURRENT: 4A RATED VOLTAGE: 250V

INSULATION RESISTANCE: 100 MOhms MIN. CONTACT RESISTANCE: 10 mOhms MAX.

ENVIRONMENT:

-40°C TO +85°C OPERATING TEMPERATURE: WATER PROOF: IP67 / IP68



THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED. COPIED OR USED AS THE APPARATUS WITHOUT WRITTEN PERMISSION. DRAWN: G. BROWN

DATE: 01/23/2019 UNITS = inch [mm]

DO NOT SCALE FROM DRAWING



SCALE:	SHEET	OF		
NTS	2		2	

MPM12A04IYYDF0Y

REV

4