


3.5mm Stereo Jack

161-7400-EX

KOBI CONN

3.5mm Stereo Jack



SPECIFICATIONS	
Contact Resistance:	50mΩ max.
Insulation Resistance:	100MΩ min. @ 500VDC
Dielectric Voltage:	500VAC for 1 minute
Life Cycle:	1,000 cycles min.
Operations Temperature Range:	-25°C ~ 80°C
Insertion/Extraction Force:	5N-20N (0.5 kgf.-2 kgf.)
Contacts:	Nickel Plated brass #1 & 3, Cold Plated #2
Body:	PBT-G30%
Electrical Rating:	34VDC/VAC @ 1A
Rating:	34VAC/DC, 1A
Mating Plugs:	17PP004-EX, 171-3300-EX, 171-3301-EX, 171-3308-EX
Threadsize:	M6 P=0.5
RoHS Compliant by Exemption	

Date Last Revised: 07-19-11

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-300830

161-7400-EX

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-7400-EX](#)