

Within Series Adaptor 37_N-75-0-1/133_N

Description

Panel adaptor jack/jack, flange mount
N jack (female) / N jack (female)

Interface standard
Series N - Not compatible to N 50 Ohms



Technical Data

Electrical Data

Impedance 75 Ω
Interface frequency max. 1.5 GHz

Mechanical Data

Number of matings 500
Weight 0.0491 kg

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing DCA-00013521
Mounting hole DOU-00008795

Ordering Information

Single package 37_N-75-0-1/133_NE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[37_N-75-0-1/133_NE](#)