

# Digital Modules

## ND-6050

Digital I/O Module



### Digital Input

- Channels: 7
- Switching Level: TTL
- Internal Pull-Up Resistor: 10 k $\Omega$
- Maximum Current: 0.5 mA
- Programmable input polarity

### Digital Output

- Channels: 8
- Maximum Current Sink: 50 mA
- Maximum Power Dissipation: 300 mW
- Programmable output polarity
- Programmable power on/safety state

### Power

- Requirement: unregulated +10 V to +30 Vdc
- Power Consumption: 0.336 W typical

## ND-6052

8-CH Isolated Digital Input Module



### Digital Input

- Channels: 8
  - 6 independent isolated channels
  - 2 isolated channels with common ground

### Switching Levels

- Low (0): +1 V (max.)
- High (1): +3.5 V to +24 V

- Internal Current Limit Resistor: 1.2 k $\Omega$

- Isolated Voltage: 5,000 VRMS

- Programmable input polarity

### Power

- Requirement: unregulated +10 V to +30 Vdc
- Power Consumption: 0.264 W

## ND-6053

16-CH Digital Input Module



### Digital Input

- Channels: 16
- Dry Contact
  - Logical level 0: close to GND
  - Logical level 1: open
  - Effective distance: 500 m (max)
- TTL Contact

- Internal Pull-Up Resistor: 10 k $\Omega$

- Programmable input polarity

### Power

- Requirement: unregulated +10 V to +30 Vdc
- Power Consumption: 0.408 W typical

## ND-6054

15-CH Isolated Digital Input Module



### Digital Input

- Channels: 15-bit digital input with 24 V external common power

### Switching Level:

- Low (0): +1 V (max.)
- High (1): +3.5 V to +24 V

- Internal Pull-Up Resistor: 1.2 k $\Omega$

- Isolated Voltage: 5,000 VRMS

- Programmable input polarity

### Power

- Requirement: unregulated +10 V to +30 Vdc
- Power Consumption: 0.216 W typical

## ND-6056

15-CH Isolated Digital Output Module



### Digital Output

- Channels: 15-bit digital open collector output with common ground

- Maximum Load Current: 300 mA

- Isolated Voltage: 3,750 VRMS

- Programmable input polarity

### Power

- Requirement: unregulated +10 V to +30 Vdc

- Power Consumption: 1.32 W

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADLINK Technology:](#)

[ND-6052](#) [ND-6056](#) [ND-6053](#) [ND-6054](#) [ND-6050](#)