



**HT HI TECH
POLYMERS OY**

HTL-Grommets

Halogen free material TPE-SEBS, TPE-SEBS-VO, IP-class IP65, operating temperature -40+100 C, country of manufacture Finland, CE-marked.

First size is plate hole size, HTL 28-6, HTL 32-14, HTL 40-7, HTL 40-10, HTL 40-14, HTL 50-7, HTL 50-8, HTL 50-9, HTL 50-14, HTL 50-21, HTL 50-36, HTL 80-16.

HTL 28-6 3,0-4,0mm 3 pcs / 5,0-9,0mm 3 pcs

HTL 32-14 3,0-7,0mm 14 pcs



HTL 40-7 10,5-15,0mm 1 pcs / 7,5-10mm 6 pcs

HTL 40-10 2,5-7mm 7pcs / 5,5-14mm 3pcs



HT HI Tech Polymers Oy
Hallitie 1
32740 Sastamala
Finland

Phone +358 3 8828 600
email: firstname.lastname@hitech-polymers.fi

www.hitech-polymers.fi

VAT: FI06768280
FI2256600620095281
OKOYFIHH

HTL 40-14 3-5mm 2 pcs / 3-6mm 8 pcs

6-9mm 2 pcs / 6-11mm 2 pcs



HTL 50-8 4-10mm 4 pcs / 7-15mm 1pcs

3-7mm 2 pcs / 12-21mm 1 pcs



HTL 50-9 3,5-7mm 5pcs / 9,5mm 4 pcs



HTL 50-21 3-7mm 20 pcs / 7-12mm 1 pcs



HTL 50-7 8-12mm 7 pcs



HTL 50-14 5-9,5mm 12 pcs / 6-11,5mm 2 pcs



HT HI Tech Polymers Oy
Hallitie 1
32740 Sastamala
Finland

Phone +358 3 8828 600
email: firstname.lastname@hitech-polymers.fi

www.hitech-polymers.fi

VAT: FI06768280
FI2256600620095281
OKOYFIHH

HTL 50-36 3,5-5,5mm 36 pcs



HTL 80-16 6-10mm 6 pcs / 6-12mm 8 pcs

13-28mm 2 pcs



HT HI Tech Polymers Oy
Hallitie 1
32740 Sastamala
Finland

Phone +358 3 8828 600
email: firstname.lastname@hitech-polymers.fi

www.hitech-polymers.fi

VAT: FI06768280
FI2256600620095281
OKOYFIHH