



Search by part # or keyword

Products

Industries & Solutions

Resources

Shop TE


Sign In



Terminals & Splices > Rings & Spades

327043

PLASTI-GRIP, Rings & Spades, Spade Tongue, 22 – 16 AWG, .26 – 1.65 mm², 509 – 3260 CMA, #6 / M3.5, Stud Diameter 3.68 mm [.145 in]



PLASTI-GRIP | PLASTI-GRIP

TE Internal #: **327043**

TE Internal Description: **PG SPD 22-16 COMM 22-18 MIL 6**

Alias #: **AMPS-0-0327043-0, E22168-000**

Terminal & Splice Type : **Spade Tongue**

Wire Size (AWG): **22 – 16**

Wire Size (mm²): **.26 – 1.65**

Wire Size (CMA): **509 – 3260**

Stud Size : **6, M3.5**

Order Samples | Similar Products |

Digital Datasheet

Compatible Parts & Tooling

Free Shipping available on most items.

QTY:

Extended Price:

We are here to help!

Get in touch with our product experts.



CHAT WITH US



EMAIL US



CALL US

Documents

Features

Product Compliance

Product Drawings

PG SPD 22-16 COMM 22-18 MIL 6

PG SPD 22-16 COMM 22-18 MIL 6

English

CAD Files

3D PDF

3D_CVM_CVM_327043_H.pdf

3D

Customer View Model

ENG_CVM_CVM_327043_H.2d_dxf.zip

English

ENG_CVM_CVM_327043_H.3d_igs.zip

English

ENG_CVM_CVM_327043_H.3d_stp.zip

English

Product Specifications

Application Specification

ENG_SS_114-2161_G.pdf

English

Product Environmental Compliance

MD_327043_03202013046_dmtec

ENG_PC_MD_327043_L(508126).xlsx

English

Agency Approvals

UL Report

[ENG_AAD_UL_E13288_19720315_A.pdf](#)

English

UL Report

[ENG_AAD_UL_E13288_19800402_A.pdf](#)

English

[ENG_AAD_UL_E13288_19791001_B.pdf](#)

English

UL

[ENG_AAD_UL_E13288_19730713_A.pdf](#)

English

CSA Certificate

[ENG_AAD_CSA_164196_6223_1693113_A.pdf](#)

English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Stud Size : **6, M3.5**
Barrel Type : **Closed Barrel**
Sealable : **No**
Insulated : **Yes**
Wire/Cable Type : **Regular Wire**
Support Style : **Insulation Support**
Shape Description : **SPADE-021**

Configuration Features

Terminal Angle : **Straight**

Electrical Characteristics

Voltage (Max) (V): **600**

Body Features

Plating Material : **Copper, Tin**
Stripe Color : **Red**
Weight per Piece (g): **.687**
Insulation Sleeve Color : **Red**
Inspection Slot : **No**

Contact Features

Terminal & Splice Type : **Spade Tongue**
Terminal Orientation : **Offset**

Mechanical Attachment

Wire Insulation Support : **With**




Dimensions	Wire Size (AWG): 22 – 16 Wire Size (mm ²): .26 – 1.65 Wire Size (CMA): 509 – 3260 Stud Diameter: 3.68 mm [.145 in] Tongue Thickness: .79 mm [.031 in] Overall Length: 21.79 mm [.8579 in] Wire Insulation Diameter (Max): 3.56 mm [.14 in] Wire Insulation Diameter: 2.667 – 3.556 mm [.105 – .14 in]
Usage Conditions	Operating Temperature Range: 105 °C [221 °F]
Operation/Application	Heavy Duty: No
Industry Standards	Government Qualified: No
Packaging Features	Packaging Method: Loose Piece Packaging Quantity: 1000
Statement of Compliance	Statement of Compliance pdf

Products with Similar Specs

[View All Similar Products](#)

THIS PRODUCT

RINGS & SPADES
327043
PLASTI-GRIP, Rings & Spades, Spade Tongue, 22 – 16 AWG, .26




From **In-Stock**

Terminal & Splice Type : **Spade Tongue**
 Wire Size : **22 – 16 AWG**
 Wire Size : **.26 – 1.65 mm²**
 Wire Size : **509 – 3260 CMA**
 Stud Size : **#6, M3.5**

TOP RESULTS


RINGS & SPADES
2-327043-1
Rings & Spades, Spade Tongue, 22 – 16 AWG, .26 – 1.65 mm², 509 –...



From **In-Stock**

Terminal & Splice Type : **Spade Tongue**
 Wire Size : **22 – 16 AWG**
 Wire Size : **.26 – 1.65 mm²**
 Wire Size : **509 – 3260 CMA**
 Stud Size : **#6, M3.5**


RINGS & SPADES
8-327043-1
Rings & Spades, Spade Tongue, 22 – 16 AWG, .26 – 1.65 mm², 509 –...



From **In-Stock**

Terminal & Splice Type : **Spade Tongue**
 Wire Size : **22 – 16 AWG**
 Wire Size : **.26 – 1.65 mm²**
 Wire Size : **509 – 3260 CMA**
 Stud Size : **#6, M3.5**

RINGS & SPADES
2-320665-1
Rings & Spades, Spade Tongue, 22 – 16 AWG, .3 – 1.42 mm², 509 –...



From **In-Stock**

Terminal & Splice Type : **Spade Tongue**
 Wire Size : **22 – 16 AWG**
 Wire Size : **.3 – 1.42 mm²**
 Wire Size : **509 – 3260 CMA**
 Stud Size : **#6, M3.5**

Also in the Series | [PLASTI-GRIP](#)



Compression Connectors (3)



Crimp Wire Pins, Tabs & Ferrules (11)



Rings & Spades (208)



Splices (45)

[ABOUT TE CONNECTIVITY](#)

[FOR PARTNERS](#)

[SUPPORT](#)

[CALL US](#)

[LIVE CHAT](#)

[UNITED STATES \(EN\)](#)