


Quartz Crystal


HC-49/U

model	KX-49
frequency	11,05920 MHz
mode	fundamental
operating temperature	-20° ~ + 70°C
frequency tolerance at +25°C	30 ppm
temperature tolerance at -20° ~ +70°C	50 ppm
load capacitance C _L	30 pF
series resonance R ₁ max.	50 Ohm
aging at +25°C (first year) max.	± 5 ppm
shunt capacitance C ₀ max.	7 pF
drive level mW max	0,5 ~ 2
RoHS	according to RoHS 2011/65/EU
order no.	12.81315


Dimensions (mm):



Wave soldering condition:



Tape specification:



Taped crystals upon request