



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
PLT3I	.06 (1.5)	3.00 (76)	.052 (1.3)	.145 (3.7)	.220 (5.6)	.180 (4.6)	.260 (6.6)	11.4 (290)	40 (178)	INTERMEDIATE	CURVED	.32 (145)
PLT4I	.06 (1.5)	4.00 (102)	.052 (1.3)	.145 (3.7)	.220 (5.6)	.180 (4.6)	.260 (6.6)	14.5 (368)	40 (178)	INTERMEDIATE	CURVED	.40 (181)
PLT1S	.06 (1.5)	1.00 (25)	.052 (1.3)	.190 (4.8)	.262 (6.7)	.220 (5.6)	.316 (8.0)	4.8 (122)	50 (222)	STANDARD	CURVED	.13 (58)
PLT1.5S	.06 (1.5)	1.50 (38)	.052 (1.3)	.190 (4.8)	.262 (6.7)	.220 (5.6)	.316 (8.0)	6.2 (157)	50 (222)	STANDARD	CURVED	.26 (118)
PLT2S	.06 (1.5)	1.88 (47.8)	.052 (1.3)	.190 (4.8)	.262 (6.7)	.220 (5.6)	.316 (8.0)	7.4 (188)	50 (222)	STANDARD	CURVED	.29 (132)
PLT2.5S	.06 (1.5)	2.50 (63.5)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	9.8 (249)	50 (222)	STANDARD	CURVED	.38 (173)
PLT3S	.06 (1.5)	3.00 (76)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	11.5 (292)	50 (222)	STANDARD	CURVED	.45 (204)

NOTES:

\*SEE [www.panduit.com](http://www.panduit.com) FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	DRAWN BY	DATE	CHK	SCALE	SHT	SIZE
							PAN-TY CABLE TIES - PLT SERIES	CEW	12-27-84	HVP	NONE	SHT 1 OF 1	A
							CUSTOMER DRAWING						
							ITEM REVISION NAME						
							W10001CB/32						
							DATASET FILE NAME						
							W10001CB/32 SS-5540 SH2_REV32						
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)						
							.x ± --- .xxx ± .020 (.51)						
							.xx ± .02 (.5) ANGLES ± ---						
							THIRD ANGLE PROJECTION						
							MATERIAL:						
							NYLON 6.6						
							DRAWING NUMBER:						
							SS-5540 SHEET 2						