



## .140 MATE-N-LOK Contacts



WIRE		.140 MATE-N-LOK CONTACT				HAND TOOLING (Instruction Sheet)
SIZE (AWG) RANGE	INSULATION DIAMETER (mm [in.])	LOOSE PIECE		STRIP FORM		
		PIN	SOCKET	PIN	SOCKET	
20-14	2.54-4.57 [.100-.180]	350389-[ ]	350388-[ ]	61627-[ ]	61626-[ ]	90247-1 (408-7434)
14-10		350391-[ ]	350390-[ ]	350201-[ ]	350200-[ ]	69710-1 (Without Dies) (408-2095) and Die 58373-[ ] or 58374-[ ]