




CATEGORY	DESCRIPTION	P/N #
CONNECTOR	Modular Jack, 8P8C, 1X1PORT	MJ88-XX11-HRVS3-X

REV.	ECN NO	DESCRIPTION	REVISED	DATE
A05	—	增加产品颜色选项	XSY	2017.04.12
A06	—	增加产品热封包装选项	YST	2019.02.23



SPECIFICATIONS:

1. Voltage: 150V AC RMS
2. Current Rating: 1.5A
3. Contact Resistance: 40mΩ MAX.
4. Insulation Resistance: 500MΩ MIN.
5. Dielectric Withstand Voltage :1000V AC
6. Operate Temperature: -40°C~80°C
7. Durability: 750 Mating Cycles MIN.

Part No.:





Table 1

X	Color	housing Material
B	Black	LCP UL94V-0
U	Blue CX018	PA9T UL94V-0
5	Green	PA9T UL94V-0

X	包装方式
C	卷带包装
P	吸塑盒包装
C1	热封式卷带包装

X	Terminal Plating
0	Au 1u" Plating
1	Au 3u" Plating
2	Au 6u" Plating
3	Au 15u" Plating
4	Au 30u" Plating
5	Au 50u" Plating

Recommend PCB Layout
(Lack Top View)
Tolerance: $\pm 0.05\text{mm}$

c	Shielding	1	Brass	Ni Plating		
b	Terminal	8	Phosphor Bronze	Au/Tin Plating		
a	Housing	1	See Table 1	See Table 1		
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR	Remark	

UNLESS OTHERWISE SPECIFIED TOLERANCES	DECIMALS:	ANGLES:
	X : ± 0.5	X : $\pm 2^\circ$
	X.X : ± 0.3	X.X : $\pm 1'$
	X.XX : ± 0.2	

东莞市合陵电子有限公司
 DongGuan Heling Electronic Co.,LTD
 Connector
 SCALE: 1/1 UNIT: mm DWG.NO:
 SIZE: A3 PAGE: 1 OF 1 REV: A06
 APPROVED BY: XSY CHECKED BY: XSY PREPARED BY: YST
 DICK
CUSTOMER COPY