

Search Results

- Evaluate
  - FAQ's
- Design a Solution
  - Part Draw ings
  - PDF-Ring Termina ..
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results

 Text Search: 'PV18-14R-C'

Your search criteria matched only one product, shown below

**PV18-14R-CY**



- Insulation support helps to prevent wire damage in bending applications
  - Ring tongue design assures a secure connection in high vibration applications
  - Brazed seam protects terminal barrel from splitting during the crimp process
  - UL Flammability UL 94V-0, maximum insulation temperature 221°F (105°C)
  - Internal barrel serrations assure good wire contact and maximum tensile strength
  - UL and CSA rated up 600 V per UL 486
- ‡UL and CSA approved tooling/product combinations.  
Note: Wire sizes #26 – #22 AWG, are not UL Listed or CSA Certified.

Part Number	PV18-14R-CY
RoHS Compliancy Status	Compliant
Note	PV18-14R-CY replaces PV18-14R-C
Part Description	Ring Terminal, 22 – 18 AWG, 1/4" stud size, vinyl insulated, funnel entry.
Product Type	Terminals
CSA Certified	Yes
UL Listed	Yes
Length (In.)	1.11
Width (In.)	.46
Clearance	.37
Max. Ins.	.150
Panduit Color Code	Red
Pricing Description	Ring Terminal, vinyl insulated, 22 - 18 AWG, 1/4" stud size, funnel entry
Stock	.03
Stud Size	1/4"
Tool	CT-100A‡, CT-600-A‡, CT-1550‡, CT-1551‡, CT-2500‡
Wire Range	22 – 18 AWG
Wire Range (mm²)	0.5 - 1.5
Min. Order UOM	PC
Min. Order Qty.	100
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.