



# CorePro GLASS LED candles and lustres

## CorePro LEDCandle ND6.5-60W B35E14827CLG

Featuring a classic heritage design, these filament LED candles combine the familiar shapes of classic incandescent bulbs with the benefits of long-lasting LED technology. The LED candle bulb is a very easy choice for people who are looking for a retrofit LED replacement, it provides 90% energy savings compared with conventional lamps. CorePro Glass LED bulbs provide excellent quality of light for stairway lighting. The LED candle bulb offers a lifetime of 15,000 hours to reduce maintenance costs.

### Product data


General information		Operating and electrical	
Cap base	E14 [ E14]	Input frequency	50 to 60 Hz
EU RoHS compliant	Yes	Power (Rated) (Nom)	6.5 W
Nominal lifetime (nom.)	15000 h	Lamp current (nom.)	50 mA
Switching cycle	20000	Wattage equivalent	60 W
	Sphere	Starting time (nom.)	0.5 s
Tier	CorePro	Warm-up time to 60% light (nom.)	0.5 s
		Power factor (nom.)	0.55
		Voltage (Nom)	220-240 V
Light technical		Temperature	
Colour Code	827 [ CCT of 2,700 K]	T-Case maximum (nom.)	55 °C
Luminous flux (nom.)	806 lm		
Colour designation	Warm white (WW)	Controls and dimming	
Correlated Colour Temperature (Nom)	2700 K	Dimmable	No
Luminous efficacy (rated) (nom.)	124.00 lm/W	Mechanical and housing	
Colour consistency	<6	Lamp Finish	Clear
Colour rendering index (nom.)	80		
LLMF at end of nominal lifetime (nom.)	70 %		

# CorePro GLASS LED candles and lustres

Bulb shape	B35 [ B 35mm]
<b>Approval and application</b>	
Energy Efficiency Class	E
Energy consumption kWh/1,000 hours	7 kWh
	387441
<b>Product data</b>	
Full product code	871951434746500

Order product name	CorePro LEDCandle ND6.5-60W B35E14827CLG
EAN/UPC – product	8719514347465
Order code	34746500
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	929002028092
Net Weight (Piece)	0.012 kg


## Dimensional drawing




CorePro LEDCandle ND6.5-60W B35E14827CLG

Product	D	C
CorePro LEDCandle ND6.5-60W B35E14827CLG	35 mm	97 mm

## Photometric data




Light Distribution Diagram



Spectral Power Distribution Colour

# CorePro GLASS LED candles and lustres


## Photometric data




General Uniform Lighting  
1 x PHILIPS 835 2700K L&L

### General uniform lighting

## Lifetime



### Lumen Maintenance Diagram



### Life Expectancy Diagram

