

## Coaxial PCB Connector 82\_MBX-S50-0-23/111\_N

### Description

Straight PCB jack

Interface Standards  
HUBER+SUHNER MBX



### Technical Data

#### Electrical Data

Impedance 50  $\Omega$   
Interface frequency max. 6 GHz

#### Mechanical Data

Board mounting type surface mount  
Weight 0.000632 kg

#### Environmental Data

Operating temperature -55 °C to 155 °C  
2011/65/EU (RoHS - including  
2015/863 and 2017/2102) compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	LCP (Liquid crystal polymer)	

### Related Documents

Outline drawing DOU-00249344  
Catalogue drawing DCA-00161372  
Mounting hole DOU-00142408

### Ordering Information

Tape and Reel package 82\_MBX-S50-0-23/111\_NM  
Single package 82\_MBX-S50-0-23/111\_NE  
Bulk 100 pcs package 82\_MBX-S50-0-23/111\_NH

### Remarks

PCB connector with stand-offs

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[82\\_MBX-S50-0-23/111\\_NH](#)