

**Honeywell Sensing and Control**

Search

**narrow your search**

**Products**

- Controls Monitoring and Lighting (352)
- Machine Safety (1727)
- Sensors (5910)
- Switches (9775)
- Wireless (39)

**Technology**

- Control and Instrumentation (1054)
- Electromechanical (9301)
- Magnetic (541)
- Microstructure (1495)
- Optical/Infrared (1042)
- More...

**new products**

**New Wireless Products**

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site  
WGLA and WPM  
XYR6000™

[find out more](#)

**white papers**

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters

**Need help?**

[Click here to contact us](#)

**BZ-2RQ784**

( Home : Products : Switches » MICRO SWITCH™ Basic Switches » Premium Large Basic Switches » BZ/BAWA/YZ )



Actual product appearance may vary. [click here to download Hi-Res image](#)

**BZ Series Standard Basic Switch, Single Pole Double Throw Circuitry, 15 A at 250 Vac, Overtravel Plunger Actuator, 2,5 N - 3,61 N [9 oz - 13 oz] Operating Force, Silver Contacts, Screw Termination, CE, CSA, DEMKO,**

[Sales & Service](#) [Distributor Inventory](#)

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

**Product Specifications**

Switch Type	MICRO SWITCH™ Standard 25,4 mm H x 17,8 mm W x 50,8 mm L [1.0 in H x 0.7 in W x 2.0 in L]
Sealed	No
Ampere Rating	15 A
Circuitry	SPDT
Actuator	Overtravel Plunger
Termination	Screw
Operating Temperature	-55 °C to 85 °C [-67 °F to 185 °F]
Voltage	250 Vac
Contact Type	Silver
Operating Force (OF)	2,5 N to 3,61 N [9.0 oz to 13.0 oz]
Release Force	1,11 N [4.0 oz] min.
Pretravel (PT)	0,38 mm [0.015 in] max.
Overtravel (OT)	3,56 mm [0.140 in] min.
Differential Travel (DT)	0,01 mm to 0,05 mm [0.0004 in to 0.0020 in]
Operating Position (OP)	49,61 mm ±1,14 mm [1.953 in ±0.045 in]
Material	Plastic
Housing Material	General Purpose Phenolic
High Temperature	204 °C [400 °F]
Agency Approvals and Standards	UL, CE, CSA
Mounting Screw Size	3,53 mm [0.139 in]
Mounting Centers	25,4 mm [1 in]
Tightening Torque	0,33 N m [3.0 in lb]
Weight	39 g [0.086 lb]
Package Height	24,1 mm [0.95 in]
Package Width	17,5 mm [0.69 in]
Package Length	49,3 mm [1.94 in]
Recommended For	Added overtravel, roller plunger for rapid cam (30 ° max) rise and slide operation, panel mount
Comment	CE: 61058-1; UL: E12252; CSA: LR41370
Availability	Global
UNSPSC Code	30211905
UNSPSC Commodity	30211905 Snap switches
Series Name	BZ/BAWA/YZ

**contacts**

- Customer Service
- Technical Support
- Global Sales & Service
- View Site Demo
- Site Comments?

**meet dr. larry**

**VIDEO** - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

**my links**

- Login to iCOM
- Login to Rep/AD Portal
- Login to Digital University

**News Center**

HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION

HONEYWELL ADDS NEW 100° AND 180° ARC CONFIGURATIONS TO ITS SMART POSITION SENSOR PORTFOLIO

HONEYWELL INTRODUCES ITS HAWK™ RESOLVERS 1-INCH SERIES, FULLY HOUSED CONFIGURATION

HONEYWELL INTRODUCES MICROPOWER OMNIPOLAR DIGITAL HALL-EFFECT SENSOR ICS WITH LOW SUPPLY VOLTAGE AND ULTRA LOW TYPICAL CURRENT

**MICRO SWITCH Anniversary site**