

Type-A USB 3.2 Gen 2 interface allows for speedy data transfers up to 10 Gbps

 silicon-power.com/web/gb/product-M80



Go Xtreme With Top-Tier Speeds

With extreme read speeds up to 600MB/s and write speeds up to 500MB/s, the Marvel Xtreme M80 is our fastest USB flash drive yet. Compared to a standard UFD, that's 5.5x and 16.7x faster, respectively! Make the most of your time and copy huge files to the drive in a matter of seconds!*

Transfer a 5GB file from a PC to the drive in as little as 12 seconds!

The Only USB Flash Drive You'll Need

The Marvel Xtreme M80 is equipped with a Type-A USB 3.2 Gen 2 interface and a massive capacity of up to 1TB. With this much space, it's the only UFD you'll need. Add to that its portable-friendly design and simpler and quicker alternative to cloud storage, and

you'll definitely want it by your side wherever you go.

Portable And Convenient Design

The Marvel Xtreme M80 has a durable aluminum housing and a detachable cap that protects the USB Type-A connector. Throw it in your bag without worrying – it's truly as portable as you. And when you're ready to use it, a built-in LED light conveniently indicates data activity.

Back-Up For The Back-Up

To ensure the safety of your data, the Marvel Xtreme M80 comes with extra security measures. A free download of the SP Widget software is available for efficient file management and AES 256-bit encryption, while the Recuva File Recovery software provides data recovery. It's also backed by a limited 5-year warranty for even greater peace of mind.

Specifications



- Capacity
 - 250GB, 500GB, 1TB
- Dimensions
 - 68.5mm x 17.8mm x 8.2mm
- Weight
 - 8.5g
- Material
 - Aluminum + Plastic

- Color
- Gray
- Interface
- Type-A USB 3.2 Gen 2 (USB 3.1 Gen 2, USB 3.1 Gen 1 & USB 3.0 & USB 2.0 backwards-compatible)
- Performance Read(max.)
- 250GB – 590MB/s
- 500GB – 600MB/s
- 1TB – 600MB/s
- Performance Write(max.)
- 250GB – 260MB/s
- 500GB – 500MB/s
- 1TB – 500MB/s
- Supported OS
- Windows 10/8.1/8/7/XP, Mac OS 10.3.X and above, Linux 2.6.X and above
- *Transfer speeds fluctuated or dropped when I copied/moved files to USB drive on a Windows 10 system.Please click [here](#) for more information
- Operating Temperature
- 0°C - 70°C
- Certification
- CE, FCC, BSMI, UKCA, Green dot, WEEE, RoHS
- Warranty
- 5 year limited warranty

Features

- Type-A USB 3.2 Gen 2 interface allows for speedy data transfers up to 10 Gbps
- Massive instant storage expansion with capacities up to 1TB
- Blazing-fast read speeds up to 600MB/s and write speeds up to 500MB/s
- Built-in LED light conveniently indicates data activity
- Portable-friendly design: durable aluminum metal housing with protective detachable cap
- Simpler and quicker alternative to cloud storage as the bridge between phones and computers
- True Plug & Play Technology eliminates the need for external power
- Recuva File Recovery allows for recovery of erased files, such as digital photos, documents, music, and videos
- Free SP Widget software available for download for backup & restore, AES 256-bit encryption, and cloud storage

Marvel Xtreme M80

250GB, 500GB, 1TB

250GB

SP250GBUF3M80V1G

500GB

SP500GBUF3M80V1G

1TB

SP001TBUF3M80V1G