





# SPECIFICATION

- 1. Rated Voltage .....230VAC
- 2. Operating Voltage .....200~240VAC
- 3. Max. Rated Current .....20mA at 230VAC/DC
- 4. Min. Sound Pressure Level .....80dB at 230VAC/60cm
- 5. Tone Nature .....Fast Pulse
- 6. Resonant Frequency .....2.9±0.5KHz
- 7. Case Material .....ABS
- 8. Operating Temperature .....-20~+60°C
- 9. Store Temperature .....-30~+70°C
- 10. Weight .....40g



<b>KEPO</b> NINGBO KEPO ELECTRONIC CO.,LTD http://www.chinaacoustic.com									
<b>Piezo Buzzer</b> KPI-4322-230									
No.	DESCRIPTION	APPROVED	DATE	UNIT	DWGNO.	SCALE		SHEET	
		APPROVALS	DATE	mm	KP3,8,40,104	NOT TO SCALE		VER 1.1	
1. 比例尺 1:1 2. 公差按 GB/T1804-M 标注 3. 未注公差按 GB/T1804-M 标注 4. 表面粗糙度按 GB/T10613 标注 5. 形位公差按 GB/T1182 标注 6. 基准按 GB/T1182 标注 7. 基准符号按 GB/T1182 标注 8. 基准字母按 GB/T1182 标注 9. 基准代号按 GB/T1182 标注 10. 基准位置按 GB/T1182 标注		DRAWN CHECKED APPROVED		DATE 05.07.28					