

2019




Tools that work for you

# PROFESSIONAL TECH TOOLS



## COMPLETE TECHNICIAN'S PROGRAM



Precision Screwdrivers • PicoFinish Drivers • TorqueControl  
Micro Bits • Blade Sets • Electronic Pliers • ESD Tweezers • Mirrors

### Wiha Precision Screwdrivers

Description	Page
Precision Slotted Drivers	4
Precision Phillips Drivers	4
Precision Pozidriv® Drivers	5
Precision Hex Drivers	5
Precision Ball End Drivers	6
Precision Nut Drivers	7
Precision Torx® Drivers	6
Precision Pentalobe Drivers	7
Precision Chip Lifters	4

### Wiha Magnetizer/Demagnetizer

Description	Page
Magnetizer/Demagnetizer	11

### Wiha Precision Protturn Drivers

Description	Page
Protturn Drivers & Blade Sets	12
Slotted, Phillips, Torx, Chip Lifter	

### Wiha TorqueControl Tools

Description	Page
Torque Cable Keys	8
TorqueControl Handle	8

### Wiha ESD Safe Precision Handles/Blades

Description	Page
SYSTEM 4 Handles/Blades	13-15

### Wiha Precision Screwdriver Accessories

Description	Page
Precision Master Tech Sets	8
Precision Pocket Clip	4
Precision Stand	4
Precision Pouch	11

### Wiha ESD Safe Precision Handle & Blades

Description	Page
SYSTEM 4 Drive-Loc Handle & Blades	15
SYSTEM 4 Drive-Loc Set	15









### Wiha Precision PicoFinish Drivers

Description	Page
PicoFinish Screwdrivers	9-12
Slotted, Phillips, Torx, TorxPlus, Hex, MagicSpring, Ball End Hex, Chip Lifter & Nut Drivers	
Tri-Wing Drivers	
Insulated PicoFinish Drivers	12



### ESD Safe Micro Bit Handles, Bits & Sets

Description	Page
Micro Bit Handles/Bits/Sets	16-21
Micro Bit Storage Handle Sets	21
ESD Safe Micro Bit Sets	18-21

**Precision Electronic Pliers/Cutters**

	Description	Page
	Electronic Diagonal Cutters Wide Pointed Head	22
	Electronic Diagonal Cutters Wide Shape w/Wire Holding Spring	22
	Electronic Diagonal Cutters Narrow Shap	22
	Electronic Diagonal Cutters Full Flush Cutters w/Wire Trapping Spring	22
	Electronic Diagonal Cutters 48° Front Cutter/Long Nose Pliers	22
	Electronic Diagonal Cutters Oblique 30° Cutting Nippers	22
	Electronic Diagonal Cutters Short Nose Precision Pliers	22
	Electronic Stripping Pliers	22

**Wiha Professional Tweezers**

	Description	Page
	ESD Safe Tweezers	23-25
	Inspection Mirrors	25

**Wiha ESD Safe Tech Tools**

ESD Safe Precision Drivers  
Slotted/Phillips/Torx®/  
TorxPlus®/Hex/Nut Drivers/  
Chip Lifter

ESD Safe Ceramic Drivers

ESD Safe SYSTEM 4  
Handles/Blades/Sets

ESD Safe Drive-Loc  
Handles/Blades/Sets

ESD Safe Pliers & Cutters



Catalog 99945.wo



**The Comfortable Precision Screwdriver**

Soft Grip Handle

CVM tool steel  
blade, hardened,  
hard chrome finish

Ergonomic multi-  
component handle  
with rotating cap for  
maximum user comfort  
and precise control

Sets In Roll-Up Pouch



**New & Improved  
PicoFinish  
Screwdrivers On  
Pages 9-12**




**Rotating cap**  
for precise turning and control with fingertip

**Precision handle**  
high quality plastic, cadmium free

**Molded on tapered handle**  
allows rapid rotation

**High performance blades**  
CVM steel, Hard chrome finished

**Tip**  
precision ground for exact fit, hard chromed non-slip surface



## Wiha Precision Chip Lifter & Accessories



**26810 Precision Chip Lifter**  
Blade CVM steel, hardened, chrome-plated. Precision handle high quality plastic, impact resistant. Standard handle

Item							
No.	mm	mm	mm	mm	Inch	lbs.	Pkg.
26810	1	3.5	50	145	5.7	.07	1

\*Metric dimensions actual - Inch dimensions approximate



**26001 Pocket Clip for Precision Screwdrivers** Tool clips turn Precision Screwdrivers into Pocket Screwdrivers.

Item No.	Fits all		lbs.		pkg.
26001	Precision handles	.01		1	



**26000 Plastic Precision Tool Rack**  
Rack holds 6 precision screwdrivers, can be set on workbench. Also has holes for hanging. Made from high quality plastic.

Item No.	Rack for 6		lbs.		Pkg.
26000	Precision screwdrivers	.08		1	

## Wiha Precision Slotted/Phillips Drivers



**260 Slotted Screwdriver, With Precision Handle** Blade high alloy chrome-vanadium-molybdenum steel. Pkg. 10

Item No.									
No.	mm	Inch	mm	Inch	mm	mm	Inch	lbs.	
26008	.80	1/32	40	1.6	0.16	120	4.7	.02	
26010	1.0	.039	40	1.6	0.18	120	4.7	.02	
26012	1.2	3/64	40	1.6	0.20	120	4.7	.02	
26015	1.5	1/16	40	1.6	0.25	120	4.7	.02	
26018	1.8	.070	40	1.6	0.30	120	4.7	.02	
26020	2.0	5/64	40	1.6	0.40	120	4.7	.02	
26022	2.0	5/64	50	2.0	0.40	145	5.7	.02	
26023	2.0	5/64	100	3.9	0.40	180	7.1	.03	
26025	2.5	3/32	50	2.0	0.40	145	5.7	.03	
26027	2.5	3/32	100	3.9	0.40	195	7.7	.03	
26028	2.5	3/32	150	6.0	0.40	245	9.6	.04	
26030	3.0	1/8	50	2.0	0.50	145	5.7	.03	
26032	3.0	1/8	60	2.4	0.50	170	6.7	.04	
26033	3.0	1/8	100	3.9	0.50	210	8.3	.04	
26034	3.0	1/8	150	5.9	0.50	260	10.2	.05	
26035	3.5	9/64	60	2.4	0.60	170	6.7	.05	
26040	4.0	5/32	60	2.4	0.80	170	6.7	.05	
26041	4.0	5/32	100	3.9	0.80	210	8.3	.06	
26042	4.0	5/32	150	5.9	0.80	260	10.2	.07	

\*Metric dimensions actual - Inch dimensions approximate



**26090 6pc Precision Slotted Set**  
Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished.

Item No.		lbs.
26090	<b>Slotted:</b> 1.5, 2.0 x 40mm 2.5, 3.0 x 50mm 3.5, 4.0 x 60mm	.27



**26099 8pc Precision Slotted Set**  
Blade high alloy CVM steel. Hard chrome finished. In canvas storage pouch.

Item No.	<b>Slotted:</b>		lbs.
26099	1.0, 1.2, 1.5, 2.0 x 40mm 2.5, 3.0 x 50mm, 3.5, 4.0 x 60mm		.54



**261 Phillips Screwdriver, With Precision Handle** Blade high alloy chrome-vanadium-molybdenum steel. Pkg. 10

Item No.								
No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.
26102	000	40	1.6	2.0	.08	120	4.7	.02
26100	00	40	1.6	2.0	.08	120	4.7	.02
26101	00	75	3.0	2.0	.08	155	6.1	.02
26105	0	50	2.0	3.0	.12	145	5.7	.02
26108	0	75	3.0	3.0	.12	170	6.7	.03
26107	0	100	3.9	3.0	.12	195	7.6	.05
26109	0	150	5.9	3.0	.12	245	9.6	.06
26110	1	60	2.4	4.0	.16	170	6.7	.05
26113	1	80	3.1	4.0	.16	190	7.5	.05
26114	1	100	3.9	4.0	.16	210	8.2	.06
26115	1	150	5.9	4.0	.16	260	10.2	.07

\*Metric dimensions actual - Inch dimensions approximate



**26190 8pc Precision Slotted & Phillips Screwdrivers and Industrial Long Nose Pliers Set**

<b>Item No. Slotted:</b>	1.5 x 40mm
26190	2.0, 2.5 x 50mm, 3.0 x 60mm
<b>Phillips:</b>	00 x 40mm
lbs. .72	0 x 50mm, 1 x 60mm
<b>Industrial Long Nose Pliers</b>	
	6.3"/160mm OAL



**26197 7pc Precision Slotted & Phillips Set** Blade high alloy CVM steel.

<b>Item No. Slotted:</b>	1.5 x 40mm
26197	2.0, 2.5 x 50mm, 3.0 x 60mm
<b>Phillips:</b>	00 x 40mm
lbs. .31	0 x 50mm, 1 x 60mm



**26199 8pc Precision Slotted/Phillips Set**

<b>Item No.</b>	<b>Slotted:</b> 1.0, 2.0 x 40mm, 3.0 x 50mm, 4.0 x 60mm		lbs.
26199	<b>Phillips:</b> 000, 00 x 40mm, 0 x 50mm, 1 x 60mm		.55


In canvas storage pouch

### Wiha Precision Slotted/Phillips Drivers



#### 26092 7pc Precision Slotted & Phillips


**Set** Blade high alloy chrome-vanadium-molybdenum steel.

Item No.		
<b>26092</b>	<b>Slotted:</b>	lbs.
	2.5 x 50mm,	.30
	2.5, 3.0, 4.0 x 100mm	
	3.0, 4.0 x 150mm	
	<b>Phillips:</b>	
	0 x 75mm	



#### 26194 4pc Precision Phillips Set


Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished.

Item No.	Phillips:	
<b>No.</b>	000, 00 x 40mm	lbs.
<b>26194</b>	0 x 50mm, 1 x 60mm	.18



#### 26192 5pc Precision Slotted & Phillips


**Set** Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	Slotted:	
<b>No.</b>	2.5, 3.0, 4.0 x 150mm	lbs. .44
<b>26192</b>	<b>Phillips:</b>	
	0, 1 x 150mm	

### Wiha Pozidriv® Precision Series



#### 262 Pozidriv® Screwdriver, With Precision Handle


Blade high alloy chrome-vanadium-molybdenum steel.  Pkg. 10









Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.
<b>26205</b>	0	50	2.0	3.0	.12	145	5.7	.03
<b>26210</b>	1	60	2.4	4.0	.16	170	6.7	.05

\*Metric dimensions actual - Inch dimensions approximate

### Wiha Hex Inch & Metric Precision Series



**263 Inch** **Inch Hex Driver, With Precision Handle** Inch sizes. Blade high alloy chrome-vanadium-molybdenum steel.  Pkg. 10


Item No.								
No.	Inch	mm	mm	Inch	mm	Inch	lbs.	
<b>26307</b>	0.028	0.7	40	1.6	120	4.7	.02	
<b>26309</b>	0.035	0.9	40	1.6	120	4.7	.02	
<b>26313</b>	0.05	1.3	40	1.6	120	4.7	.02	
<b>26316</b>	1/16	-	50	2.0	145	5.7	.03	
<b>26320</b>	5/64	2.0	50	2.0	145	5.7	.03	
<b>26323</b>	3/32	-	60	2.4	170	6.7	.04	
<b>26327</b>	7/64	-	60	2.4	170	6.7	.04	
<b>26331</b>	1/8	-	60	2.4	170	6.7	.04	
<b>26333</b>	9/64		60	2.4	170	6.7	.05	
<b>26336</b>	5/32		60	2.4	170	6.7	.05	

\*Metric dimensions actual - Inch dimensions approximate











#### 26391 8pc Precision Hex Driver Set - Inch

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	Hex Inch:	
<b>26391</b>	.028, .035, .050 x 1.6"	lbs. .32
	1/16, 5/64 x 2.0"	
	3/32, 7/64, 1/8 x 2.4"	



**263 Metric** **Metric Hex Driver, With Precision Handle** Metric sizes. Blade high alloy chrome-vanadium-molybdenum steel.


Item No.								
No.	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
<b>26307</b>	.7	.028	40	1.6	120	4.7	.02	10
<b>26309</b>	.9	.035	40	1.6	120	4.7	.02	10
<b>26313</b>	1.3	.050	40	1.6	120	4.7	.02	10
<b>26315</b>	1.5	-	50	2.0	145	5.7	.03	10
<b>26320</b>	2.0	5/64	50	2.0	145	5.7	.03	10
<b>26325</b>	2.5	-	60	2.4	170	6.7	.04	10
<b>26330</b>	3.0	-	60	2.4	170	6.7	.04	10
<b>26340</b>	4.0	-	60	2.4	170	6.7	.05	10

\*Metric dimensions actual - Inch dimensions approximate



#### 26390 7pc Precision Hex Driver Set - Metric


Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	Hex Metric:	
<b>26390</b>	.7, .9, 1.3 x 40mm	lbs. .28
	1.5, 2.0 x 50mm	
	2.5, 3.0 x 60mm	




#### 26399 8pc Precision Hex Driver Set - Inch

Blade high alloy CVM steel. Hard chrome finished. In canvas storage pouch

Item No.	Hex Inch:	
<b>26399</b>	.028, .035, .050 x 1.6"	lbs. .55
	1/16, 5/64 x 2.0", 3/32, 7/64, 1/8 x 2.4"	

### Y-Type Precision Driver

#### Y-Type








(Used in iPhone 7 or higher series) 



#### 26601 Y-Type Precision Screwdriver


Blade high alloy CVM steel.

Hard chrome finished.

Item No.							
No.	Size	mm	Inch	mm	Inch	mm	Inch
<b>26601</b>	000	40	1.6	2.0	.08	120	4.75

\*Metric dimensions actual - Inch dimensions approximate

## Wiha Ball End Precision Series




### 264 Inch Ball End Hex Inch Screwdriver

**With Precision Handle** Angle entry up to 30°. Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finish.

Item	No.	Inch	mm	Inch	mm	Inch	lbs.	Pkg.
	26413	.050	40	1.6	120	4.7	.02	10
	26416	1/16	50	2.0	145	5.7	.03	10
	26419	5/64	50	2.0	145	5.7	.03	10
	26423	3/32	50	2.0	145	5.7	.03	10
	26427	7/64	60	2.4	170	6.7	.03	10
	26431	1/8	60	2.4	170	6.7	.05	10
	26436	9/64	60	2.4	170	6.7	.05	10
	26439	5/32	60	2.4	170	6.7	.05	10

\*Metric dimensions actual - Inch dimensions approximate



### 264 Metric Ball End Hex Metric Screwdriver

**With Precision Handle** Angle entry up to 30°. Blade high alloy CVM steel.

Item	No.	mm	Inch	mm	Inch	mm	Inch	lbs.	Pkg.
	26413	1.3	.050	40	1.6	120	4.7	.02	10
	26415	1.5	-	50	2.0	145	5.7	.03	10
	26420	2.0	-	50	2.0	145	5.7	.03	10
	26425	2.5	-	60	2.4	170	6.7	.04	10
	26430	3.0	-	60	2.4	170	6.7	.05	10
	26440	4.0	-	60	2.4	170	6.7	.05	10

\*Metric dimensions actual - Inch dimensions approximate



### 26491 5pc Ball End Hex Driver Set - Metric

Angle entry up to 30°. Blade high alloy chrome-vanadium-molybdenum-steel.

Item	No.	Ball End Hex Metric:	lbs.
	26491	1.3 x 40mm 1.5, 2.0 x 50mm 2.5, 3.0 x 60mm	.25



### 26490 8 Piece Ball End Hex Driver Set - Inch

Angle entry up to 30°. Blade high alloy chrome-vanadium-molybdenum steel.

Item	No.	Hex Inch:	lbs.
	26490	.050 x 1.6, 1/16, 5/64, 3/32 x 2.0, 7/64, 1/8, 9/64, 5/32 x 2.4"	.28



### 26499 8pc Ball End Hex Driver Set - Inch

Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished.

Item	Ball End Hex Inch:	lbs.	
	26499	.050 x 1.6" 1/16, 5/64, 3/32 x 2.0" 7/64, 1/8, 9/64, 5/32 x 2.4"	.62

## Wiha TORX® Precision Series



### 26792 7pc TORX® Screwdriver Set

Blade high alloy chrome-vanadium-molybdenum steel.

Item	No.	TORX®:	lbs.
	26792	T5, T6, T7, T8 x 40mm T9, T10 x 50mm T15 x 60mm	.33

## Wiha TORX® Precision Series



### 267 TORX® Screwdriver, With Precision Handle

Blade high alloy chrome-vanadium-molybdenum steel.

Item	No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
	26701	T1	40	1.6	120	4.7	.01	10
	26702	T2	40	1.6	120	4.7	.02	10
	26703	T3	40	1.6	120	4.7	.02	10
	26704	T4	40	1.6	120	4.7	.02	10
	26705	T5	40	1.6	120	4.7	.02	10
	26706	T6	40	1.6	120	4.7	.02	10
	26707	T7	40	1.6	120	4.7	.02	10
	26708	T8	40	1.6	120	4.7	.03	10
	26709	T9	50	2.0	145	5.7	.03	10
	26710	T10	50	2.0	145	5.7	.03	10
	26715	T15	60	2.4	170	6.7	.05	10
	26720	T20	60	2.4	170	6.7	.05	10

\*Metric dimensions actual - Inch dimensions approximate



### 26790 6pc TORX® Screwdriver Set

Blade high alloy chrome-vanadium-molybdenum steel.

Item	No.	TORX®:	lbs.
	26790	T6, T7, T8 x 40mm T9, T10 x 50mm T15 x 60mm	.30

### 26791 8pc TORX® Screwdriver Set

Item No.	TORX®:
26791	T1, T2, T3, T4, T5, T6, T7, T8



### 26799 8pc TORX® Screwdriver Set

Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished. In canvas storage pouch

Item	No.	TORX®:	lbs.
	26799	T3, T4, T5, T6, T7, T8 x 40mm T9 x T10 x 50mm	.50

## Wiha Pentalobe Precision Series

Wiha Pentalobe drivers will fit fasteners used in "Apple" brand products including iPhone, Mac Book & Mac Air

- Exact fit precision machined tips
- High performance CRM72 tool steel
- Hard chromed finish blades & tips
- Tapered ergonomic handle
- Easy spin finger tip control cap



### 267 Pentalobe Screwdrivers, With

**Precision Handle** Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
26761	PL1	40	1.6	120	4.7	.01	1
26762	PL2	40	1.6	120	4.7	.02	1
26763	PL3	40	1.6	120	4.7	.02	1
26764	PL4	40	1.6	120	4.7	.02	1
26765	PL5	40	1.6	120	4.7	.02	1
26766	PL6	40	1.6	120	4.7	.02	1

\*Metric dimensions actual - Inch dimensions approximate



### 26794 6pc Precision Pentalobe Screwdriver Set

Blade high alloy CVM steel. Hard chrome finished. Super hardened best wear resistance long life.

Item No.	Pentalobe Drivers:	lbs.
26794	PL1, PL2, PL3, PL4, PL5, PL6	.35

## Wiha Nut Driver Precision Series



### 265 Metric Metric Nut Driver With Precision

**Handle** Metric sizes. Blade CVM steel. Hard chrome finished.

Item No.	mm	mm	Inch	mm	Inch	mm	mm	lbs.	Pkg.
26510	1.5	60	2.4	140	5.5	2.5	3.0	.03	10
26515	1.8	60	2.4	140	5.5	2.9	3.5	.03	10
26520	2.0	60	2.4	140	5.5	3.2	4.0	.04	10
26525	2.5	60	2.4	155	6.1	4.0	4.0	.04	10
26530	3.0	60	2.4	155	6.1	5.0	5.0	.05	10
26532	3.2	60	2.4	155	6.1	5.0	5.0	.05	10
26535	3.5	60	2.4	155	6.1	5.3	6.0	.05	10
26540	4.0	60	2.4	155	6.1	5.5	6.0	.05	10
26545	4.5	60	2.4	155	6.1	6.2	7.0	.05	10
26550	5.0	60	2.4	155	6.1	6.8	7.0	.05	10
26555	5.5	60	2.4	170	6.7	7.6	8.0	.06	10
26560	6.0	60	2.4	170	6.7	8.2	9.0	.06	10
26570	7.0	60	2.4	170	6.7	9.6	10.0	.06	10

\*Metric dimensions actual - Inch dimensions approximate



### 26590 8pc Precision Nut Driver Set - Metric

Blade CVM steel.

Item No.	Metric Nut Drivers:	lbs.
26590	2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5, 6.0 x 60mm	.48

### 26592 7pc Nut Driver Set - Metric

Item No.	Metric Nut Drivers:
26592	1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm



### 26598 8pc Precision Nut Driver Set - Metric

Blade high alloy CVM steel. Hard chrome finished. In canvas storage pouch

Item No.	Metric Nut Drivers:	lbs.
26598	2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5, 6.0 x 60mm	.70



### 265 Inch Inch Nut Driver With Precision

**Handle** Inch sizes. Blade CVM steel. Hard chrome finished.

Item No.	Inch	mm	Inch	mm	Inch	mm	mm	lbs.	Pkg.
26523	3/32	60	2.4	155	6.1	.16	.16	.04	10
26527	7/64	60	2.4	155	6.1	.20	.20	.05	10
26531	1/8	60	2.4	155	6.1	.20	.20	.05	10
26536	9/64	60	2.4	155	6.1	.21	.24	.05	10
26539	5/32	60	2.4	155	6.1	.22	.24	.05	10
26547	3/16	60	2.4	155	6.1	.25	.28	.05	10
26556	7/32	60	2.4	170	6.7	.30	.32	.06	10
26563	1/4	60	2.4	170	6.7	.34	.36	.06	10

\*Metric dimensions actual - Inch dimensions approximate



### 26591 8pc Precision Nut Driver Set - Inch

Blade CVM steel.

Item No.	Inch Nut Drivers:	lbs.
26591	3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4" x 2.4"	.47




### 26599 8pc Precision Nut Driver Set - Inch

Blade high alloy CVM steel. Hard chrome finished. In canvas storage pouch

Item No.	Inch Nut Drivers:	lbs.
26599	3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4" x 2.4"	.72

## Wiha Precision Screwdriver Set



<b>92189</b>	<b>Master Technicians Bench Top Set</b> Metal frame. Equipped with 50 precision drivers.
<b>Item No.</b>	<b>Slotted:</b> 1.5, 2.0, 2.5, 3.0, 3.5, 4.0
<b>92189</b>	<b>Phillips:</b> #000, #00, #0, #1
	<b>Pentalobe:</b> PL1, PL2, PL3, PL4
lbs.	<b>TORX®:</b> T1, T2, T3, T4, T5, T6,
3.67	T7, T8, T9, T10
	<b>Metric Hex:</b> 1.27, 1.5, 2.0, 2.5, 3.0
	<b>Inch Hex:</b> .028, .035, .050, 1/16,
	5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
	<b>Metric Nut Drivers:</b> 1.5, 1.8, 2.0,
	2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5
	26810 Chip Lifter



<b>92191</b>	<b>51pc Precision Tool Tray Set</b> Tool box tray. Equipped with 51 precision drivers.
<b>Item No.</b>	<b>Slotted:</b> .8, 1.0, 1.2, 1.5, 1.8, 2.0,
<b>92191</b>	2.5, 3.0, 3.5, 4.0
	<b>Phillips:</b> #000, #00, #0, #1
lbs.	<b>Torx®:</b> T1, T2, T3, T4, T5, T6,
3.14	T7, T8, T9, T10
	<b>Metric Hex:</b> 1.27, 1.5, 2.0, 2.5, 3.0, 4.0
	<b>Inch Hex:</b> .028, .035, .050, 1/16,
	5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
	<b>Metric Nut Drivers:</b> 1.5, 1.8, 2.0,
	2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5
	26810 Chip Lifter



<b>92190</b>	<b>Master Technicians Bench Top Set</b> Metal frame. Equipped with 50 precision drivers.
<b>Item No.</b>	<b>Slotted:</b> .8, 1.0, 1.2, 1.5, 1.8, 2.0,
<b>92190</b>	2.5, 3.0, 3.5, 4.0
	<b>Phillips:</b> #000, #00, #0, #1
lbs.	<b>TORX®:</b> T1, T2, T3, T4, T5, T6,
3.67	T7, T8, T9, T10
	<b>Metric Hex:</b> 1.27, 1.5, 2.0, 2.5, 3.0
	<b>Inch Hex:</b> .028, .035, .050, 1/16,
	5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
	<b>Metric Nut Drivers:</b> 1.5, 1.8, 2.0,
	2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5
	26810 Chip Lifter

## Wiha Magnetizer/Demagnetizer

Magnetize or Demagnetize tools and small parts instantly

**Shatterproof Box** is made from high quality plastic

Uses 2 C8 industrial permanent magnets



(+) to Magnetize

(-) to Demagnetize

**40010 Magnetizer and Demagnetizer**  
To magnetize and demagnetize steel screwdriver blades, tweezers and similar tools. Box high quality plastic, shock-resistant, green, cadmium free.

### Application:

To magnetize, lead tool slowly through the (+) opening, to demagnetize guide tool slowly through the (-) opening.

<b>Item</b>	
<b>No.</b>	Dimensions lbs.
<b>40010</b>	2.1" x 2.0" x 1.1" .30

(Parts under 1" Length or 1/8" Diameter may not demagnetize)

## Wiha Torque Cable Keys



### 286 Torque Cable Key For Threaded Hex Connectors

For torque controlled fastening of cable plug connectors with Hex heads. Used with Wiha-TorqueControl Screwdrivers.

Item No.	Size	mm	mm	mm	Max Nm	lbs.	Pkg.
<b>28620</b>	8mm	4.0	78	218	1.0	.06	1
<b>28622</b>	9mm	4.0	78	218	1.0	.06	1
<b>28626</b>	12mm	4.0	78	218	1.5	.06	1
<b>28627</b>	13mm	4.0	78	218	1.5	.06	1
<b>28629</b>	14mm	4.0	78	218	1.5	.06	1
<b>28633</b>	18mm	4.0	78	218	1.5	.06	1

### 28644 Torque Cable Key For Threaded Hex Connectors - Inch

Item No.	Size	mm	mm	mm	Max Nm	lbs.	Pkg.
<b>28644</b>	1/2"	4.0	78	218	1.5	.06	1



+/-6% accuracy tolerance  
Certificate of calibration

### 28552 Adjustable TorqueVario-S Handle -

**In Newton Meter Scale** EN ISO 6798, BS EN 26789, ASME B107.14M. Ergonomic molded multi-component handle, light and compact. Handle sizes proportioned to optimize torque range. Audible and perceptible click when the torque setting has been attained, automatically resets for next torque cycle.

<b>Item</b>	Newton	
<b>No.</b>	Meter Scale	Increments mm lbs. Pkg.
<b>28552</b>	0.8 - 2.0Nm	.10 Nm 126 - 131 .45 1



**Wiha Soft Grip PicoFinish Precision Screwdrivers**

**The Comfortable Precision Screwdriver**

Soft Grip Handle

Sets In Roll-Up Pouch

CVM tool steel blade, hardened, hard chrome finish

Ergonomic multi-component handle with rotating cap for maximum user comfort and precise control



Ergonomic multi-component handle with rotating cap for maximum user comfort and precise control



**26195 5pc Precision Screwdrivers With Precision Soft PicoFinish Handle**

Item	Slotted:	
No.	1.5, 2.5, 3.5mm	lbs.
26195	Phillips: #0, #1	.25

\* No Pouch - In clamshell



**26196 5pc Precision Screwdrivers With Precision Soft PicoFinish Handle**

Item	Phillips: #0, #1	
No.	Pentalobe: PL1	lbs.
26196	Tri-Wing: #000	.25
	Tweezers: 2a SA ESD Flat Round Tip	

\* No Pouch - In clamshell



**26198 11pc Smartphone Precision Screwdrivers With Precision Soft PicoFinish Handle**

Item	Slotted: 1.8mm	
No.	Phillips: #000, #00, #0	
26198	TORX®: T3, T4, T5, T6	
	Pentalobe: PL1	
lbs.	Tri-Wing: #000	
.59	Tweezers: PSF SA ESD Long Flat Tip	



**260 Slotted Precision Screwdriver, With PicoFinish Handle**

Blade CVM steel, hardened, hard chromed.

Item	↓	↓	←	←	←	←	
No.	mm	Inch	mm	Inch	mm	Inch	Pkg.
26050	0.8	.03	40	1.6	134	5.3	10
26051	1.0	.04	40	1.6	134	5.3	10
26052	1.2	.05	40	1.6	134	5.3	10
26053	1.5	.06	40	1.6	134	5.3	10
26055	1.8	.07	40	1.6	134	5.3	10
26060	2.0	.08	40	1.6	140	5.5	10
26061	2.0	.08	60	2.4	160	6.3	10
26065	2.5	.09	50	2.0	150	5.9	10
26066	2.5	.09	75	3.0	175	6.9	10
26068	2.5	.09	100	3.9	200	7.9	10
26070	3.0	.13	50	2.0	150	5.9	10
26072	3.0	.13	100	3.9	200	7.9	10
26073	3.0	.13	150	5.9	250	9.8	10
26074	3.5	.14	60	2.4	160	6.3	10
26076	4.0	.16	60	2.4	160	6.3	10
26079	4.0	.16	100	3.9	200	7.9	10
26080	4.0	.16	150	5.9	250	9.8	10

\*Metric dimensions actual - Inch dimensions approximate



**261 Phillips Precision Screwdriver, With Soft PicoFinish Precision Handle**

Blade high alloy CVM steel. Hard chrome finished.

Item	+	←	←	←	←	←	
No.	Size	mm	Inch	mm	Inch	mm	Inch
26130	000	40	1.6	2.0	.08	134	5.3
26132	00	40	1.6	2.0	.08	134	5.3
26135	0	50	2.0	3.0	.12	150	5.9
26136	0	75	3.0	3.0	.12	175	6.9
26140	1	60	2.4	4.0	.16	160	6.3
26142	1	80	3.1	4.0	.16	180	7.1
26145	1	150	5.9	4.0	.16	250	9.8

\*Metric dimensions actual - Inch dimensions approximate



**26193 8pc Slotted & Phillips Precision Driver Set, With Soft PicoFinish Handle**

Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit. In storage pouch

Item	Slotted:	
No.	1.0, 1.5, 2.0 x 40mm	lbs.
26193	2.5 x 50mm, 3.5 x 60mm	.55
	Phillips: 00 x 40mm	
	0 x 50mm, 1 x 60mm	



**26093 8pc Slotted Precision Screwdriver Set, With Soft PicoFinish Handle**

In storage pouch

Item		
No.	Slotted: .8, 1.2, 1.5, 2.0 x 40mm	lbs.
26093	2.5, 3.0 x 50mm, 3.5, 4.0 x 60mm	.54

## Wiha Pico Soft Grip TORX®



**267 TORX® Screwdriver, With Precision Soft PicoFinish Handle** Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item						
No.	Size	mm	Inch	mm	Inch	Pkg.
26732	T1	40	1.6	134	5.3	10
26733	T2	40	1.6	134	5.3	10
26735	T3	40	1.6	134	5.3	10
26736	T4	40	1.6	134	5.3	10
26737	T5	40	1.6	134	5.3	10
26739	T6	40	1.6	140	5.5	10
26741	T7	40	1.6	140	5.5	10
26743	T8	40	1.6	140	5.5	10
26745	T9	50	2.0	150	5.9	10
26747	T10	50	2.0	150	5.9	10
26749	T15	60	2.4	160	6.3	10
26751	T20	60	2.4	160	6.3	10

\*Metric dimensions actual - Inch dimensions approximate

In storage pouch



**26793 8pc TORX® Precision Driver Set, With Soft PicoFinish Handle** Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit.

Item	TORX®:	
No.	T1, T2, T3, T4,	lbs.
26793	T5, T6, T7, T8	.50

In storage pouch



**26796 8pc TORX® Precision Driver Set, Soft PicoFinish Handle** Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit.

Item	TORX®:	
No.	T5, T6, T7, T8 x 40mm	lbs. .57
26796	T9, T10 x 50mm, T15, T20 x 60mm	

## Pico Soft Grip Hex Inch & Metric



**263 Hex Inch Screwdriver, With Precision Soft PicoFinish Handle** Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item						
No.	Inch	mm	Inch	mm	Inch	Pkg.
26341	0.028(0.7)	40	1.6	134	5.3	10
26343	0.035(0.9)	40	1.6	134	5.3	10
26345	0.05(1.3)	40	1.6	134	5.3	10
26349	5/64(2.0)	50	2.0	150	5.9	10
26363	1/16	50	2.0	144	5.7	10
26367	3/32	60	2.4	160	6.3	10
26369	7/64	60	2.4	160	6.3	10
26371	1/8	60	2.4	160	6.3	10

\*Metric dimensions actual - Inch dimensions approximate



In storage pouch



**26392 8pc Hex Inch Precision Driver Set, Soft PicoFinish Handle** Blade high alloy CVM steel, hardened, hard chromed.

Item	Hex Inch:	
No.	.028, .035, .050 x 1.6"	.24
26392	5/64, 1/16 x 2.0", 3/32, 7/64, 1/8 x 2.4"	



**263 Hex Metric Driver, With Precision Soft PicoFinish Handle**

Item						
No.	mm	mm	Inch	mm	Inch	Pkg.
26341	.7(.028)	40	1.6	134	5.3	10
26343	.9(.035)	40	1.6	134	5.3	10
26345	1.3(.050)	40	1.6	134	5.3	10
26347	1.5	50	2.0	144	5.7	10
26349	2.0(5/64)	50	2.0	150	5.9	10
26351	2.5	60	2.4	160	6.3	10
26353	3.0	60	2.4	160	6.3	10

\*Metric dimensions actual - Inch dimensions approximate



In storage pouch



**26393 7pc Hex Metric Precision Driver Set, Soft PicoFinish Handle** Blade high alloy CVM steel, hardened, hard chromed.

Item No.	Hex Metric:	
26393	.7, .9, 1.3 x 40mm	.22
	1.5, 2.0 x 50mm, 2.5, 3.0 x 60mm	

## Pico Soft Grip Ball End Inch & Metric



**264 Ball End Hex Inch Screwdriver, With Precision Soft PicoFinish Handle** Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item						
No.	Inch	Inch	mm	Inch	mm	pkg.
26455	1/16	2.0	50	5.9	150	10
26457	5/64	2.0	50	5.9	150	10
26459	3/32	2.0	50	5.9	150	10
26461	7/64	2.4	60	6.3	160	10
26463	1/8	2.4	60	6.3	160	10
26465	9/64	2.4	60	6.3	160	10
26467	5/32	2.4	60	6.3	160	10

\*Metric dimensions actual - Inch dimensions approximate



**26493 7pc Inch Ball End Hex Precision Driver Set, With Soft PicoFinish Handle** Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit. In storage pouch

Item	
No.	Ball End Hex Inch: .27
26493	1/16, 5/64, 3/32 x 2.0" 7/64, 1/8, 9/64, 5/32 x 2.4"



**264 Ball End Hex Metric Screwdriver, With Precision Soft PicoFinish Handle.** Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item						
No.	mm	mm	Inch	mm	Inch	pkg.
26441	1.3	40	1.6	134	5.3	10
26443	1.5	50	2.0	150	5.9	10
26445	2.0	50	2.0	150	5.9	10
26447	2.5	60	2.4	160	6.3	10
26449	3.0	60	2.4	160	6.3	10

\*Metric dimensions actual - Inch dimensions approximate

**Pico Soft Grip Nut Drivers Inch & Metric**



**265 Inch Nut Drivers, With Precision Soft PicoFinish Handle** Blade high alloy chrome-vanadium-molybdenum tool steel, hardened, hard chrome finish.

Item						
No.	Inch	Inch	mm	Inch	mm	pkg.
26571	3/32	2.4	60	6.3	160	10
26572	7/64	2.4	60	6.3	160	10
26573	1/8	2.4	60	6.3	160	10
26574	9/64	2.4	60	6.3	160	10
26575	5/32	2.4	60	6.3	160	10
26576	3/16	2.4	60	6.3	160	10
26577	7/32	2.4	60	6.3	160	10
26578	1/4	2.4	60	6.3	160	10

\*Metric dimensions actual - Inch dimensions approximate



**265 Metric Nut Drivers, With Precision PicoFinish Handle** Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item						
No.	mm	mm	Inch	mm	Inch	pkg.
26579	1.5	60	2.4	160	6.3	10
26581	2.0	60	2.4	160	6.3	10
26582	2.5	60	2.4	160	6.3	10
26583	3.0	60	2.4	160	6.3	10
26584	3.5	60	2.4	160	6.3	10
26585	4.0	60	2.4	160	6.3	10
26586	4.5	60	2.4	160	6.3	10
26587	5.0	60	2.4	160	6.3	10
26588	5.5	60	2.4	160	6.3	10
26589	6.0	60	2.4	160	6.3	10

\*Metric dimensions actual - Inch dimensions approximate



**26593 8pc Inch Nut Driver Set, With Precision Soft PicoFinish Handle** Blade high alloy CVM tool steel, hardened, hard chrome finish. Chrom-Top finish on tip for a perfect fit. In storage pouch

Item	Inch Nut Drivers:		lbs.	.72
No.	3/32, 7/64, 1/8, 9/64,			
26593	5/32, 3/16, 7/32, 1/4" x 2.4"			



**26596 8pc Metric Nut Driver Set, With Precision Soft PicoFinish Handle**

Item	Metric Nut Drivers:	
No.	2.0, 2.5, 3.0, 3.5, 4.0,	lbs.
26596	4.5, 5.0, 5.5 x 60mm	.66

**Pico Soft Grip Pentalobe**



**267 Pentalobe Screwdriver, With Precision Soft PicoFinish Handle** Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item						
No.	Size	Inch	mm	Inch	mm	pkg.
26771	PL1	1.6	40	5.5	140	10
26772	PL2	1.6	40	5.5	140	10
26773	PL3	1.6	40	5.5	140	10
26774	PL4	1.6	40	5.5	140	10
26775	PL5	1.6	40	5.5	140	10
26776	PL6	1.6	40	5.5	140	10

\*Metric dimensions actual - Inch dimensions approximate



**26795 6pc Precision Pentalobe Driver Set, Soft PicoFinish Handle** Blade high alloy CVM steel. Hard chrome finished.

Item No.	Pentalobe Drivers:	
26795	PL1, PL2, PL3, PL4, PL5, PL6	lbs.
		.40

**Pico Soft Grip Precision Chip Lifter**



**26815 Soft PicoFinish Precision Chip Lifter** Blade CVM steel, hardened, hard chromed.

Item							
No.	mm	mm	mm	mm	Inch	lbs.	Pkg.
26815	1	3.5	50	150	5.9	.03	1

Standard Soft PicoFinish handle

**Pico Soft Grip Y-Type Precision Driver**

**Y-Type**  
(Used in iphone 7 or higher series)



**266 Y-Type Precision Screwdriver, With Soft PicoFinish Precision Handle** Blade high alloy CVM steel. Hard chrome finished.

Item							
No.	Size	mm	Inch	mm	Inch	mm	Inch
26631	000	40	1.6	2.0	.08	140	5.5



**75973 23pc Micro Bit Set, With Soft PicoFinish Handle** CVM steel Micro Bits, hardened, on 4 mm hex stock. Ergonomic multi-component handle with rotating cap for maximum user comfort and precise control.

Item	Slotted:	1.5, 2.0, 2.5, 3.0, 3.5mm
No.	Phillips:	000, 00, 0, 1, 2
75973	TORX®:	T1, T2, T3, T4, T5, T6, T7, T8, T9, T10
lbs.	PicoFinish® Precision Handle	
.82	Micro Bit Holder - 100mm	
	Micro Bit Socket Adapter 1/4"	

## PicoFinish MagicSpring Precision Screwdrivers



**267** MagicSpring Screw Holding **TORX®** Screwdriver, With Wiha-Precision Soft PicoFinish Handle. Blade high alloy CVM steel, hardened, hard chromed. Molded on ergonomic Wiha-PicoFinish precision handle, molded on, soft grips.

Item	Icon	Icon	Icon	Icon	Icon	Icon	
No.	Size	mm	Inch	mm	Inch	lbs.	Pkg.
26721	T6	40	1.6	140	5.5	.03	10
26723	T7	40	1.6	140	5.5	.03	10
26725	T8	40	1.6	140	5.5	.03	10
26727	T9	50	2.0	150	5.9	.04	10
26729	T10	50	2.0	150	5.9	.04	10
26731	T15	60	2.4	160	6.3	.04	10

\*Metric dimensions actual - Inch dimensions approximate



**26798** 6pc MagicSpring Screw Holding **TORX®** Screwdriver Set, With Wiha-Precision Soft PicoFinish Handle

Blade high alloy CVM steel, hardened, hard chromed. Molded on ergonomic Wiha-PicoFinish precision handle, molded on, soft grips. In storage pouch

Item	Icon	Icon
No.	MagicSpring <b>TORX®</b> :	lbs.
26798	T6, T7, T8 x 40mm	.45
	T9, T10, T15 x 50mm	



**91118** Rugged Polyester Canvas Storage Pouch. Holds 8 Precision Tools up to 170mm in length. Folding pouch. Has security flaps and velcro closer.

Item	Icon	Icon	
No.	Size	lbs.	pkg.
91118	14 1/2" W x 7 3/4" L	.13	1

## Insulated PicoFinish Precision Screwdrivers

1000Volt



**320** Insulated Slotted PicoFinish Screwdrivers. Individually Tested Protective Insulation 1000Volt AC, VDE & GS Tested.

High quality CV steel, through hardened, black finish. Rotating cap for precise turning and control with fingertip.

Item	Icon	Icon	Icon	Icon	Icon	Icon
No.	mm	Inch	mm	mm	lbs.	Pkg.
32000	1.5	.06	40	154	.05	1
32001	2.0	.08	40	154	.07	1
32002	2.5	.10	60	160	.07	1
32003	3.0	.12	60	160	.08	1
32004	3.5	.14	60	160	.08	1

1000Volt



**321** Insulated Phillips PicoFinish Screwdrivers. Individually Tested Protective Insulation 1000Volt AC, VDE & GS Tested.

Item	Icon	Icon	Icon	Icon	Icon
No.	Size	mm	mm	lbs.	Pkg.
32106	00	40	154	.05	1
32107	0	60	160	.07	1
32108	1	60	160	.08	1

1000Volt



Individually Tested Protective Insulation 1000Volt AC, VDE and GS Tested

**32088** 8pc Slotted/Phillips PicoFinish Set

Item	Icon	Icon
No.	Slotted: 1.5, 2.0, 2.5, 3.0, 3.5mm	lbs.
32088	Phillips: #00, #0, #1	.35


1000Volt



**32085** 5pc Slotted/Phillips PicoFinish Set

Item	Icon	Icon
No.	Slotted: 1.5, 2.5, 3.5mm	lbs.
32085	Phillips: #0, #1	.26

## Wiha Protturn Precision Screwdrivers



Tip precision ground for exact fit

Molded on ergonomic handle

Rotating cap for precise turning and control with fingertip

Tapered handle allows rapid rotation

Blade CVM steel, black finish blades



**62994** 14pc Inch/Metric Ball End Hex

Work Tech Pack Protturn precision ball retainer handle & 13 Wiha interchangeable blades.

**62994** Set includes the following blades:

Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0mm

lbs. .66

Set in canvas storage pouch



**96800** Protturn Precision Chip Lifter

Molded on precision handle. Blade CVM tool steel, hardened, black finish.

Item	Icon	Icon	Icon	Icon	Icon	Icon
No.	Size	mm	mm	Inch	lbs.	pkg.
96800	1.0	50	145	5.7	.07	1

Wiha SYSTEM 4 Precision Handles and Blades

**Rotating Cap**  
for precise turning & control

**Tapered Handle**  
allows rapid rotation, requires less clearance

**Blades**  
chrome-vanadium-molybdenum steel, hardened, hard chromed. On 4mm Hex shafts

**Tips**  
Exact fit, precision machined

**Precision Handle**  
high quality plastic, cadmium free. ESD Safe or Standard styles

15mm  
Collet Lock Handle adjustable blade length from 15 to 95mm / .6" to 3.75"  
95mm



**26900 SYS 4 Standard Precision Handle**, with rotating control cap. Accepts all SYSTEM 4 interchangeable blades. Wiha Precision handle, tapered, impact resistant. Ball retainer hold. 110mm/4.3" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
26900	4.0	.1574	14.0	.55	.04



**28000 ESD Safe Dissipative Precision Handle** with rotating control cap. Surface resistant 10<sup>6</sup>-10<sup>9</sup> Ohms. 4 mm hex retainer for all SYSTEM 4 interchangeable blades. Tapered handle, high quality plastic, impact resistant. Ball retainer hold. 110mm/4.3" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
28000	4.0	.1574	14.0	.55	.04



**269 SYSTEM 4 Slotted Reversible Blade** High alloy CVM steel, hardened, hard chromed. Wiha vapor Chrome-Top finish on tips.

Item					
No.	mm	mm	mm	Inch	lbs.
26903	1.5 + 3.0	120	4.7	.05	
26904	2.0 + 3.5	120	4.7	.05	
26905	2.5 + 4.0	120	4.7	.06	



**269 SYSTEM 4 Pozidriv® Reversible Blade** High alloy CVM steel, hardened, hard chromed. Wiha vapor Chrome-Top finish on tips.

Item					
No.	Size	Size	mm	Inch	lbs.
26922	0 + 1	120	4.7	.03	

Notes:

Blank lines for notes.



**269 SYSTEM 4 Phillips Reversible Blade** High alloy CVM steel, hardened, hard chromed. Wiha vapor Chrome-Top finish on tips.

Item					
No.	Size	Size	mm	Inch	lbs.
26911	000 + 00	120	4.7	.03	
26912	0 + 1	120	4.7	.03	



**269 SYS 4 TORX® Reversible Blade** High alloy CVM steel, hardened, vapor chrome protected, Wiha vapor Chrome-Top finish on tips. 120mm/4.7" OAL.

Item				
No.	Size	Size	lbs.	
26951	T6 + T8	.03		
26952	T7 + T9	.03		
26953	T10 + T15	.03		
26954	T15 + T20	.03		



**269 SYSTEM 4 Combined Slotted/Phillips Reversible Blade** High alloy CVM steel, hardened, hard chromed.

Item					
No.	mm	Size	mm	Inch	lbs.
26971	1.5+	000	120	4.7	.05
26972	2.0+	00	120	4.7	.05
26973	3.0+	0	120	4.7	.05
26974	4.0+	1	120	4.7	.06



**269 SYSTEM 4 TORX® Interchangeable Blade** High alloy CVM steel, hardened, Wiha vapor Chrome-Top finish on tips. 120mm/4.7" OAL

Item		
No.	Size	lbs.
26955	T3	.03
26956	T4	.03
26957	T5	.03



Wiha SYSTEM 4 Drive-Loc Precision Locking Tools



**26906 SoftFinish® Cushion Grip Drive-Loc Handle** 4 mm hex retainer for all SYSTEM 4 interchangeable blades. Ball retainer hold. 105mm/4.13" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
26906	4.0	.1574	23	.91	.08



**26961 ESD Safe Dissipative Precision Drive-Loc Handle** Surface resistant 10<sup>6</sup>-10<sup>9</sup> Ohms. 4 mm hex retainer for all SYSTEM 4 interchangeable blades. Ball retainer hold. 105mm/4.13" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
26961	4.0	.1574	23	.91	.08



**269 SYSTEM 4 Slotted Drive-Loc Reversible Locking Blades**  
On 4mm Hex blades

Item			
No.	mm	mm	lbs.
26958	1.5 + 3.0		.02
26959	2.0 + 3.5		.02
26960	2.5 + 4.0		.02



**269 SYSTEM 4 Phillips Drive-Loc Reversible Locking Blades**  
On 4mm Hex blades

Item			
No.	Size	Size	lbs.
26975	000 + 00		.02
26976	0 + 1		.02



**280 SYSTEM 4 Pozidriv® Drive-Loc Reversible Locking Blades**  
On 4mm Hex blades

Item			
No.	Size	Size	lbs.
28002	0 + 1		.02



**269 SYSTEM 4 TORX® Drive-Loc Reversible Locking Blades**  
On 4mm Hex blades

Item			
No.	Size	Size	lbs.
26977	T1 + T2		.02
26978	T3 + T4		.02
26979	T5 + T6		.02
26980	T6 + T8		.02
26981	T7 + T9		.02
26982	T10 + T15		.02
26983	T15 + T20		.02



**280 SYSTEM 4 Metric Hex Drive-Loc Reversible Locking Blades**  
On 4mm Hex blades

Item			
No.	mm	mm	lbs.
28003	1.3 + 1.3		.02
28004	1.5 + 1.5		.02
28005	2.0 + 2.0		.02
28006	2.5 + 2.5		.02
28007	3.0 + 3.0		.02
28008	4.0 + 4.0		.02



**280 SYSTEM 4 Metric Nut Drivers Drive-Loc Reversible Locking Blades**  
On 4mm Hex blades

Item			
No.	mm	mm	lbs.
28012	3.2 + -		.02



**26985 12pc Drive-Loc IV Precision ESD Safe Set** In storage pouch

Item No.	ESD Safe Drive-Loc Handle
26985	Slotted: 1.5x3.0, 2.0x3.5, 2.5x4.0 lbs. .44 Phillips: 000x00, 0x1 TORX®: T1xT2, T3xT4, T5xT6, T6xT8, T7xT9, T10xT15




**26930 7pc Drive-Loc IV TORX® Precision ESD Safe Set** In storage pouch

Item No.	ESD Safe Drive-Loc Handle
26930	TORX®: T3xT4, T5xT6, T6xT8, T7xT9, T10xT15, T15xT20 lbs. .56

Micro Bits Made in Germany

## Wiha SYSTEM 4 Micro Bits - 10 Bit Packs



CVM steel, hardened, on 4 mm hex stock.





Bits High alloy CVM steel, hardened

Tips Exact fit, precision machined

Use bits directly in handle or with 4" bit extension







**756 SYSTEM 4 Hex Metric Micro Bits**

Item				
No.	mm	mm	Inch	lbs.
75616	.7	28	1.1	.06
75617	.9	28	1.1	.06
75618	1.3	28	1.1	.06
75619	1.5	28	1.1	.07
75620	2.0	28	1.1	.07
75621	2.5	28	1.1	.07
75622	3.0	28	1.1	.08
75623	4.0	28	1.1	.08







**756 SYSTEM 4 TORX® Micro Bits**

Item				
No.	Size	mm	Inch	lbs.
75660	T1	28	1.1	.06
75661	T2	28	1.1	.06
75662	T3	28	1.1	.06
75663	T4	28	1.1	.06
75664	T5	28	1.1	.06
75665	T6	28	1.1	.06
75666	T7	28	1.1	.06
75667	T8	28	1.1	.07
75668	T9	28	1.1	.07
75669	T10	28	1.1	.07
75670	T15	28	1.1	.08
75671	T20	28	1.1	.08







**756 SYSTEM 4 Slotted Micro Bits**

Item				
No.	mm	mm	Inch	lbs.
75602	0.8	28	1.1	.06
75603	1.2	28	1.1	.06
75604	1.5	28	1.1	.06
75605	1.8	28	1.1	.06
75606	2.0	28	1.1	.07
75607	2.5	28	1.1	.07
75608	3.0	28	1.1	.07
75609	3.5	28	1.1	.07
75610	4.0	28	1.1	.08







**756 SYSTEM 4 Hex Inch Micro Bits**

Item				
No.	Inch	mm	Inch	lbs.
75628	.028	28	1.1	.06
75629	.035	28	1.1	.06
75630	.050	28	1.1	.06
75631	1/16	28	1.1	.06
75632	5/64	28	1.1	.06
75633	3/32	28	1.1	.07
75634	7/64	28	1.1	.07
75635	1/8	28	1.1	.07
75636	9/64	28	1.1	.08
75637	5/32	28	1.1	.08







**756 SYSTEM 4 Security TORX® Micro Bits**

Item				
No.	Size	mm	Inch	lbs.
75681	T10s	28	1.1	.07
75683	T20s	28	1.1	.08







**756 SYSTEM 4 Phillips Micro Bits**

Item				
No.	Size	mm	Inch	lbs.
75611	000	28	1.1	.06
75612	00	28	1.1	.06
75613	0	28	1.1	.06
75614	1	28	1.1	.07
75615	2	28	1.1	.07







**756 SYS 4 Metric Security Hex Micro Bits**

Item				
No.	mm	mm	Inch	lbs.
75624	2.0	28	1.1	.06
75626	3.0	28	1.1	.07
75627	4.0	28	1.1	.08







**756 SYSTEM 4 Inch Nut Setters**

Item No.				
Inch	Inch	mm	Inch	lbs.
75644	5/64	30	1.2	.07
75645	3/32	30	1.2	.07
75646	7/64	30	1.2	.07
75647	1/8	30	1.2	.07
75648	9/64	30	1.2	.08
75649	5/32	30	1.2	.08
75650	3/16	30	1.2	.08
75651	7/32	30	1.2	.09







**756 SYSTEM 4 Pentalobe Micro Bits**

Item				
No.	Size	mm	Inch	lbs.
75672	PL1	28	1.1	.06
75673	PL2	28	1.1	.06
75674	PL3	28	1.1	.07
75675	PL4	28	1.1	.07
75676	PL5	28	1.1	.07







**756 SYS 4 Security Hex Inch Micro Bits**

Item				
No.	Inch	mm	Inch	lbs.
75638	5/64	28	1.1	.06
75639	3/32	28	1.1	.06
75641	1/8	28	1.1	.07



**756 SYSTEM 4 Metric Nut Setters**

Item No.				
Metric	mm	mm	Inch	lbs.
75652	2.0	30	1.2	.07
75653	2.5	30	1.2	.07
75654	3.0	30	1.2	.07
75655	3.5	30	1.2	.07
75656	4.0	30	1.2	.08
75657	4.5	30	1.2	.08
75658	5.0	30	1.2	.08
75659	5.5	30	1.2	.09



**Wiha SYSTEM 4 Micro Bits**

**SYSTEM 4 Handles & Micro Bits**

**Rotating Cap** for precise turning and control

**Tips**  
Exact fit, precision machined

**Tapered Handle** allows rapid rotation, requires less clearance

**Bits** High alloy CVM steel, hardened

Use bits directly in handle or with 4" bit extension

**75800 SYSTEM 4 Standard Precision Bit Handle** Accepts all SYSTEM 4 Series bits. 110mm/4.3" OAL

Item	Standard	Slotted	Phillips	TORX	Security TORX
No.	mm	Inch	mm	Inch	lbs.
75800	4.0	.1574	14.0	.55	.06

**75801 SYSTEM 4 ESD Safe Dissipative Precision Bit Handle** 110mm/4.3" OAL

**Advantages:**

- For working in ESD sensitive applications Surface resistant 10<sup>6</sup>-10<sup>9</sup> Ohms
- Ball retainer holds bits securely in place
- Accepts all SYSTEM 4 Series bits

Item	Standard	Slotted	Phillips	TORX	Security TORX
No.	mm	Inch	mm	Inch	lbs.
75801	4.0	.1574	14.0	.55	.06

**SYSTEM 4 Micro Bit Extension Blades**

**75900 Extension Blade For SYS 4 Micro Bits** Shaft CVM steel, hardened, corrosion protected. Ball retainer bit extension for 4mm bits.

Item	Standard	Slotted	Phillips	TORX	Security TORX
No.	Size	mm	mm	lbs.	
75900	4.0	100	4.0	.07	

**75901 Magnetic Bit Extension Blade For SYS 4 Micro Bits** Shaft CVM steel, hardened, corrosion protected. Magnetic bit holder.

Item	Standard	Slotted	Phillips	TORX	Security TORX
No.	Size	mm	mm	lbs.	
75901	4.0	100	4.0	.04	

**750 SYSTEM 4 Slotted Micro Bits** CVM steel, hardened, on 4 mm hex stock.

Item	Standard	Slotted	Phillips	TORX	Security TORX
No.	mm	mm	Inch	lbs.	
75008	0.8	28	1.1	.01	
75012	1.2	28	1.1	.01	
75015	1.5	28	1.1	.01	
75018	1.8	28	1.1	.01	
75020	2.0	28	1.1	.01	
75025	2.5	28	1.1	.01	
75030	3.0	28	1.1	.01	
75035	3.5	28	1.1	.01	
75040	4.0	28	1.1	.01	

**751 SYSTEM 4 Phillips Micro Bits** CVM steel, hardened, on 4 mm hex stock.

Item	Standard	Slotted	Phillips	TORX	Security TORX
No.	Size	mm	Inch	lbs.	
75105	000	28	1.1	.01	
75110	00	28	1.1	.01	
75115	0	28	1.1	.01	
75120	1	28	1.1	.01	
75125	2	28	1.1	.02	

**753 SYSTEM 4 Hex Metric Micro Bits** CVM steel, hardened, on 4 mm hex stock.

Item	Standard	Slotted	Phillips	TORX	Security TORX
No.	mm	mm	Inch	lbs.	
75307	.7	28	1.1	.01	
75309	.9	28	1.1	.01	
75313	1.3	28	1.1	.01	
75315	1.5	28	1.1	.01	
75320	2.0	28	1.1	.01	
75325	2.5	28	1.1	.01	
75330	3.0	28	1.1	.01	
75340	4.0	28	1.1	.01	

**753 SYSTEM 4 Hex Inch Micro Bits** CVM steel, hardened, on 4 mm hex stock.

Item	Standard	Slotted	Phillips	TORX	Security TORX
No.	Inch	mm	Inch	lbs.	
75307	.028	28	1.1	.01	
75309	.035	28	1.1	.01	
75313	.050	28	1.1	.01	
75350	1/16	28	1.1	.01	
75352	5/64	28	1.1	.01	
75354	3/32	28	1.1	.01	
75356	7/64	28	1.1	.01	
75358	1/8	28	1.1	.01	
75360	9/64	28	1.1	.01	
75340	5/32	28	1.1	.01	

**757 SYSTEM 4 TORX® Micro Bits** CVM steel, hardened, on 4 mm stock.

Item	Standard	Slotted	Phillips	TORX	Security TORX
No.	Size	mm	Inch	lbs.	
75701	T1	28	1.1	.01	
75702	T2	28	1.1	.01	
75703	T3	28	1.1	.01	
75704	T4	28	1.1	.01	
75705	T5	28	1.1	.01	
75706	T6	28	1.1	.01	
75707	T7	28	1.1	.01	
75708	T8	28	1.1	.01	
75709	T9	28	1.1	.01	
75710	T10	28	1.1	.01	
75715	T15	28	1.1	.01	
75720	T20	28	1.1	.01	

**757 SYSTEM 4 Security TORX® Micro Bits**

Item	Standard	Slotted	Phillips	TORX	Security TORX
No.	Size	mm	Inch	lbs.	
75735	T10s	28	1.1	.01	
75742	T20s	28	1.1	.01	

**753 SYS 4 Metric Security Hex Micro Bits** CVM steel, hardened, on 4 mm hex stock.

Item	Standard	Slotted	Phillips	TORX	Security TORX
No.	mm	mm	Inch	lbs.	
75322	2.0	28	1.1	.01	
75332	3.0	28	1.1	.01	
75342	4.0	28	1.1	.01	

**753 SYS 4 Security Hex Inch Micro Bits**

Item	Standard	Slotted	Phillips	TORX	Security TORX
No.	Inch	mm	Inch	lbs.	
75362	5/64	28	1.1	.01	
75364	3/32	28	1.1	.01	
75366	7/64	28	1.1	.01	
75368	1/8	28	1.1	.01	
75370	9/64	28	1.1	.01	
75372	5/32	28	1.1	.01	

**Micro Bit 1/4" Drive Power Tool Adapter For 4mm Bits**

2.3" OAL

**75902 Micro Bit 1/4" Drive Power Tool Adapter** CVM steel, hardened, corrosion protected.

Item	Standard	Slotted	Phillips	TORX	Security TORX
No.	Size	mm	mm	lbs.	
75902	4.0	60	4.0	.07	

## Wiha SYSTEM 4 Micro Bits



**757 SYSTEM 4 Pentalobe Micro Bits** CVM steel, hardened, on 4 mm hex stock.

Item No.	Size	mm	Inch	lbs.
75743	PL1	28	1.1	.01
75744	PL2	28	1.1	.01
75745	PL3	28	1.1	.01
75746	PL4	28	1.1	.01
75747	PL5	28	1.1	.01
75748	PL6	28	1.1	.01




**758 SYSTEM 4 Metric & Inch Nut Setters** CVM steel, hardened, on 4 mm hex stock.

Item No.	Metric	mm	mm	Inch	lbs.
75820	2.0	30	1.2	.01	
75821	2.5	30	1.2	.01	
75822	3.0	30	1.2	.01	
75823	3.5	30	1.2	.01	
75824	4.0	30	1.2	.01	
75825	4.5	30	1.2	.01	
75826	5.0	30	1.2	.01	
75827	5.5	30	1.2	.01	

Item No.	Inch	Inch	mm	Inch	lbs.
75810	5/64	30	1.2	.01	
75811	3/32	30	1.2	.01	
75812	7/64	30	1.2	.01	
75813	1/8	30	1.2	.01	
75814	9/64	30	1.2	.01	
75815	5/32	30	1.2	.01	
75816	3/16	30	1.2	.01	
75817	7/32	30	1.2	.01	

## Micro Bit Replacement Packs On 4mm Hex Stock



**75982 10pc SYSTEM 4 Hex Inch Micro Bit Replacement Pack**


CVM steel, hardened, on 4 mm hex stock.

Item No.

**75982 SYSTEM 4 Micro Bit Set**

Hex Inch: .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

lbs. .06



**75987 10pc SYSTEM 4 Slotted & Phillips Micro Bit Replacement Pack**

CVM steel, hardened, on 4 mm hex stock.

Item No.

**75987 SYSTEM 4 Micro Bit Set**

Slotted: 1.5, 2.0, 2.5, 3.0, 3.5mm

Phillips: #000, 00, 0, 1

lbs. .06



**75984 10pc SYSTEM 4 Slotted Micro Bit Replacement Pack**

CVM steel, hardened, on 4 mm hex stock.

Item No.

**75984 SYSTEM 4 Micro Bit Set**

Slotted: 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm

lbs. .06



**75988 10pc SYSTEM 4 TORX Micro Bit Replacement Pack**

CVM steel, hardened, on 4 mm hex stock.

Item No.

**75988 SYSTEM 4 Micro Bit Set**

TORX: T1, T2, T3, T4, T5, T6, T7, T8, T9, T10

lbs. .06



**75986 10pc SYSTEM 4 Phillips & Pentalobe Micro Bit Replacement Pack**

CVM steel, hardened, on 4 mm hex stock.

Item No.

**75986 SYSTEM 4 Micro Bit Set**

Phillips: #000, 00, 0, 1

Pentalobe: PL1, PL2, PL3, PL4, PL5, PL6

lbs. .06

## 1/4" Drive Micro Bit Tool Adapters



**75802 Micro Bit To 1/4" Drive Insert Bit Adapter** magnets to hold 4mm Micro Bits

Item No.	Size	mm	mm	lbs.
75802	4.0	25	4.0	.01



**75803 Long Micro Bit To 1/4" Drive Insert Bit Adapter** Uses spring clip non-magnetic to hold 4mm Micro Bits

Item No.	Size	mm	mm	lbs.
75803	4.0	38	4.0	.02

## Micro Bit 4mm To 1/4" Socket Adapter



**75806 Micro Bit 4mm to 1/4" Socket Adapter** CVM steel, hardened.

Item No.	mm	Inch	lbs.
75806	28	1.125	.02

**Wiha SYS 4 Micro Bits & Compact Bit Sets**



26 Pc. Set

**75999 26pc SYS 4 Slotted, Phillips, Hex Inch & Metric Precision Interchangeable Bit Set. In Compact Fold Out Box.**

Precision handle, bit extension & 24 interchangeable bits.

**Item No. Combination Bit Set**

**75999** Set with Standard Precision Handle

**Set includes the following bits:**

↓ **Slotted:** 1.5, 2.0, 3.0, 4.0mm


**Phillips:** 000, 00, 0, 1

**Hex Metric:** .7, .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm

**Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

**100mm Bit Extension**

**lbs. .64**



26 Pc. Set

**75995 26pc SYSTEM 4 Precision Interchangeable Bit Set. In Compact Fold Out Box**

Sets includes Wiha precision handle, bit extension & 24 Wiha interchangeable bits.

**Item SYSTEM 4 Micro Bit Set**

**No.** Set with ESD Safe Precision Handle

**75995** and the following bits:

**TORX®:** T1, T2, T3, T4, T5, T6, T7, T8, T9, T10


**Pentalobe:** PL1, PL2, PL3, PL4, PL5, PL6

↓ **Slotted:** 1.5, 2.0, 2.5, 3.0mm

**Phillips:** #000, 00, 0, 1

**100mm Bit Extension**

**lbs. .54**



27 Pc. Set

**75994 27pc SYSTEM 4 Slotted/Phillips/Hex Metric/ TORX® Precision Interchangeable Bit Set. In Compact Fold Out Box.**

Set includes Wiha precision handle, bit extension and 25 Wiha interchangeable bits.

**Item SYSTEM 4**

**No. Combination Bit Set**

**75994** Set with ESD Safe Precision Handle

**Set includes the following bits:**

↓ **Slotted:** 1.5, 2.0, 3.0, 4.0mm

**Phillips:** 000, 00, 0, 1

**TORX®:**

T3, T4, T5, T6, T7, T8, T9, T10, T15

**Hex Metric:** .7, .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm

**100mm Bit Extension**

**lbs. .64**



18 Pc. Set

**75395 18pc SYS 4 Hex Inch & Metric Precision Interchangeable Bit Set. In Compact Fold Out Box.**

Wiha precision handle, bit extension and 16 Wiha interchangeable bits.

**Item No. Combination Bit Set**

**75395** Set with Standard Precision Handle


**Includes the following bits:**

**Hex Metric:** .7, .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm

**Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

**100mm Bit Extension**

**lbs. .58**



27 Pc. Set

**759 sets 27pc SYSTEM 4 Slotted/Phillips/Hex Inch/ TORX® Precision Interchangeable Bit Set. In Compact Fold Out Box.**

Sets include your choice of Wiha precision handle, bit extension & 25 Wiha interchangeable bits.

**Item Handle Options for SYSTEM 4**

**No. Combination Bit Sets**

**75991** Set with Standard Precision Handle

**75992** Set with ESD Safe Precision Handle

**Sets include the following bits:**

↓ **Slotted:** 1.5, 2.0, 3.0, 4.0mm

**Phillips:** 000, 00, 0, 1


**TORX®:** T3, T4, T5,

T6, T7, T8, T9, T10, T15

**Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

**100mm Bit Extension**

**lbs. .64**



40 Pc. Set

**75996 40pc SYSTEM 4 Interchangeable Bit Set.**

Includes Wiha precision handle, bit extension & 38 interchangeable bits.

**Item SYSTEM 4**

**No. Combination Bit Set**

**75996** Set with ESD Safe Precision Handle

**Set includes the following bits:**

↓ **Slotted:** 0.8, 1.2, 1.5,

1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm

**Phillips:** 000, 00, 0, 1

**TORX®:** T3, T4, T5,

T6, T7, T8, T9, T10, T15

**Hex Metric:** 1.3, 1.5,

2.0, 2.5, 3.0, 4.0mm

**Hex Inch:** .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

**100mm Bit Extension**

**lbs. 1.04**



## Technicians MicroBit Sets

- Micro Precision Bits on 4mm Hex Drive
- Bits of Exclusive CRM-72 Tool Steel
- Handle uses non-magnetic ball retainer
- Use bits in extension only
- Standard extension adds 4" to length
- Non-magnetic bit extension

Surface resistance of handles is 10<sup>9</sup> - 10<sup>10</sup> Ohms

Rotation cap

Light weight & compact

Handle tapered for precise control

Bits hardened for extreme durability



### 75096 16pc SYSTEM 4 Hex Inch & Metric Compact ESD Precision Interchangeable Bit Set

Item No.	Combination Bit Set
75096	Set with ESD Safe Precision Handle
	Hex Inch: 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
	Hex Metric: .9, 1.3, 1.5, 2.0, 2.5, lbs. 3.0, 4.0mm
	100mm Bit Extension



### 75097 16pc SYSTEM 4 Slotted, Phillips, Pentalobe Compact ESD Precision Interchangeable Bit Set


Item No.	Combination Bit Set
75097	Set with ESD Safe Precision Handle
	Slotted: 1.2, 1.5, 2.0, 2.5, 3.0mm
	Phillips: 000, 00, 0, 1, 2
	Pentalobe: PL1, PL2, PL3, PL4
	100mm Bit Extension



### 91109 Black Cartridge Holder


Holds 14 Micro bits 4mm. 1" OAL

Item No.	mm	mm	lbs.
91109	4.0	25.4	.01



### 75094 16pc SYSTEM 4 Slotted, Phillips, Hex Inch Compact ESD Precision Interchangeable Bit Set

Item No.	Combination Bit Set
75094	Set with ESD Safe Precision Handle
	Slotted: 1.5, 2.0, 2.5, 3.0mm
	Phillips: 00, 0, 1
	Hex Inch: .035, .050, 1/16, 5/64, lbs. 3/32, 7/64, 1/8"
	100mm Bit Extension




Item No.	Combination Bit Set
75095	Set with ESD Safe Precision Handle
	Slotted: 1.5, 2.0, 2.5, 3.0mm
	Phillips: 00, 0, 1
	Hex Metric: .9, 1.3, 1.5, 2.0, 2.5, lbs. 3.0, 4.0mm
	100mm Bit Extension

## SYSTEM 4 Interchangeable Bit Sets



Includes Dust Cover




### 75968 68pc SYSTEM 4 Micro Bit Set

Includes ESD handle, Micro bit storage handle, micro bit extension & 65 micro bits.

Item No.	Includes the following micro bits:
75968	Slotted: 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, lbs. 3.0, 3.5, 4.0mm
	Phillips: 000, 00, 0, 1, 2
	TORX: T1, T2, T3, T4, T5, T6, T7, T8, T9, T10, T15, T20
	Hex Metric: .7, .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
	Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
	Nut Drivers Metric: 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5mm
	Nut Drivers Inch: 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32"
	Pentalobe: PL1, PL2, PL3, PL4, PL5, PL6
	Magnetic 1/4" to 4mm Adapter

\* Does not include storage box



### 75971 68pc SYSTEM 4 Micro Bit Set

Includes ESD handle, Micro bit storage handle, micro bit extension & 65 micro bits.

Item No.	Set In Zipper Case
75971	Includes the following micro bits:
	Slotted: 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, lbs. 3.0, 3.5, 4.0mm
	Phillips: 000, 00, 0, 1, 2
	TORX: T1, T2, T3, T4, T5, T6, T7, T8, T9, T10, T15, T20
	Hex Metric: .7, .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
	Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
	Nut Drivers Metric: 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5mm
	Nut Drivers Inch: 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32"
	Pentalobe: PL1, PL2, PL3, PL4, PL5, PL6
	Magnetic 1/4" to 4mm Adapter







**SYSTEM 4**  
**Interchangeable Bit Sets**



**75980 68pc SYSTEM 4 Master Tech Micro Bit Set.** Includes Wiha ESD Safe Precision Handle, 1/4" to 4mm Adapter, 100mm Bit Extension & 36 Micro Bits.

**Item No. SYSTEM 4 Micro Bit Set**

**75980 Includes The Following Bits:**





- ↓  **Slotted:** 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm
  -  **Phillips:** 000, 00, 0, 1, 2
  -  **TORX®:** T1, T2, T3, T4, T5, T6, T7, T8, T9, T10
  -  **Hex Metric:** 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
  -  **Pentalobe:** PL1, PL2, PL3, PL4, PL5, PL6
-  **lbs. .38**



**75993 28pc SYSTEM 4 Premium ESD Safe Micro Bit Set.** Includes Wiha ESD Safe Precision Handle, 1/4" to 4mm Adapter, 100mm Bit Extension, ESD Safe Tweezers & 21 Micro Bits.

**Item No. SYSTEM 4 Micro Bit Set**

**75993 Micro Bits:**

- ↓  **Slotted:** 0.8, 1.5, 2.0, 2.5, 3.0, 3.5mm
  -  **Phillips:** 000, 00, 0, 1, 2
  -  **TORX®:** T1, T2, T3, T4, T5, T6, T7, T8, T9, T10
- ESD Safe Tweezers:**  
**5SA ESD, 7aSA ESD, 2ASA ESD, AASA ESD, OOSA ESD**
-  **lbs. .95**

**Micro Bit Handle Storage Sets**

Micro precision bits on 4mm hex drive

Storage handle

Bits hardened for extreme durability

Bits of exclusive CRM-72 tool steel






**75981 7pc Micro Bit Handle Storage Slotted & Phillips Bit Set**

Wiha precision storage handle & 6 Micro Bit interchangeable 4mm bits.

**Item** Set with Micro Bit Precision

**No.** Storage Handle

- 75981** ↓  **Slotted:** 1.2, 1.5, 2.0mm
-  **Phillips:** 000, 00, 0
-  **lbs. .08**





**75985 7pc Micro Bit Handle Storage TORX® Bit Set**

Wiha precision storage handle & 6 Micro Bit interchangeable 4mm bits.

**Item** Set with Micro Bit Precision




**No.** Storage Handle

- 75985**  **TORX®** T3, T4, T5, T6, T7, T8
-  **lbs. .08**



**75805 SYSTEM 4 Micro Bit Storage Handle**

Accepts all SYSTEM 4 Series bits. 108mm / 4.25" OAL

<b>Item</b>			
<b>No.</b>	mm	Inch	lbs.
<b>75805</b>	4.0	.1574	.05



**75983 7pc Micro Bit Handle Storage Hex Inch Bit Set**

Wiha precision storage handle & 6 Micro Bit interchangeable 4mm bits.

**Item** Set with Micro Bit Precision

**No.** Storage Handle

- 75983**  **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8"
-  **lbs. .08**



## The Comfortable Precision Pliers & Cutters

Electronics pliers with cutting edges are designed especially for cutting soft to medium hard wires.

Precision ground cutting edges for smooth cuts

Glare free black finish

Lay-on, riveted precision joint

Light weight design for maximum user comfort in production work

C70 tool steel HR60 hardness



## Electronic Diagonal Cutters



**56812 Precision Electronic Diagonal Cutters, Narrow Shape** Extra narrow, short head for working in particularly restricted spaces. Cutting edge - full flush. With return spring. For absolutely flush cutting of copper wires in difficult to access locations.  $\approx$  lbs. .19

Item No.	mm	Inch	Cut Capacity	Pkg.
56812	118	4.5	0.8mm/16AWG	1

## Electronic Oblique 48° Cutter



**56833 Electronic Oblique 48° Cutter** Wide pointed head. Cutting edge - full flush. With cutting edge at 48° for cutting obliquely from above or from the side. C70 special tool steel. For absolutely flush cutting of copper wires in difficult to access locations.

Item No.	mm	Inch	Cut Capacity	lbs.	Pkg.
56833	138	5.5	1.3mm/16AWG	.22	1

## Electronic Diagonal Cutters



**56818 Precision Electronic Diagonal Cutters, Wide Pointed Head** Cutting edge - full flush. With return spring. C70 special tool steel. For an absolutely flush cut of copper wire.

Item No.	mm	Inch	Cut Capacity	lbs.	Pkg.
56818	138	5.5	1.3mm/16AWG	.22	1

## Electronic Diagonal Cutters



**56813 Precision Electronic Diagonal Full Flush Cutters With Wire Trapping Spring** Extra narrow, short head for working in particularly restricted spaces. Cutting edge - full flush. With return spring. C70 special tool steel. For absolutely flush cutting of copper wires in difficult to access locations.

Item No.	mm	Inch	Cut Capacity	lbs.	Pkg.
56813	128	5.0	1.0mm/16AWG	.19	1

## Narrow Front Cutter/Long Nose Pliers



**56830 Electronic Narrow 30° Front Cutter / Long Nose Pliers** Extremely narrow, short head for working in particularly restricted spaces. Cutting edge - full flush. Edge at 30° to face end of pliers for cutting obliquely from above or from the side. C70 special tool steel. For absolutely flush cutting of copper wires in difficult to access locations.

Item No.	mm	Inch	Cut Capacity	lbs.	Pkg.
56830	118	4.5	0.6mm/16AWG	.19	1

## Electronic Diagonal Cutters



**56815 Precision Electronic Diagonal Cutters, Wide Pointed Head** Cutting edge - semi flush. With return spring. C70 special tool steel. Universal small diagonal cutter for cutting copper wires.  $\approx$  lbs. .23

Item No.	mm	Inch	Cut Capacity	Hard Wire	Pkg.
56815	138	5.5	2.0mm/16AWG	0.8	1

## Electronic Diagonal Cutters



**56825 Precision Electronic Diagonal Cutters, Wide Shape With Wire Holding Spring** Wide, Pointed head. Cutting edge - full flush. With return spring & fixture for holding ends of wires that have been cut off. For an absolutely flush cut of copper wire.

Item No.	mm	Inch	Cut Capacity	lbs.	Pkg.
56825	138	5.5	1.3mm/16AWG	.23	1

## Electronic Stripping Pliers



**56871 Electronic Stripping Pliers** Wide long head with ridged gripping surface, shears blade and firm wire stripping stations. With opening spring and locking mechanism. Wire stripping stations 0.81 / 1.0 / 1.3 / 1.6 / 2.0 / 2.59mm, AWG 20 / 18 / 16 / 14 / 12 / 10.

#56871	mm	Inch	Ø	AWG	lbs.	Pkg.
	180	7.0	0.81-2.59	20-10	.15	1

## Electronic Pointed Pliers



**56801 Electronic Short Nose Precision Pliers** Narrow, short head. Smooth jaws. Width at tip is only 1.2mm. C70 special tool steel. For holding small components as well as for holding and angling wires.

Item No.	mm	Inch	Pkg.	lbs.
56801	138	5.5	1	.23

# Professional Quality ESD Tweezers

**ESD SAFE • STATIC DISSIPATIVE • HYPO ALLERGENIC COATED • TEXTURED GRIPPING SURFACE**



### Universal Fine Point Tweezers

Item No.	Description	wt.
44501	AA SA ESD - 130mm	.09

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### Very Fine Points/Tapered To Tip

Item No.	Description	wt.
44508	4 SA ESD - 110mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### Angled 3.5 to 7mm Diameter

Item No.	Description	wt.
44515	54 SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### Long Narrow Body Low Force

Item No.	Description	wt.
44503	SS SA ESD - 135mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### Extra Fine Points/Tapered To Tip

Item No.	Description	wt.
44509	5 SA ESD - 110mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### Narrow Rounded Tip Serrated, Guide Pin

Item No.	Description	wt.
44518	22 SA ESD - 150mm	.10

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### Reduced Body To Medium Point

Item No.	Description	wt.
44504	2 SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### Curved Extra Fine Rounded Tips

Item No.	Description	wt.
44510	7a SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### Universal Blunt Tip Serrated

Item No.	Description	wt.
44520	40 SA ESD - 145mm	.11


Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### Flat Round Tip Smooth Sides

Item No.	Description	wt.
44505	2a SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### Holds 0.8 to 2mm Diameter

Item No.	Description	wt.
44511	50 SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### MicroTip 45° Hook 1x1x2mm

Item No.	Description	wt.
44521	12 SA-SMD ESD-120mm	.09

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### Fine Round Points For Assembly

Item No.	Description	wt.
44506	3 SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### Holds 1.5 to 3mm Diameter

Item No.	Description	wt.
44512	51 SA ESD - 130mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### 10pc ESD Safe Tweezers Set

Item No.	Description	wt.
44593	10pc Set Includes:	1.05

AA SA Fine Point, 2a SA Flat Round Tip, 3 SA Round Point, 3c SA Fine Round Points Shorter, 4 SA Very Fine Points, 7a SA Curved Extra Fine, PSF SA Flat-1.0mm Wide, 7abb SA Curved Extra Fine, 5bb SA Extra Fine Bent, 4b SA Very Fine Point 40°



### Fine Round Points Shorter

Item No.	Description	wt.
44507	3c SA ESD - 110mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### Holds 6.5 to 10mm Diameter

Item No.	Description	wt.
44514	53 SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.

## Wiha Professional Quality ESD Safe Tweezers



### MicroTip For Chips Angled 1.6 x 1 x 1mm

Item No.	Description	wt.
44522	13 SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### Flat Bent 35° - 2mm Diameter Grip Radius

Item No.	Description	wt.
44530	59 SA-SMD ESD-117mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### Narrow Body, Bent, Long Guide Pin, Serrated

Item No.	Description	wt.
55532	22b SA ESD - 155mm	.10

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### Long Flat to 1.0mm Wide No Serration

Item No.	Description	wt.
44523	PSF SA ESD-125mm	.09

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### ESD Safe General Purpose Fine Point

Item No.	Description	wt.
44531	1 SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### Blunt Tips - 1.0mm Wide Serrated

Item No.	Description	wt.
55533	PSF SA ESD S -125mm	.09

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### Curved Extra Fine, 3mm Long Straight Tip

Item No.	Description	wt.
44525	7abb SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### Heavy Duty Strong Tweezers Tapered To Strong Point

Item No.	Description	wt.
44532	00 SA ESD - 120mm	.09

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### Flat and Broad Tips 3mm Wide

Item No.	Description	wt.
55534	F SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### Angled Extra Fine Points Bent 30° - 3mm Long Tips

Item No.	Description	wt.
44527	5abb SA ESD - 117mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### Angled & Slightly Bent With Extra Fine Tips

Item No.	Description	wt.
44533	7 SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### MicroTip Straight & 0.5mm Slot Milled

Item No.	Description	wt.
55535	8ab SA-SMD ESD-120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### Extra Fine Points Bent 30° - 3mm Long Tips

Item No.	Description	wt.
44528	5bb SA ESD-107mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### MicroTip 30° Bend & 0.5mm Slot Milled

Item No.	Description	wt.
55531	11SA-SMD ESD-117mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



### MicroTip 30° Bent & Angled With 0.5 Slot

Item No.	Description	wt.
55536	19 SA-SMD ESD-120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



## Wiha Professional Quality ESD Safe Tweezers



### Chip Holding Curved Fine MicroTip

Item No.	Description	↕↔ wt.
55537	R10 SA SMD ESD - 117mm	.07

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommeloy. Special stainless steel, anti-magnetic and acid resistant.



### Very Fine Points 40° Tapered To Tip

Item No.	Description	↕↔ wt.
55539	4b SA ESD - 110mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommeloy. Special stainless steel, anti-magnetic and acid resistant.



### Wafer Tweezer

Item No.	Description	↕↔ wt.
55538	72a SA ESD -	.07

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommeloy. Special stainless steel, anti-magnetic and acid resistant.



### 9mm Wide With Back Stop Pins - Wafer

Item No.	Description	↕↔ wt.
55546	89 SA ESD - 125mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommeloy. Special stainless steel, anti-magnetic and acid resistant.



### Angled 12mm Wide Flat, Back Stop - Wafer

Item No.	Description	↕↔ wt.
55547	91 SA ESD - 125mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommeloy. Special stainless steel, anti-magnetic and acid resistant.

## Inspection Mirrors All Stainless Detachable & Boilable

### Inspection Mirrors - Detachable All Stainless

For Visual Checks and Fault Finding at Inaccessible Locations

Natural Finish, Stainless Steel

Light weight, tubular

Stainless Steel

Mirrors-Clean Room Quality



### Inspection Mirror - Stainless 10mm

Item No.	Description	↕↔ wt.
40410	#0 IM - 216mm	.09



### Inspection Mirror - Stainless 26mm

Item No.	Description	↕↔ wt.
40426	#6 IM - 229mm	.10



### Inspection Mirror - Stainless 14mm

Item No.	Description	↕↔ wt.
40414	#0 IM - 216mm	.09



### Inspection Mirror - Stainless 30mm

Item No.	Description	↕↔ wt.
40430	#8 IM - 232mm	.10



### Inspection Mirror - Stainless 20mm

Item No.	Description	↕↔ wt.
40420	#3 IM - 224mm	.09



### Inspection Mirror - Stainless 22mm Short Stem

Item No.	Description	↕↔ wt.
40422	#4 IM - 224mm	.10



### Inspection Mirror - Stainless 24mm Short Stem

Item No.	Description	↕↔ wt.
40424	#5 IM - 225mm	.10



### 7pc Inspection Mirror Set

Item No.	Description	↕↔ wt.
40490	7pc Set Includes: 10mm, 14mm, 20mm, 22mm, 24mm, 26mm, 30mm	.67




### Disposable Inspection Mirrors

Item No.	Description	↕↔ wt.
40425	5 Pack - Plastic	.10

Set includes: White disposable inspection mirror #5 Inspection Mirrors - 24mm x 146mm

Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page
26000	4	26145	9	26449	10	26631	11	26911	13	26975	15
26001	4	26190	4	26455	10	26701	6	26912	13	26976	15
26008	4	26192	5	26457	10	26702	6	26913	14	26977	15
26010	4	26193	9	26459	10	26703	6	26914	14	26978	15
26012	4	26194	5	26461	10	26704	6	26916	14	26979	15
26015	4	26195	9	26463	10	26705	6	26917	14	26980	15
26018	4	26196	9	26465	10	26706	6	26918	14	26981	15
26020	4	26197	4	26467	10	26707	6	26919	14	26982	15
26022	4	26198	9	26490	6	26708	6	26920	14	26983	15
26023	4	26199	4	26491	6	26709	6	26921	14	26985	15
26025	4	26205	5	26493	10	26710	6	26922	13	28000	13
26027	4	26210	5	26499	6	26715	6	26923	14	28002	15
26028	4	26307	5	26510	7	26720	6	26924	14	28003	15
26030	4	26309	5	26515	7	26721	12	26925	14	28004	15
26032	4	26313	5	26520	7	26723	12	26926	14	28005	15
26033	4	26315	5	26523	7	26725	12	26927	14	28006	15
26034	4	26316	5	26525	7	26727	12	26928	14	28007	15
26035	4	26320	5	26527	7	26729	12	26929	14	28008	15
26040	4	26323	5	26530	7	26731	12	26930	15	28012	15
26041	4	26325	5	26531	7	26732	10	26932	14	28021	14
26042	4	26327	5	26532	7	26733	10	26934	14	28023	14
26050	9	26330	5	26535	7	26735	10	26935	14	28024	14
26051	9	26331	5	26536	7	26736	10	26936	14	28026	14
26052	9	26333	5	26539	7	26737	10	26937	14	28027	14
26053	9	26336	5	26540	7	26739	10	26938	14	28028	14
26055	9	26340	5	26545	7	26741	10	26939	14	28029	14
26060	9	26341	10	26547	7	26743	10	26940	14	28033	14
26061	9	26343	10	26550	7	26745	10	26941	14	28034	14
26065	9	26345	10	26555	7	26747	10	26942	14	28035	14
26066	9	26347	10	26556	7	26749	10	26943	14	28036	14
26068	9	26349	10	26560	7	26751	10	26944	14	28037	14
26070	9	26351	10	26563	7	26761	7	26945	14	28552	8
26072	9	26353	10	26570	7	26762	7	26946	14	28620	8
26073	9	26363	10	26571	11	26763	7	26947	14	28622	8
26074	9	26367	10	26572	11	26764	7	26948	14	28624	8
26076	9	26369	10	26573	11	26765	7	26949	14	28626	8
26079	9	26371	10	26574	11	26766	7	26950	14	28627	8
26080	9	26390	5	26575	11	26771	11	26951	13	28629	8
26090	4	26391	5	26576	11	26772	11	26952	13	28632	8
26092	5	26392	10	26577	11	26773	11	26953	13	28633	8
26093	9	26393	10	26578	11	26774	11	26954	13	28637	8
26099	4	26399	5	26579	11	26775	11	26955	13	28644	8
26100	4	26413	6	26581	11	26776	11	26956	13	32000	12
26101	4	26415	6	26582	11	26790	6	26957	13	32001	12
26102	4	26416	6	26583	11	26791	6	26958	15	32002	12
26105	4	26419	6	26584	11	26792	6	26959	15	32003	12
26107	4	26420	6	26585	11	26793	10	26960	15	32004	12
26108	4	26423	6	26586	11	26794	7	26961	15	32085	12
26109	4	26425	6	26587	11	26795	11	26962	14	32088	12
26110	4	26427	6	26588	11	26796	10	26963	14	32106	12
26113	4	26430	6	26589	11	26798	12	26964	14	32107	12
26114	4	26431	6	26590	7	26799	6	26965	14	32108	12
26115	4	26436	6	26591	7	26810	4	26966	14	40010	8
26130	9	26439	6	26592	7	26815	11	26968	14	40410	25
26132	9	26440	6	26593	11	26900	13	26969	14	40414	25
26135	9	26441	10	26596	11	26903	13	26971	13	40420	25
26136	9	26443	10	26598	7	26904	13	26972	13	40422	25
26140	9	26445	10	26599	7	26905	13	26973	13	40424	25
26142	9	26447	10	26601	5	26906	15	26974	13	40425	25

Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page
40426	25	75093	20	75628	16	75735	17	75994	19		
40430	25	75094	20	75629	16	75742	17	75995	19		
40490	25	75095	20	75630	16	75743	18	75996	19		
44501	23	75096	20	75631	16	75744	18	75999	19		
44503	23	75097	20	75632	16	75745	18	91109	20		
44504	23	75105	17	75633	16	75746	18	91118	11		
44505	23	75110	17	75634	16	75747	18	92189	8		
44506	23	75115	17	75635	16	75748	18	92190	8		
44507	23	75120	17	75636	16	75800	17	92191	8		
44508	23	75125	17	75637	16	75801	17	96800	12		
44509	23	75307	17	75638	16	75802	18				
44510	23	75309	17	75639	16	75803	18				
44511	23	75313	17	75641	16	75805	21				
44512	23	75315	17	75644	16	75806	18				
44514	23	75320	17	75645	16	75810	18				
44515	23	75322	17	75646	16	75811	18				
44518	23	75325	17	75647	16	75812	18				
44520	23	75330	17	75648	16	75813	18				
44521	23	75332	17	75649	16	75814	18				
44522	24	75340	17	75650	16	75815	18				
44523	24	75342	17	75651	16	75816	18				
44525	24	75350	17	75652	16	75817	18				
44527	24	75352	17	75653	16	75820	18				
44528	24	75354	17	75654	16	75821	18				
44530	24	75356	17	75655	16	75822	18				
44531	24	75358	17	75657	16	75823	18				
44532	24	75360	17	75658	16	75824	18				
44533	24	75362	17	75659	16	75825	18				
44593	23	75364	17	75660	16	75826	18				
55531	24	75366	17	75661	16	75827	18				
55532	24	75368	17	75662	16	75900	17				
55533	24	75370	17	75663	16	75901	17				
55534	24	75372	17	75664	16	75902	17				
55535	24	75395	19	75665	16	75965	20				
55536	24	75602	16	75666	16	75968	20				
55537	25	75603	16	75667	16	75971	20				
55538	25	75604	16	75668	16	75973	11				
55539	25	75605	16	75669	16	75980	21				
55546	25	75606	16	75670	16	75981	21				
55547	25	75607	16	75671	16	75982	18				
56801	22	75608	16	75672	16	75983	21				
56812	22	75609	16	75673	16	75993	21				
56813	22	75610	16	75674	16	75984	18				
56815	22	75611	16	75675	16	75985	21				
56818	22	75612	16	75676	16	75986	18				
56825	22	75613	16	75681	16	75987	18				
56830	22	75614	16	75683	16	75988	18				
56833	22	75615	16	75701	17	75991	19				
56871	22	75616	16	75702	17	75992	19				
62994	12	75617	16	75703	17						
75008	17	75618	16	75704	17						
75012	17	75619	16	75705	17						
75015	17	75620	16	75706	17						
75018	17	75621	16	75707	17						
75020	17	75622	16	75708	17						
75025	17	75623	16	75709	17						
75030	17	75624	16	75710	17						
75035	17	75626	16	75715	17						
75040	17	75627	16	75720	17						

 **Prop65 WARNING:** This product could expose you to chemicals including Vinyl Chloride, Ethylene Glycol, Ni or CrVI, which are known to the state of California to cause cancer or reproductive harm. For more information go to [www.P65warnings.ca.gov/](http://www.P65warnings.ca.gov/)



# PROFESSIONAL TECH TOOLS



(800) 494-6104  
 fax: (800) 494-7456  
 cservice@wihatools.com  
 www.wihatools.com

**Wiha Quality Tools**  
 1348 Dundas Circle  
 Monticello, MN 55362  
 tel: 763.295.6591  
 fax: 763.295.6598

**Wiha Tools Canada Ltd.**  
 www.wihatools.ca  
 Brampton, ONT L6T 4X4  
 tel: 866.494.0096 or 763.295.6591  
 fax: 763.295.6598

Like Us On **facebook**

To:

Catalog Item No. 99006 .wo  
 version - 9/1/19

Subject to change without notice

©2019 Willi Hahn Corporation

®Torx is a registered trademark of  
 Acument Intellectual Properties LLC.



99934.wo - Hex Tools Catalog



99914.wo - TORX Catalog



99001.wo - TorqueControl Catalog



99951.wo - Bits Catalog




99919.wo - Insulated Catalog



99002.wo - Screwdrivers Catalog




99004.wo - Shop Tools Catalog



99977.wo - Pliers/Crimpers Catalog



99945.wo - ESD Catalog



99007.wo - Merchandise Catalog

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Wiha:

[26325](#) [26330](#) [75742](#) [76131](#) [76113](#) [76129](#) [75705](#) [26982](#) [75706](#) [75715](#) [76111](#) [75720](#) [76107](#) [76121](#) [76123](#)  
[75708](#) [76117](#) [28552](#) [75709](#) [75710](#) [75739](#) [75707](#) [26978](#) [75704](#) [26980](#) [76106](#) [76109](#) [75703](#) [76119](#) [26935](#)  
[26926](#) [26913](#) [26916](#) [26927](#) [26932](#) [26914](#) [26924](#) [26937](#) [26929](#) [26917](#) [26918](#) [26971](#) [28633](#) [56825](#) [28626](#)  
[28632](#) [26938](#) [26949](#) [56801](#) [56813](#) [56818](#) [26956](#) [26958](#) [26976](#) [28027](#) [26957](#) [26963](#) [26968](#) [26911](#) [26940](#)  
[26954](#) [26941](#) [26945](#) [26947](#) [28023](#) [28029](#) [26959](#) [40425](#) [56830](#) [75395](#) [26922](#) [28644](#) [26943](#) [26708](#) [28637](#)  
[56815](#) [26967](#) [40422](#) [28622](#) [56871](#) [26965](#) [56812](#) [56833](#) [75999](#) [26055](#) [26960](#) [75800](#) [28629](#) [28627](#) [75902](#)  
[40424](#) [75360](#) [75368](#) [75735](#) [75327](#) [75340](#) [28620](#) [75320](#) [75358](#) [75309](#)