

Between Series Adaptor 31_MBX-SMA-50-1/111_N

Description

Adaptor jack/jack
MBX jack (female) / SMA jack (female)

Interface standards
Series MBX - HUBER+SUHNER MBX
Series SMA - IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz
Frequency range	DC to 6 GHz
Return loss	≥ 28 dB

Mechanical Data

Number of matings	500
Weight	0.002751 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - MBX jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze	SUCOPRO Plating
Body	Bronze	SUCOPRO Plating
Insulator	PFA / PTFE / LCP	

Interface - SMA jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze	SUCOPRO Plating
Body	Bronze	SUCOPRO Plating
Insulator	PFA / PTFE / LCP	

Related Documents

Outline drawing	DOU-00162045
-----------------	--------------

Ordering Information

Single package	31_MBX-SMA-50-1/111_NE
----------------	------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[31_MBX-SMA-50-1/111_NE](#)