

## **A43.10.100 0 °C ... 120 °C L1=60 x 9 mm alu CL.2**

### **Bimetallic thermometer, for heating technology A43**

Item number: 14138715  
Quantity: 1 pcs.  
Order code: A4310100G-C1F-060ECKBB-1ZZZZZ1-KSK2ZZZ  
Overview: A43.10.100 0 °C ... 120 °C L1=60 x 9 mm alu CL.2  
Case material: aluminium  
pointer: plastic, black  
Window: acrylic, (SAN)  
Thermowell: detachable, friction retained; Brass  
Process connection [E, d6]: G1/2B  
\*WIKA\*  
Dial color, 1-colored

Details: Bimetallic thermometer, for heating technology A43  
Model: A43  
Design: standard, aluminium case  
Nominal size [NG, d1]: 100 mm  
Case material: aluminium  
Unit: °C  
Scale range: 0 °C ... 120 °C  
Insertion length [L1]: 60 mm  
Stem diameter [d5]: 9 mm  
Stem material: aluminum  
Thermowell: detachable, friction retained;  
Thermowell material: Brass  
Process connection [E, d6]: G1/2B  
Manufacturer logo: \*WIKA\*  
Dial printed (Number of colors): Dial color, 1-colored  
pointer model: plastic, black  
Window: acrylic, (SAN)  
Accuracy class: class 2 per EN 13190