

# Type-A USB 3.2 Gen 2 interface enables fast data transfers up to 10 Gbps

---

 [silicon-power.com/web/product-M80](https://silicon-power.com/web/product-M80)



Marvel Xtreme M80

## **Go to the extreme with top-tier speeds**

---

With extreme read speeds of up to 600MB/s and write speeds of up to 500MB/s, the Marvel Xtreme M80 is our fastest USB flash drive yet. Make the most of your time and copy huge files to the drive in seconds!

\*Transfer a 5GB file from a PC to the drive in just 12 seconds!

## **Technical specifications**

---



- capacity
- 250GB, 500GB, 1TB
- size
- 68.5mm x 17.8mm x 8.2mm
- weight
- 8.5g
- material
- aluminum + plastic
- colour
- Gray
- interface
- Type-A USB 3.2 Gen 2 (compatible with USB 3.1, USB 3.0, USB 2.0)
- Performance read (max.)
- 250GB – 590MB/s
- 500GB – 600MB/s
- 1TB – 600MB/s
- Performance write (max.)
- 250GB – 260MB/s
- 500GB – 500MB/s
- 1TB – 500MB/s
- Supported OS

- Windows 10/8.1/8/7/XP, Mac OS 10.3.X and above, Linux 2.6.X and above  
\*Transfer speeds fluctuated or dropped when I copied/moved files to USB drive on a Windows 10 system. Please click [here](#) for more info
- operating temperatur
- 0°C - 70°C
- certification
- CE, FCC, BSMI, UKCA, Green Dot, WEEE, RoHS
- warranty
- 5 year limited warranty

## features

---

- Type-A USB 3.2 Gen 2 interface enables fast data transfers up to 10 Gbps
- Massive instant storage expansion with capacities up to 1TB
- Blazing fast read speeds of up to 600MB/s and write speeds of up to 500MB/s
- Built-in LED light conveniently indicates data activity
- Carry-friendly design: Robust aluminum metal housing with removable protective cap
- Easier and faster alternative to cloud storage as a bridge between phones and computers
- True plug & play technology eliminates the need for an external power supply
- Recuva File Recovery allows recovering deleted files such as digital photos, documents, music and videos
- Free downloadable SP Widget software for backup and restore, AES 256-bit encryption and cloud storage available

1TB

SP001TBUF3M80V1G