

Standard Nylon Cable Ties




04-241750 Features

- Low Insertion and Pull Through Force
- One Piece Design for High Tensile Strength
- Advanced Pawl and Teeth Design
- Angled Tail for Quicker Initial Insertion Alignment
- Tail Finger Grips for Easier Handling and Tightening
- Rounded Safety Edges Eliminate Insulation Damage



WT-01



Color Code Chart

0	UV Black	11	Fluorescent Green
1	Brown	12	Fluorescent Pink
2	Red	13	Fluorescent Yellow
3	Orange	14	Fluorescent Orange
4	Yellow	15	Fluorescent Blue
5	Green	30	Heat Stabilized Black
6	Blue		
7	Purple		
8	Gray		
9	Natural		

18 lb. Miniature (4" ties available in all colors, **ALL OTHERS** available in colors 0, 9, and 30 **ONLY**, Note 5, Note 6)

NTE Type No.	Length	Width	Thickness	Max. Bundle Dia. (Note 3)	Mil Spec (Note 4)	Qty. per Bag	Diag No.
04-0418xx	4.12 / 104.77	.095 / 2.413	.042 / 1.066	.875 / 22.225	MS3367-4	100	WT-01
04-0418xxM	4.12 / 104.77	.095 / 2.413	.042 / 1.066	.875 / 22.225	MS3367-4	1000	WT-01
04-0618xx	6.18 / 157.14	.095 / 2.413	.042 / 1.066	1.500 / 38.10	MS3367-4	100	WT-01
04-0618xxM	6.18 / 157.14	.095 / 2.413	.042 / 1.066	1.500 / 38.10	MS3367-4	1000	WT-01
04-0818xx	8.18 / 207.94	.095 / 2.413	.042 / 1.066	2.187 / 55.562	MS3367-4	100	WT-01
04-0818xxM	8.18 / 207.94	.095 / 2.413	.042 / 1.066	2.187 / 55.562	MS3367-4	1000	WT-01

40 lb. Intermediate (Available in colors 0, 2, 4, 5, 6, and 9 **ONLY**, Note 5)

NTE Type No.	Length	Width	Thickness	Max. Bundle Dia. (Note 3)	Mil Spec (Note 4)	Qty. per Bag	Diag No.
04-0540xx	5.84 / 148.33	.140 / 3.556	.049 / 1.244	1.437 / 36.512	MS3367-5	100	WT-01
04-0540xxM	5.84 / 148.33	.140 / 3.556	.049 / 1.244	1.437 / 36.512	MS3367-5	1000	WT-01
04-0840xx	8.87 / 225.40	.140 / 3.556	.049 / 1.244	2.37 / 60.32	N/A	100	WT-01
04-0840xxM	8.87 / 225.40	.140 / 3.556	.049 / 1.244	2.37 / 60.32	N/A	1000	WT-01

50 lb. Standard (17" ties available in colors 0 and 9 **ONLY**, All other lengths available in all colors, Note 5, Note 6)

NTE Type No.	Length	Width	Thickness	Max. Bundle Dia. (Note 3)	Mil Spec (Note 4)	Qty. per Bag	Diag No.
04-0750xx	7.56 / 192.07	.180 / 4.572	.052 / 1.320	1.875 / 47.625	MS3367-1	100	WT-01
04-0750xxM	7.56 / 192.07	.180 / 4.572	.052 / 1.320	1.875 / 47.625	MS3367-1	1000	WT-01
04-1150xx	11.25 / 285.75	.180 / 4.572	.052 / 1.320	3.062 / 77.787	MS3367-7	100	WT-01
04-1150xxD	11.25 / 285.75	.180 / 4.572	.052 / 1.320	3.062 / 77.787	MS3367-7	500	WT-01
04-1150xxM	11.25 / 285.75	.180 / 4.572	.052 / 1.320	3.062 / 77.787	MS3367-7	1000	WT-01
04-1450xx	14.56 / 369.87	.180 / 4.572	.052 / 1.320	4.125 / 104.775	MS3367-2	100	WT-01
04-1450xxD	14.56 / 369.87	.180 / 4.572	.052 / 1.320	4.125 / 104.775	MS3367-2	500	WT-01
04-1750xx	17.09 / 434.16	.187 / 4.749	.060 / 1.524	4.750 / 120.65	N/A	100	WT-01

120 lb. Heavy Duty (Available in colors 0, 9, and 30 **ONLY**, Note 6)

NTE Type No.	Length	Width	Thickness	Max. Bundle Dia. (Note 3)	Mil Spec (Note 4)	Qty. per Bag	Diag No.
04-08120xx	8.70 / 220.98	.300 / 7.620	.076 / 1.930	2.060 / 52.38	N/A	100	WT-01
04-14120xxL	15.09 / 383.36	.300 / 7.620	.076 / 1.930	4.060 / 103.18	MS3367-3	50	WT-01
04-14120xx	15.09 / 383.36	.300 / 7.620	.076 / 1.930	4.060 / 103.18	MS3367-3	100	WT-01

175 lb. Extra Heavy Duty (Available in colors 0 and 9 **ONLY**)

NTE Type No.	Length	Width	Thickness	Max. Bundle Dia. (Note 3)	Mil Spec (Note 4)	Qty. per Bag	Diag No.
04-24175x	25.25 / 641.35	.340 / 8.636	.090 / 2.286	7.180 / 182.56	MS3367-8, 9 & 10	50	WT-01
04-481750L	48.56 / 1233.47	.340 / 8.636	.090 / 2.286	14.500 / 368.3	MS3367-16-0	50	WT-01

Note 1. Replace "x" or "xx" in device number with corresponding color code from the "Color Code Chart".

Note 2. Dimensions are listed as "inch / millimeter".

Note 3. "Max. Bundle Dia." is defined as the maximum bundle diameter achieved after insertion for 3 "clicks" due to having a 3 tooth pawl.

Note 4. Mil Spec not available for fluorescent and heat stabilized types.

Note 5. Colored and Fluorescent types available in 100 per bag **ONLY**.

Note 6. Working temperature, heat stabilized types: -40° to +257°F (-40° to +125°C)