


ROHS - COMPLIANT

LTR	REV.	DESCRIPTION	DATE



NOTES:

1. CABLE:

UL-2725 30AWG(7/0.102 B.C)*2C INS:SR-PVC ID:0.8±0.05
 +30AWG(7/0.102 B.C)*2C INS:SR-PVC ID:0.6±0.05+AL-FOIL/MYLAR
 +DRAIN WIRE 32AWG(1/0.203 B.C)+BRAID(8/2/0.1 T.C)
 PVC JACKET OD:4.0±0.15mm COLOR: BEIGE(NK-A03) REV 2.0

2. CONNECTER:

P1:USB A TYPE MALE GOLD FLASH CONTACT,
 NICKEL PLATED SHELL
 P2:USB B TYPE MALE GOLD FLASH CONTACT,
 NICKEL PLATED SHELL
 3.HOOD: MOLDED TYPE,PVC 45P, COLOR:BEIGE(NK-A03)
 4.ELECTRICLE TEST:
 <1>100% OPEN SHORT & MIS WIRE TEST.
 <2>CONTACT RESISTANCE 3 Ohms MAX.
 <3>INSULATION RESISTANCE 10M Ohms MIN.
 5.PACKING:<1>EACH PC / POLYBAG + EAN CODE LABEL & ROHS LABEL
 <2>EACH CARTON / ROHS LABEL(L*W=35*22mm)

P1

P2

- | | | | |
|---------|-------|---|--------|
| RED 1 | _____ | 1 | VCC |
| WHITE 2 | _____ | 2 | -DATA |
| GREEN 3 | _____ | 3 | +DATA |
| BLACK 4 | _____ | 4 | GROUND |
| SHELL | _____ | | SHELL |

2DIRECT GMBH

Title
 USB A/M - B/M CABLE REV 2.0

Tolerance	Inch	M/M
X	.015	.30
XX	.010	.10
XXX	.005	.05

Drawn **FANNIE 04/14/06** Customer P/NI

Check	App'd	Customer
Engr	Scale NONE	Units m/m
	Dwg No. 170-2688	Third Angle Projection
	REV: A	Sheet 1/2

DWG	P/N	L+T	EAN CODE
170-2688-3	CU0009	5000±50mm	4260113560327
170-2688-2	CU0008	3000±30mm	4260113560310
170-2688-1	CU0007	2000±30mm	4260113560303