


# connecting cable NEBV-S1G25-K-5-N-LE25-S6

Part number: 575418

FESTO



## Data sheet

| Feature                                 | Value                          |
|---|--------------------------------|
| Mounting type                           | 4-40UNC                        |
| Assembly position                       | Any                            |
| Product weight                          | 777 g                          |
| Electrical connection                   | Plug socket<br>Sub-D<br>25-pin |
| Operating voltage range DC              | <= 30 V                        |
| Acceptable current load at 40°C         | 2.6 A                          |
| Cable length                            | 5 m                            |
| Cable attribute                         | For static applications        |
| Min. cable bending radius               | 122 mm                         |
| Cable diameter                          | 10.2 mm                        |
| Cable diameter tolerance                | ± 0,25 mm                      |
| Cable structure                         | 25x0,34                        |
| Protection class                        | IP40                           |
| Ambient temperature                     | -5 ... 80 °C                   |
| Materials note                          | Conforms to RoHS               |
| Degree of contamination                 | 2                              |
| Corrosion resistance classification CRC | 0 - No corrosion stress        |
| Material cable sheath                   | PVC                            |
| Material housing                        | Reinforced PC                  |
| Material electrical contact             | Bronze<br>Gold plated          |