

2020







PROFESSIONAL SCREWDRIVERS & NUT DRIVERS




COMPLETE SCREWDRIVER AND NUT DRIVER PROGRAM





Wiha SoftFinish® CushionGrip Screwdrivers

	Description	Page
	SoftFinish® Slotted/Phillips Drivers	4-7
	Stubby Slotted/Phillips Drivers	7
	SoftFinish® Square Drivers	7
	SoftFinish® Pozidriv® Drivers	8
	SoftFinish® Spanner Drivers	8
	Torx®/TR Torx® Screwdrivers	9-10
	SoftFinish® MagicSpring Drivers	9
	SoftFinish® MagicRing Drivers	12-13
	Measuring Scale Screwdrivers	8


Wiha 3K Series Screwdrivers

	Description	Page
	3K Series Slotted/Phillips	14
	3K Series Torx® Drivers	14
	3K Series Pozidriv® Drivers	14
	3K Series Square Drivers	14
	3K Series Hex Inch & Metric	15


Wiha Drive-Loc VI Tools

	Description	Page
	Drive-Loc VI Handles	16
	Drive-Loc VI Blades	16-17

Wiha Drive-Loc VI Sets

	Description	Page
	Drive-Loc VI Blade Sets	17-18


Wiha MicroFinish Non-Slip Grip Drivers

	Description	Page
	MicroFinish Slotted Drivers	18-19
	MicroFinish Phillips Drivers	18-19
	MicroFinish Torx® Drivers	19
	MicroFinish Bit Holder	19



Wiha Powerhandle Screwdrivers

	Description	Page
	Powerhandle Torx® Drivers	15





Wiha Proturm Screwdrivers

	Description	Page
	Proturm Torx® Drivers	15

Wiha Offset Screwdrivers

	Description	Page
	Slotted & Phillips Offset Drivers	15
	Torx® Offset Screwdrivers	15


Wiha Power Blades & Sets

	Description	Page
	CentroFix Blade Holder	20
	90mm Power Blades	20-21
	Power Blade Sets	20-21
	Power Blade Nut Drivers 100mm Inch/Metric & Sets	36-37


Wiha Precision Screwdrivers

	Description	Page	
	Precision Slotted Drivers	22-23	
	Precision Phillips Drivers	22-23	
	Precision Pozidriv® Drivers	23	
	Precision Hex Drivers	23	
	Precision Ball End Drivers	24	
	Precision Torx® Drivers	24	
	Precision Pentalobe Drivers	25	
		Precision Chip Lifters	22
		Precision Pocket Clip & Rack	22
		Precision Screwdriver Sets	25


Wiha Magnetizer/Demagnetizer

	Description	Page
	Magnetizer/Demagnetizer	25



Wiha Precision PicoFinish Drivers

	Description	Page
	PicoFinish Screwdrivers	26-28
	Slotted, Phillips, Torx, TorxPlus, Hex, MagicSpring, Ball End Hex, Chip Lifter	









Wiha ESD Safe Precision Handles/Blades

	Description	Page
	SYSTEM 4 Handles/Blades	29-30
	SYSTEM 4 Sets	31

Wiha ESD Safe Precision Handle & Blades

	Description	Page
	SYSTEM 4 Drive-Loc IV Handle & Blades	30-31
	SYSTEM 4 Drive-Loc Set	31

Wiha Nut Drivers

	Description	Page
	SoftFinish® Nut Drivers	32-34
	Hollow Shaft Nut Drivers	34
	T-handle Nut Drivers	35
	Drive-Loc VI Nut Drivers	36
	Precision Nut Drivers	37
	PicoFinish® Nut Drivers	28
	SYS 4 Nut Driver Blades/Sets	31
	Power Blade Nut Drivers	37

Wiha Insulated Screwdrivers



99919 - Insulated Catalog

- Insulated Slotted
- Insulated Phillips
- Insulated Terminal Block Xeno
- Insulated Square Drivers
- Insulated Hex Metric Drivers
- Insulated Torx® Drivers
- Insulated Nut Drivers
- Insulated Torque Drivers
- Insulated *SlimLine* Drivers

Wiha ESD Safe Screwdrivers

ESD Safe SoftFinish® Drivers
Slotted/Phillips/Torx®

ESD Safe Precision Drivers
Slotted/Phillips/Torx®/
TorxPlus®/Hex/Nut Drivers/
Chip Lifter

ESD Safe Ceramic Drivers

ESD Safe SYSTEM 4
Handles/Blades/Sets

ESD Safe Drive-Loc VI
Handles/Blades/Sets



99945 - ESD Catalog

Wiha SoftFinish® Handle - Ergonomic Cushion Grip

The Wiha SoftFinish® Handle: Featuring advanced technology dual material molding. A remarkable improvement in handle design, comfort and performance. The SoftFinish® ergonomic shape allows maximum torque and user comfort.

Handle is molded directly onto the blade for a permanent bond. Large optimized handle diameter allows higher torque with less user hand fatigue

All blades are made of Wiha's exclusive formula chrome-vanadium-molybdenum tool steel, super hardened & hard chrome finish for unmatched durability

Wiha tips are precision machined to exact tolerances for a perfect fit every time



Wiha exclusive "SoftFinish® Zone" features solid molded core with soft outer cushion grip. Requires less force, yet achieves 40% more torque than conventional handles

Wiha SoftFinish® Extra Heavy Duty



530 Slotted Screwdriver, With Wiha-SoftFinish® Handle & Solid Metal Cap

Hex blade extending through handle manufactured from high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component. Hex bolster for additional torque.

Item No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
53010*	3.5	.139	75	3.0	0.6	.024	4.0	5/32	186	7.3	30	1.18	.16	10
53015*	4.5	.177	90	3.5	0.8	.031	4.0	5/32	201	7.9	30	1.18	.17	10
53020	5.5	.196	100	3.9	1.0	.039	5.0	13/64	213	8.4	36	1.42	.23	10
53025	6.5	.255	125	5.0	1.2	.047	6.0	1/4	238	9.4	36	1.42	.33	10
53027	8.0	.315	150	5.9	1.2	.047	8.0	5/16	268	10.6	41	1.61	.56	10
53035	10.0	.393	175	7.0	1.6	.063	8.0	5/16	293	11.6	41	1.61	.58	10
53040	12.0	.472	200	8.0	2.0	.079	10.0	25/64	318	12.5	41	1.61	.76	10

*No Hex Bolster



531 Phillips Screwdriver, With Wiha-SoftFinish® Handle & Solid Metal Cap

Hex blade extending through handle manufactured from high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component. Hex bolster for additional torque.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
53110	1	80	3.1	5.0	13/64	186	7.3	30	1.18	.20	10
53115	2	100	3.9	6.0	1/4	213	8.4	36	1.42	.32	10
53120	3	150	5.9	8.0	5/16	268	10.6	41	1.61	.56	10



53090 5pc Slotted & Phillips Set - Extra Heavy Duty

Item No.	Slotted:	lbs.
53090	5.5, 6.5, 8.0mm	1.85



53075 5pc Slotted & Phillips Set - Extra Heavy Duty


Item No.	Slotted:	lbs.
53075	4.5, 5.5, 6.5mm	1.48



53096 6pc Slotted & Phillips Set - Extra Heavy Duty

Item No.	Slotted:	lbs.
53096	3.5, 4.5, 5.5, 6.5mm	1.69

SoftFinish® Extra Heavy Duty



53097 7pc Slotted & Phillips Set - Extra Heavy Duty

Item	Slotted:	⌘
No.	5.5, 6.5, 8.0, 10.0mm	lbs.
53097	Phillips: #1, 2, 3	3.15



53099 10pc Slotted & Phillips Set - Extra Heavy Duty

Item	Slotted: 3.5, 4.5, 5.5,	⌘
No.	6.5, 8.0, 10.0, 12.0mm	lbs.
53099	Phillips: #1, 2, 3	4.20

SoftFinish® Slotted & Phillips



30276 7pc Slotted & Phillips Set CVM

steel, hardened, hard chromed. Wiha-Chromtop tips. Handle, multi-component, cushion grip.

Item No.	Tip Size	Blade	Tip Style	⌘	lbs.
30816	1/4"	4" Hex	Keystone	⌘	1.87
30825	5/16"	6" Hex	Keystone	⌘	
30218	3/16"	3" Round	Cabinet	⌘	
30219	3/16"	6" Round	Cabinet	⌘	
30222	1/4"	4" Round	Cabinet	⌘	
31110	#1	3" Round	Phillips	⌘	
31115	#2	4" Round	Phillips	⌘	

Wiha SoftFinish® Heavy Duty Screwdriver



308 Slotted Screwdriver, Wiha-SoftFinish® Cushion Grip Handle

Hex blade high alloy CVM steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Hex bolster for additional torque (No Bolster 30813 & 30814)

Item	⌘	⌘	⌘	⌘	⌘	⌘	⌘	⌘	⌘	⌘	⌘	⌘	⌘	⌘	⌘	⌘	⌘	⌘
No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.		
30813	3.5	.137	75	2.9	0.6	.023	186	7.3	4.0	5/32	30	1.18	.16	10				
30814	4.5	.177	90	3.5	0.8	.032	201	7.9	4.0	5/32	30	1.18	.17	10				
30815	5.5	.216	100	3.9	1.0	.039	213	8.4	5.0	13/64	36	1.42	.19	10				
30816	6.5	.216	100	3.9	1.2	.047	213	8.4	6.0	1/4	36	1.42	.22	10				
30817	6.5	.255	125	5.0	1.2	.047	238	9.4	6.0	1/4	36	1.42	.23	10				
30820	7.0	.275	125	5.0	1.1	.043	238	9.4	6.0	1/4	36	1.42	.23	10				
30825	8.0	.315	150	5.9	1.2	.047	271	10.7	8.0	5/16	41	1.61	.37	10				
30830	10.0	.393	175	7.0	1.6	.063	296	11.7	8.0	5/16	41	1.61	.40	10				
30835	12.0	.472	200	8.0	2.0	.079	321	12.6	10.0	25/64	41	1.61	.58	10				



312 Phillips Screwdriver, Wiha-SoftFinish® Cushion Grip Handle

Hex blade high alloy CVM steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Hex bolster for additional torque.

Item	⌘	⌘	⌘	⌘	⌘	⌘	⌘	⌘	⌘	⌘	⌘	⌘	⌘	⌘	⌘	⌘
No.	Size	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.					
31201	1	80	3.1	5.0	3/16	186	7.3	30	1.18	.13	10					
31202	2	100	3.9	6.0	7/32	213	8.4	36	1.42	.21	10					
31203	3	150	5.9	8.0	5/16	271	10.7	41	1.61	.37	10					



30892 5pc Slotted & Phillips Set

Item	Slotted:	⌘
No.	5.5, 7.0, 8.0mm	lbs.
30892	Phillips: #1, 2	1.33



30898 8pc Slotted & Phillips Set

Item	Slotted: 5.5, 6.5,	⌘
No.	7.0, 8.0, 10.0mm	lbs.
30898	Phillips: #1, 2, 3	2.52



30896 6pc Slotted & Phillips Set

Item	Slotted: 3.5, 4.5,	⌘
No.	5.5, 7.0mm	lbs.
30896	Phillips: #1, 2	1.34

Wiha SoftFinish® Handle - Standard Series



302 Slotted Screwdriver, With Wiha-SoftFinish® Handle Round blade, high alloy CVM, hardened, hard chromed. Wiha-Chromtop tips. Handle, multi-component, cushion grip.

Item No.	↓	↓	⇄	⇄	⊕	⊕	⇄	⇄	⊕	⊕	↶↷	⇄
	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
30202*	2.0	.079	65	2.6	0.4	.016	169	6.7	23	.91	.05	10
30203*	2.5	.098	75	3.0	0.4	.016	179	7.0	23	.91	.05	10
30204*	3.0	.118	80	3.1	0.5	.020	184	7.2	23	.91	.06	10
30205*	3.0	.118	100	3.9	0.5	.020	204	8.0	23	.91	.06	10
30206*	3.0	.118	150	5.9	0.5	.020	254	10.0	23	.91	.07	10
30208*	3.0	.118	200	8.0	0.5	.020	304	12.0	23	.91	.07	10
30210*	3.5	.139	100	3.9	0.6	.024	204	8.0	23	.91	.07	10
30212*	3.5	.139	200	8.0	0.6	.024	304	12.0	23	.91	.09	10
30215*	4.0	.157	100	3.9	0.8	.031	211	8.3	30	1.18	.11	10
30217*	4.0	.157	150	5.9	0.8	.031	261	10.3	30	1.18	.12	10
30216*	4.0	.157	200	8.0	0.8	.031	311	12.2	30	1.18	.14	10
30218*	4.5	.187	80	3.1	0.8	.031	191	7.5	30	1.18	.11	10
30211*	4.5	.187	125	5.0	0.8	.031	236	9.3	30	1.18	.12	10
30219*	4.5	.187	150	5.9	0.8	.031	261	10.2	30	1.18	.12	10
30220*	5.5	.216	125	5.0	1.0	.039	236	9.3	30	1.18	.15	10
30238*	5.5	.216	300	11.8	1.0	.039	411	16.1	30	1.18	.24	10
30221*	5.5	.216	200	8.0	1.0	.039	311	12.2	30	1.18	.20	10
30222	6.0	.250	100	3.9	1.2	.047	218	8.6	36	1.42	.17	10
30223	6.5	.255	100	3.9	1.2	.039	218	8.6	36	1.42	.20	10
30225	6.5	.255	150	5.9	1.2	.047	268	10.6	36	1.42	.22	10
30226	6.5	.255	200	8.0	1.2	.047	318	12.5	36	1.42	.22	10
30227	8.0	.315	150	5.9	1.2	.047	274	10.8	41	1.61	.29	10
30230	8.0	.315	175	7.0	1.2	.047	299	11.8	41	1.61	.30	10
30232	8.0	.315	300	11.8	1.2	.047	424	16.7	41	1.61	.36	10
30235	10.0	.393	200	8.0	1.6	.063	324	12.8	41	1.61	.36	10
30236	12.0	.472	250	9.8	2.0	.078	374	14.7	41	1.61	.52	10

*Cabinet Tips



311 Phillips Screwdriver, With Wiha-SoftFinish® Handle Round blade, high alloy CVM steel, hardened, hard chromed. Wiha-Chromtop tips. Handle, multi-component, cushion grip.

Item No.	⊕	⇄	⇄	↓	↓	⇄	⇄	⊕	⊕	↶↷	⇄
	Size	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
31105	0	60	2.4	3.0	.118	164	6.5	23	.91	.06	10
31110	1	80	3.1	4.5	.177	191	7.5	30	1.18	.11	10
31112	1	200	8.0	4.5	.177	311	12.3	30	1.18	.15	10
31114	1	300	12.0	4.5	.177	411	16.2	30	1.18	.18	10
31115	2	100	3.9	6.0	.236	218	8.6	36	1.42	.20	10
31117	2	200	8.0	6.0	.236	318	12.5	36	1.42	.25	10
31118	2	300	12.0	6.0	.236	418	16.5	36	1.42	.30	10
31120	3	150	5.9	8.0	.315	274	10.8	41	1.61	.33	10
31125	4	200	8.0	10.0	.393	323	12.7	41	1.61	.51	10



30294 6pc Slotted/Phillips Screwdriver Set

Item No.	↓	⇄	⊕	⇄	↶↷
	mm	mm	Size	mm	lbs.
30294	4.0	100	1	80	1.29
	6.5	150	2	100	
	8.0	150			
	4.0*	25			

*Stubby screwdriver with Wiha SoftFinish® handle



30298 8pc Slotted/Phillips Screwdriver Set

Item No.	↓	⇄	⊕	⇄	↶↷
	mm	mm	Size	mm	lbs.
30298	3.0	100	1	80	1.87
	4.0	100	2	100	
	5.5	125	3	150	
	6.5	150			
	8.0	175			



30297 12pc Slotted & Phillips Screwdriver Set

Item No.	↓	⇄	⊕	⇄	↶↷
	mm	mm	Size	mm	lbs.
30297	3.0	100	0	60	2.48
	4.0	100	1	80	
	5.5	125	2*	25	
	6.5	150	2	100	
	6.5*	25	3	150	
	8.0	175			
	10	200			

*Stubby screwdriver with Wiha SoftFinish® handle

Wiha SoftFinish® Handle - Stubby Screwdrivers



302 Stubby Slotted Screwdriver, With Wiha-SoftFinish® Handle

Item No.	↓	↑	←	→	⊖	⊕	←	→	⊖	⊕	↶	↷	lbs.	pkg.
	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch				
30239	4.0	.157	25	1.0	0.8	.031	75	2.95	34	1.34			.09	10
30255	5.5	.216	25	1.0	1.0	.039	75	2.95	34	1.34			.09	10
30265	6.5	.255	25	1.0	1.2	.047	75	2.95	34	1.34			.10	10



311 Stubby Phillips Screwdriver, With Wiha-SoftFinish® Handle

Item No.	⊕	←	→	⊖	⊕	←	→	⊖	⊕	↶	↷	lbs.	pkg.
	Size	mm	Inch	mm	Inch	mm	Inch	mm	Inch				
31135	1	25	1.0	4.5	.177	75	3.0	34	1.34			.09	10
31140	2	25	1.0	6.0	.236	75	3.0	34	1.34			.10	10



31193 2pc Slotted Stubby Screwdriver Set

Item No.	↓	↑	←	→	↶	↷	lbs.
	mm	mm	mm	mm			
31193	4.0	25	6.5	25			.24



31192 2pc Phillips Stubby Screwdriver Set

Item No.	⊕	←	⊕	←	↶	↷	lbs.
	Size	mm	Size	mm			
31192	1	25	2	25			.24

Wiha SoftFinish® Handle - Square Drivers



358 Square Screwdriver, With Wiha-SoftFinish® Handle

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item No.	□	←	→	⊖	⊕	←	→	⊖	⊕	↶	↷	lbs.	pkg.
	Size	mm	Inch	mm	Inch	mm	Inch	mm	Inch				
35800	0	80	3.1	4.0	5/32	191	7.5	30	1.18			.11	10
35801	1	100	3.9	4.5	5/32	210	8.2	30	1.18			.12	10
35802	2	150	5.9	6.0	1/4	268	10.5	36	1.42			.19	10
35803	3	150	5.9	6.0	1/4	268	10.5	36	1.42			.22	10



30290 10pc Slotted, Phillips & Square Cushion Grip Drivers

Item No.	Slotted: 3.0, 3.5, 4.5, 6.5mm	↶	↷	lbs.
30290	Phillips: 0, 1, 2			1.54
	Square: 1, 2, 3			



31190 2pc Slotted & Phillips Stubby Screwdriver Set

Item No.	↓	↑	⊕	←	↶	↷	lbs.
	mm	mm	Size	mm			
31190	4.0	25	1	25			.24



31191 2pc Slotted & Phillips Stubby Screwdriver Set

Item No.	↓	↑	⊕	←	↶	↷	lbs.
	mm	mm	Size	mm			
31191	6.5	25	2	25			.24



30289 8pc Slotted, Phillips & Square Cushion Grip Drivers In Molded Case

Item No.	Slotted: 3.0, 4.5, 5.5, 6.5mm	↶	↷	lbs.
30289	Phillips: #1, 2			1.69
	Square: #0, 1			



35894 4pc SoftFinish® Square Tip Screwdriver Set

Round blade high alloy CVM steel, hardened, hard chromed.

Item No.	□	←	□	←	↶	↷	lbs.
	Size	mm	Size	mm			
35894	0	80	2	150			.77
	1	100	3	150			



30291 6pc Slotted, Phillips & Square Cushion Grip Drivers

Item No.	Slotted: 4.5, 6.5mm	↶	↷	lbs.
30291	Phillips: 1, 2			1.00
	Square: 1, 2			

Wiha SoftFinish® Pozidriv®



313 Pozidriv® Screwdriver, With Wiha-SoftFinish® Handle

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
31305	0	60	2.4	3.0	.118	164	6.5	23	.91	.06	10
31310	1	80	3.1	4.5	.177	191	7.5	30	1.18	.11	10
31312	1	200	8.0	4.5	.177	311	12.3	30	1.18	.15	10
31315	2	100	3.9	6.0	.236	218	8.6	36	1.42	.20	10
31320	3	150	5.9	8.0	.315	274	10.8	41	1.61	.33	10

Wiha SoftFinish® Slotted Spanner Nut Drivers



305 Slotted Spanner Nut Drivers, With Wiha-SoftFinish® Handle

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item No.	Size	mm	Inch	mm	mm	mm	Inch	mm	Inch	pkg.
30520	M2	80	3.5	1.0	4.5	184	7.2	23	.91	1
30523	M2.3	90	3.5	1.0	5.0	201	7.9	30	1.18	1
30526	M2.6	100	3.9	1.2	5.5	201	7.9	30	1.18	1
30535	M3.5	100	3.9	1.4	7.0	218	8.6	36	1.42	1
30540	M4	100	3.9	1.4	8.0	218	8.6	36	1.42	1
30580	M8	150	5.9	3.0	14.0	274	10.8	41	1.61	1

Soft Grip BiCut SuperCut & Screwdriver Set



32644 7pc Soft Grip BiCut SuperCut & Screwdriver Set

Item No. BiCut SuperCut:
32644 8.0"/200mm BiCut SuperCut
Screwdrivers: Phillips: #0, #1, #2
Slotted: 3.0, 4.0, 6.5mm

Industrial BiCut SuperCut & Screwdriver Set



30942 7pc Industrial BiCut SuperCut & Screwdriver Set

Item No. BiCut SuperCut:
30942 8.0"/200mm BiCut SuperCut
Screwdrivers: Phillips: #0, #1, #2
Slotted: 3.0, 4.0, 6.5mm

Wiha SoftFinish® Handle - Standard Series Sets



30299 20pc Slotted, Phillips, TORX®, Square & Pozidriv® Set


Item No.	Slotted:	Phillips:	TORX®:	Square:	Pozidriv®:	lbs.
30299	3.0, 4.0, 5.5, 6.5, 8.0mm	0, 1, 2	T6, T8, T10, T15, T20, T25, T30	1, 2, 3	1, 2	3.27

Soft Grip BiCut SuperCut & Screwdriver Set

Wiha SoftFinish® CushionGrip Drivers



*Inch & Metric scale on #2 Phillips



Perfect for measuring small parts on the go

30295 5pc Slotted & Phillips Screwdriver Set

Item No.	Slotted	Phillips	Size	mm	lbs.
30295	3.0, 4.0, 6.5	1	80	100	1.02

Wiha SoftFinish® CushionGrip Drivers

With Inch & MM Scale on Blades




Inch and Metric

- Perfect for measuring small parts on the go
- Quickly check drilled hole depths & diameters
- Patented design with permanent laser marking
- Chrome-vanadium-molybdenum tool steel shafts
- Hardened & tempered for long life performance
- Precision machined exact fit tips
- Hard chrome surfaces for incredible wear resistance



31194 2pc Slotted & Phillips Measuring Scale Screwdriver Set

Item	Slotted	Phillips	Size	mm	lbs.
No.	mm	mm			
31194	5.5	125	2	100	.37



Inch & Metric scales



302 Measuring Scale Slotted Screwdriver, With Wiha-SoftFinish® Cushion Grip Handle

Item	Slotted	Phillips	Size	mm	Inch	mm	Inch	mm	Inch	mm	Inch	Scale	lbs.	pkg.	
No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch	Scale	lbs.	pkg.
30237	5.5	7/32	125	5.0	1.0	.039	236	9.3	30	1.18	30-110	.16	10		



Inch & Metric scales



311 Measuring Scale Phillips Screwdriver, With Wiha-SoftFinish® Cushion Grip Handle

Item	Phillips	Size	mm	Inch	mm	Inch	mm	Inch	mm	Inch	Scale	lbs.	pkg.	
No.	Size	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch	Scale	lbs.	pkg.
31137	2	100	3.9	6.0	1/4	218	8.6	36	1.42	20-90	.21	10		

Wiha Screw Holding TORX® Tools

- Laser welded assembly
- Holds screws securely
- Won't damage screws
- Doesn't weaken tool
- Exact fit tips
- Hardened tool steel blades
- Holds standard Torx screws*
- Stainless rotary spring



Screw Holding TORX®

Laser Welded MagicSpring Assembly



362 MagicSpring Screw Holding TORX® Screwdriver, With Wiha-SoftFinish® Handle

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item	Torx	Size	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.	
No.	Size	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
36202	T6	60	2.4	3.5	.139	164	6.5	23	.91	.07	10		
36203	T7	60	2.4	3.5	.139	164	6.5	23	.91	.07	10		
36207	T8	60	2.4	3.5	.139	164	6.5	23	.91	.07	10		
36234	T9	60	2.4	4.0	.157	171	6.7	30	1.18	.11	10		
36244	T10	80	3.1	4.0	.157	191	7.5	30	1.18	.11	10		
36249	T15	80	3.1	4.0	.157	191	7.5	30	1.18	.11	10		
36254	T20	100	3.9	4.0	.157	211	8.3	36	1.42	.16	10		
36256	T25	100	3.9	4.5	.177	211	8.3	36	1.42	.17	10		
36257	T27	115	4.5	5.5	.216	233	9.2	36	1.42	.20	10		
36258	T30	115	4.5	6.0	.236	233	9.2	36	1.42	.21	10		



36290 6pc Set MagicSpring Screw Holding TORX® SoftFinish Screwdrivers

Round blade high alloy CVM steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips. Molded on.

Item	Torx	Size	mm	Torx	Size	mm	lbs.
No.	Size	mm	Size	mm	lbs.		
36290	T8	60	T20	100	.98		
	T10	80	T25	100			
	T15	80	T30	115			



Screw Holding TORX®



*MagicSpring tools will hold Torx® screws made to CamCar Textron Torx® specifications

Wiha TORX® SoftFinish® Screwdrivers



362 TORX® Screwdriver, With Wiha-SoftFinish® Handle

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item	⚙️	⚔️	⚔️	⚔️	⚔️	⚔️	⚔️	⚔️	⚔️	⚔️	⚔️
No.	Size	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
36264	T5	60	2.4	2.5	.098	164	6.5	23	.91	.05	10
36266	T6	60	2.4	3.5	.139	164	6.5	23	.91	.06	10
36268	T7	60	2.4	3.5	.139	164	6.5	23	.91	.06	10
36270	T8	60	2.4	3.5	.139	164	6.5	23	.91	.06	10
36272	T9	60	2.4	4.0	.157	171	6.7	30	1.18	.10	10
36274	T10	80	3.1	4.0	.157	191	7.5	30	1.18	.11	10
36276	T15	80	3.1	4.0	.157	191	7.5	30	1.18	.11	10
36278	T20	100	3.9	4.0	.157	211	8.3	36	1.42	.11	10
36280	T25	100	3.9	4.5	.177	211	8.3	36	1.42	.12	10
36282	T27	115	4.5	5.5	.216	233	9.2	36	1.42	.19	10
36284	T30	115	4.5	6.0	.236	233	9.2	36	1.42	.20	10
36286	T40	130	5.1	7.0	.275	254	10.0	41	1.61	.27	10
36288	T45	130	5.1	8.0	.315	254	10.0	41	1.61	.31	10



#36291



36291 6pc TORX® SoftFinish® - Cushion Grip Set

Round blade high alloy CVM steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component.

Item	⚙️	⚔️	⚔️	⚔️	⚔️
No.	Size	mm	Size	mm	lbs.
36291	T6	60	T9	60	.77
	T7	60	T10	80	
	T8	60	T15	80	

36201 6pc Set - TORX®

Item	⚙️	⚔️	⚔️	⚔️	⚔️
No.	Size	mm	Size	mm	lbs.
36201	T6	60	T15	80	.83
	T8	60	T20	100	
	T10	80	T25	100	



36294 8 Piece TORX® Set

Item	TORX®:	⚔️
No.	T6, T8, T10, T15,	lbs.
36294	T20, T25, T27, T30	1.38



36267 12 Piece TORX® Set

Item	TORX®:	⚔️
No.	T5, T6, T7, T8, T9,	lbs.
36267	T10, T15, T20, T25, T27, T30, T40	2.03

Wiha Security TORX® Screwdrivers



362 Security TORX® Screwdriver With Wiha-SoftFinish® Handle Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item	⚙️	⚔️	⚔️	⚔️	⚔️	⚔️	⚔️	⚔️	⚔️	⚔️	⚔️
No.	Size	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
36269	T7s	60	2.4	3.5	.139	164	6.5	23	.91	.06	10
36271	T8s	60	2.4	3.5	.139	164	6.5	23	.91	.06	10
36273	T9s	60	2.4	4.0	.157	171	6.7	23	.91	.10	10
36275	T10s	80	3.1	4.0	.157	191	7.5	30	1.18	.11	10
36277	T15s	80	3.1	4.0	.157	191	7.5	30	1.18	.11	10
36279	T20s	100	3.9	4.0	.157	211	8.3	30	1.18	.11	10
36281	T25s	100	3.9	4.5	.177	211	8.3	30	1.18	.11	10
36283	T27s	115	4.5	5.5	.216	233	9.2	36	1.42	.19	10
36285	T30s	115	4.5	6.0	.236	233	9.2	36	1.42	.20	10
36287	T40s	130	5.1	7.0	.275	254	10.0	41	1.61	.28	10



36298 7pc Set - Security TORX®

Item	Security TORX®:	⚔️
No.	T7s, T8s, T9s, T10s,	lbs.
36298	T15s, T20s, T25s	.95



36259 10pc Set - Security TORX®

Item	Security TORX®:	⚔️
No.	T7s, T8s, T9s, T10s,	lbs.
36259	T15s, T20s, T25s, T27s, T30s, T40s	1.5

Wiha TORXPlus® Cushion Grip Drivers



Not for use in standard Torx fasteners

362 TORXPlus® Screwdriver With Wiha SoftFinish® Handle

Round blade high alloy Chrome-vanadium-molybdenum tool steel, hardened, hard chromed. Wiha-Chromtop finish on tips.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
36211	IP6	60	2.4	3.5	.139	164	6.5	23	.91	.06	10
36223	IP7	60	2.4	3.5	.139	164	6.5	23	.91	.06	10
36228	IP8	60	2.4	4.0	.157	171	6.7	23	.91	.10	10
36229	IP9	60	2.4	4.0	.157	171	6.7	30	1.18	.11	10
36233	IP10	80	3.1	4.0	.157	191	7.5	30	1.18	.11	10
36238	IP15	80	3.1	4.0	.157	191	7.5	30	1.18	.11	10
36239	IP20	100	3.9	4.5	.177	211	8.3	36	1.42	.11	10
36243	IP25	100	3.9	5.5	.216	211	8.3	36	1.42	.19	10
36248	IP27	115	4.5	6.0	.236	233	9.2	36	1.42	.20	10
36253	IP30	115	4.5	7.0	.275	233	9.2	36	1.42	.28	10
36255	IP40	130	5.1	7.0	.275	254	10.0	41	1.61	.28	10



36296 6pc TORXPlus® Blade high alloy CVM steel, hardened, hard chromed. Wiha-SoftFinish® handle, multi-component.

Item No.	Size	mm	Size	mm	lbs.
36296	IP6	60	IP9	60	.62
	IP7	60	IP10	80	
	IP8	60	IP15	80	



36299 7pc TORXPlus® Blade high alloy CVM steel, hardened, hard chromed. Wiha-SoftFinish® handle, multi-component.

Item No.	Size	mm	Size	mm	lbs.
36299	IP8	60	IP25	100	.99
	IP10	80	IP30	115	
	IP15	80	IP40	130	
	IP20	100			



In clamshell for hanging

Not for use in standard Torx fasteners

362 TORXPlus® Screwdriver With Wiha SoftFinish® Handle In Clamshell

Round blade high alloy Chrome-vanadium-molybdenum tool steel, hardened, hard chromed. Wiha-Chromtop finish on tips.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
36214	IP6	60	2.4	3.5	.139	164	6.5	23	.91	.06	1
36231	IP7	60	2.4	3.5	.139	164	6.5	23	.91	.06	1
36232	IP8	60	2.4	4.0	.157	171	6.7	23	.91	.10	1
36241	IP9	60	2.4	4.0	.157	171	6.7	30	1.18	.11	1
36242	IP10	80	3.1	4.0	.157	191	7.5	30	1.18	.11	1
36246	IP15	80	3.1	4.0	.157	191	7.5	30	1.18	.11	1
36247	IP20	100	3.9	4.5	.177	211	8.3	36	1.42	.11	1
36252	IP25	100	3.9	5.5	.216	211	8.3	36	1.42	.19	1
36262	IP27	115	4.5	6.0	.236	233	9.2	36	1.42	.20	1
36263	IP30	115	4.5	7.0	.275	233	9.2	36	1.42	.28	1
36265	IP40	130	5.1	7.0	.275	254	10.0	41	1.61	.28	1



36297 8pc TORXPlus® Blade high alloy CVM steel, hardened, hard chromed. Wiha-SoftFinish handle, multi-component.


Item No.	Size	mm	Size	mm	lbs.
36297	IP6	60	IP10	80	1.47
	IP7	60	IP15	80	
	IP8	60	IP20	100	
	IP9	60	IP25	100	

Wiha MagicRing SoftFinish® Hex Drivers

Screw Holding Hex Tools



Don't Drop That Screw!
Save Valuable Time!
Improve Productivity!
Make The Job Easy!



367 MagicRing Ball End Hex-Driver Inch, With Wiha-SoftFinish® Handle Hex blade, high alloy CVM steel, hardened, hard chromed. SoftFinish® handle, multi-component, cushion grip.

Item No.	Hex	Ball End	Hex	Hex	Hex	Hex	Hex	Hex	Hex	Hex
No.	Inch	Inch	mm	mm	Inch	mm	Inch	lbs.	pkg.	
36710*	.050	3.1	80	179	7.0	23	.91	.06	10	
36713*	1/16	3.1	80	204	8.0	23	.91	.06	10	
36716*	5/64	3.9	100	204	8.0	23	.91	.07	10	
36719*	3/32	3.9	100	204	8.0	23	.91	.07	10	
36723*	7/64	3.9	100	211	8.3	23	.91	.07	10	
With MagicRing										
36726	1/8	3.9	100	243	9.6	30	1.18	.12	10	
36728	9/64	3.9	100	243	9.6	30	1.18	.12	10	
36732	5/32	5.0	125	271	10.7	30	1.18	.12	10	
36734	3/16	6.0	150	271	10.7	30	1.18	.16	10	
36736	7/32	6.0	150	271	10.7	36	1.42	.23	10	
36738	1/4	6.0	150	271	10.7	36	1.42	.25	10	
36742	5/16	8.0	200	271	10.7	36	1.42	.37	10	
36744	3/8	8.0	200	271	10.7	41	1.61	.54	10	

* Standard Ball - No Ring



36791 13pc MagicRing Inch Ball End Screwdriver Set Hex blade chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	Hex	Ball End	Hex	Hex	Hex
No.	Inch	Inch	Inch	Inch	lbs.
36791	.050*	3.0	5/32	5.0	2.58
	1/16*	3.0	3/16	6.0	
	5/64*	4.0	7/32	6.0	
	3/32*	4.0	1/4	6.0	
	7/64*	4.0	5/16	8.0	
	1/8	4.0	3/8	8.0	
	9/64	4.0			

* Standard Ball - No Ring



36793 8pc MagicRing Inch Ball End

Screwdriver Set Hex blade CVM steel, hardened, hard chromed. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	Hex	Ball End	Hex	Hex	Hex
No.	Inch	Inch	Inch	Inch	lbs.
36793	1/8	4.0	7/32	6.0	2.25
	9/64	4.0	1/4	6.0	
	5/32	5.0	5/16	8.0	
	3/16	6.0	3/8	8.0	



36794 6pc MagicRing Inch Ball End

Screwdriver Set Hex blade CVM steel, hardened, hard chromed. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	Hex	Ball End	Hex	Hex	Hex
No.	Inch	Inch	Inch	Inch	lbs.
36794	1/8	4.0	3/16	6.0	1.34
	9/64	4.0	7/32	6.0	
	5/32	5.0	1/4	6.0	

Wiha MagicRing SoftFinish® Hex Drivers

Screw Holding Hex Tools



Hardened spring steel retaining ring holds screws on

Hard chrome super durable corrosion resistant finish

Precision machined for exact fit

Made from Wiha exclusive CVM hardened tool steel



Hard Chrome Finish

Screw Holding



36790 9pc MagicRing Metric Ball End Hex Screwdriver Set Hex blade CVM steel, hardened, hard chromed. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	Hex	Hex	Hex	Hex	lbs.
36790	1.5*	75	5.0	150	2.06
	2.0*	100	6.0	150	
	2.5*	100	8.0	200	
	3.0	100	10.0	200	
	4.0	125			

* Standard Ball - No Ring



36792 6pc MagicRing Metric Ball End Hex Screwdriver Set Hex blade chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	Hex	Hex	Hex	Hex	lbs.
36792	3.0	100	6.0	150	1.86
	4.0	125	8.0	200	
	5.0	150	10.0	200	

367 MagicRing Ball End Hex Driver Metric, With Wiha-SoftFinish® Handle Hex blade, high alloy CVM steel, hardened, hard chromed. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	Hex	Hex	Hex	Hex	Hex	Hex	Hex	Hex	Hex	lbs.	pkg.
36715*	1.5	75	3.0	179	7.0	23	.91	.06	10		
36720*	2.0	100	3.9	204	8.0	23	.91	.07	10		
36725*	2.5	100	3.9	204	8.0	23	.91	.07	10		
With MagicRing											
36730	3.0	100	3.9	204	8.0	23	.91	.07	10		
36740	4.0	125	5.0	211	8.3	30	1.18	.12	10		
36750	5.0	150	5.0	243	9.6	30	1.18	.16	10		
36760	6.0	150	5.0	243	9.6	36	1.42	.23	10		
36780	8.0	200	8.0	268	10.6	36	1.42	.37	10		
36786	10.0	200	8.0	271	10.7	41	1.61	.54	10		

* Standard Ball - No Ring

Switch Cabinet Keys



21105 Pen Style Control Cabinet Key

For applications with all common switch cabinets and locking systems. Diecast Zinc, polished finish. Includes: Square 5, 6, 7, 8mm, Triangular 9mm, Double Bit Key 5mm/Internal & 9mm/External, Universal 1/4" Bit Adapter, Magnetic Bit Holder & 2 Double Insert Bits: Slotted 7mm / Phillips #2 / TORX T20/T25

Item No.	mm	Inch	Pkg.	lbs.
21105	140	5.5"	1	.30



21103 Switch Cabinet Key

For applications with all common switch cabinets and locking systems. Diecast Zinc. Bit insert Slotted 7.0mm & Phillips #2. Adapter for 1/4" bits on securing chain and 1/4" bit adapter in one arm.

Item No.	mm	Inch	Pkg.	lbs.
21103	76	3.0"	1	.22

Wiha SoftFinish® Bit Holders

Magnetic



Retainer out of stainless steel

384 1/4" Magnetic Bit Holding Drivers, With Wiha SoftFinish® Handle Ergonomic cushion grip, magnetic, holds bit and screw. Shaft CVM steel, nickel-plated. Pkg. 1

Item	Size	mm	Inch	mm	Inch	lbs.
38450	1/4"	125	5.0	240	9.46	.23
38460	1/4"	300	11.8	400	15.69	.37



For working in confined spaces

28103 Magnetic 1/4" Bit Holder With Wiha SoftFinish® Stubby Handle Stainless steel with strong magnet. Wiha-SoftFinish® handle multi-component, cushion grips.

Item	Size	Inch	mm	Inch	lbs.	pkg.
28103	1/4"	57	2.2	.11	1	




Plastic coated flexible metal

Stainless steel with retaining ring

38600 Bit Holder 1/4" with Retaining Ring With Flexible Shaft Wiha-SoftFinish® handle multi-component, cushion grips.

Item	Size	Inch	mm	Inch	mm	Inch	lbs.	pkg.
38600	1/4"	150	5.9	268	10.6	.30	1	

Adjustable Blade Length
Magnetic Bit Holder



28489 Drive-Loc VI Bit Holder

High alloy CVM steel, through hardened, hard chrome finish. Wiha-SoftFinish® handle multi-component, cushion grips.

Item	Size	Inch	Extends	lbs.	pkg.
28489	1/4"	1-3/4"	to 4-7/8"	.36	1

Wiha 3K Series Screwdrivers and Sets



450 Slotted Screwdriver, With Wiha-3K Series Handle Blade chrome-vanadium-molybdenum steel, chrome nickel-plated. Wiha-3k Ergo handle, cushion grip. Precision black tips.

Item	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	Pkg.
45056	4.5	150	5.9	1.0	.04	257	10.1	.14	10
45057	4.5	200	8.0	1.0	.04	306	12.0	.15	10
45060	6.0	100	3.9	0.9	.04	218	8.5	.20	10
45062	6.0	200	8.0	0.9	.04	318	12.5	.25	10
45065	6.5	150	5.9	1.2	.05	268	10.5	.23	10
45067	8.0	150	5.9	1.2	.05	268	10.5	.26	10

* Stubby screwdriver with Wiha Powerhandle - 45064
** Cabinet Tip



451 Phillips Screwdriver, With Wiha-3K Series Handle pkg. 10

Item	Size	mm	Inch	mm	Inch	lbs.
45147	2	200	8.0	318	12.5	.25
45152	3	150	5.9	268	10.5	.31



452 Pozidriv® Screwdriver, With Wiha-3K Series Handle Wiha-3k Ergo handle, cushion grip. Black tip.

Item	Size	mm	Inch	mm	Inch	lbs.
45205	0	60	2.4	146	5.7	.06
45225	2	100	3.9	219	8.6	.21



458 Square Tip Screwdriver, With Wiha-3K Series Handle Blade CVM steel, hard chromed shaft. Wiha-3k Ergo handle, cushion grip. Black tip. Pkg. 1

Item	Size	mm	Inch	mm	Inch	lbs.
45831	1	80	3.1	187	7.3	.14
45832	2	100	3.9	210	8.3	.16
45833	3	150	5.9	271	10.7	.24



45891 3pc Square Tip 3K Driver Set Blade CVM, chrome nickel-plated. Wiha-3k Ergo handle, cushion grip. Precision black tips.


Item	Slotted:	lbs.
No. 45891	#1, 2, 3	.52



455 TORX® Screwdriver, With Wiha-3K Series Handle Blade high alloy CVM steel, hardened, precision black tip. Molded on ergonomic Wiha-3K Series handle, impact resistant.

Item	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
45525	T25	100	3.9	6.0	1/4	215	8.4	.20	10
45527	T27	115	4.5	7.0	9/32	240	9.4	.28	10
45540	T40	130	5.1	7.0	9/32	248	9.7	.25	10
45545	T45	130	5.1	8.0	5/16	249	9.8	.30	10
45550	T50	130	5.1	9.0	3/8	249	9.8	.33	10

Wiha Ball End 3K Series Screwdrivers & Sets



Metric / Soft Grip

467 Ball End Hex Metric Screwdriver, With Wiha-3K Ergo Handle Blades of CVM special steel, hardened, black finish. Molded on Wiha-3K Ergo soft grip handles.

Item						
No.	Size	mm	mm	Inch	mm	Inch
46715	1.5	75	3.0	161	6.3	.07
46720	2.0	100	3.9	186	7.3	.07
46725	2.5	100	3.9	186	7.3	.07
46740	4.0	100	3.9	197	7.8	.11
46750	5.0	100	3.9	197	7.8	.13
46760	6.0	150	5.9	257	10.1	.21
46786	10.0	200	8.0	319	12.6	.52



Inch / Soft Grip

467 Ball End Hex Inch Drivers, With 3K Ergo Soft Grip Handles Blades of CVM special steel, hardened, black finish. Molded on Wiha-3K Ergo soft grip handles.

Item						
No.	Inch	Inch	mm	Inch	mm	lbs.
46702	.050	2.9	75	6.3	160	.07
46704	1/16	2.9	75	6.3	160	.07
46706	5/64	3.9	100	7.3	185	.07
46712	1/8	3.9	100	7.7	196	.09
46716	5/32	3.9	100	7.7	196	.11
46722	7/32	5.9	150	10.0	254	.19

NOTES:

Wiha Powerhandle TORX® Made in Germany



362 TORX® Screwdriver, With Wiha-Powerhandle CVM steel blade, hardened, hard chromed. Wiha-powerhandle cellulose-acetate.

Item									
No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
36240	T25	100	3.9	4.5	.177	200	7.9	.18	10
36250	T30	115	4.5	6.0	.236	225	8.9	.28	10

Wiha TORX® Protturn Screwdrivers



455 TORX® Screwdriver, With Wiha-Protturn Handle Blade high alloy CVM steel, hardened, black finish. Molded on ergonomic Wiha-Protturn handle, impact resistant.

Item									
No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
45505	T6	50	2.0	3.5	.139	129	5.1	.05	10
45521	T10	80	3.1	4.0	.157	170	6.7	.10	10
45546	T30	115	4.5	6.0	.236	215	8.4	.20	10
45551	T40	130	5.1	7.0	.275	240	9.4	.28	10

Wiha Offset Screwdrivers



161 Phillips Offset Screwdriver, With Handle For working in confined spaces. Blade CVM special steel, hardened, hard chromed. Handle high quality plastic, impact resistant.

Item							
No.	Size	mm	Inch	mm	Inch	lbs.	Pkg.
16112	1 + 2	125	4.9	5.5	.217	.08	10



207 Slotted Offset Screwdriver, With Handle

Item									
No.	mm	Inch	mm	Inch	mm	Inch	lbs.	Pkg.	
20715	6.5	1/4	125	5.0	1.2	.05	.07	10	

Wiha Offset Screwdrivers



207 TORX® Offset Screwdriver With Molded Handle Working in confined spaces. CVM special steel, hardened, black finish.

Item			
No.	Size	lbs.	pkg.
20756	T6 + T8	.02	1
20757	T7 + T9	.02	1
20758	T10 + T15	.02	1
20759	T20 + T25	.07	1
20760	T27 + T30	.10	1



20799 TORX® Offset Screwdriver Set, 5pc Molded Handle.

Item				
No.	T6+T8, T7+T9, T10+T15, T20+T25, T27+T30	lbs.	pkg.	
20799		.24	1	

Wiha Drive-Loc VI Handles & Blades

For Adjustable Length Locking Blades

Ergonomic handles in ESD Safe, cushioned & non-slip grip



See Drive-Loc VI Nut drivers on Page 39

Blade length can be adjusted from 1.7 to 4.7" in 1/8" increments

Blades high quality CVM steel, hard chrome finish

Adjust interchangeable blades from 40 to 120mm

Drive-Loc mechanism guarantees a secure hold & rapid blade exchange



28488 Drive-Loc VI Cushion Grip Handle

Wiha-SoftFinish® impact resistant, with roll off protection.

Item	mm	mm	Inch	mm	Inch	lbs.
28488	6.0	115	4.5	36.0	1.41	.26



28486 ESD Safe Drive-Loc VI Cushion Grip Handle

Wiha-SoftFinish® impact resistant, with roll off protection.

Item	mm	mm	Inch	mm	Inch	lbs.
28486	6.0	115	4.5	36.0	1.41	.21



28487 Drive-Loc VI MicroFinish Non-Slip Grip Handle

Wiha-MicroFinish handle, won't peel, crack or deteriorate when exposed to petroleum solvents.

Item	mm	mm	Inch	mm	Inch	lbs.
28487	6.0	115	4.5	36.0	1.41	.20



10810 Drive-Loc VI Standard Narrow Profile Tech Handle

Dynamic non-locking, impact resistant, friction hold. Fits all Drive-Loc blades. Does not have locking feature.

Item	mm	mm	Inch	mm	Inch	lbs.
10810	6.0	135	5.3	15.2	.60	.16



281 Slotted Drive-Loc VI Interchangeable Blade

High alloy CVM steel, through hardened, hard chrome finish. OAL 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item	mm + mm	lbs.	pkg.
28106	3.5 4.5	.10	1
28108	5.5 6.5	.10	1



281 Slotted & Phillips Drive-Loc VI Interchangeable Blade

High alloy CVM steel, through hardened, hard chrome finish. OAL 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item	mm + Size	lbs.	pkg.
28107	3.0 0	.10	1
28109	4.0 1	.10	1
28110	6.0 2	.10	1



28112 Phillips Drive-Loc VI Interchangeable Blade

High alloy CVM steel, through hardened, hard chrome finish. OAL 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item	Size + Size	lbs.	pkg.
28112	1 2	.10	1



28137 Square Drive-Loc VI Interchangeable Blade

High alloy CVM steel, through hardened, hard chrome finish. OAL 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item	Size + Size	lbs.	pkg.
28137	1 2	.10	1



28114 Pozidriv® Drive-Loc VI Interchangeable Blade

High alloy CVM steel, through hardened, hard chrome finish. OAL 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item	Size + Size	lbs.	pkg.
28114	1 2	.10	1



281 Tri-wing® Drive-Loc VI Interchangeable Blade

High alloy CVM steel, through hardened, hard chrome finish. OAL 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item	Size + Size	lbs.	pkg.
28138	0 1	.10	1
28139	2 3	.10	1
28140	4 5	.10	1



281 Torq Set® Drive-Loc VI Interchangeable Blade

High alloy CVM steel, through hardened, hard chrome finish. OAL 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item	Size + Size	lbs.	pkg.
28142	2 4	.08	1
28143	6 8	.10	1



281 TORX® Drive-Loc VI Interchangeable Blade

OAL 150mm/5.9"

Item	Size + Size	lbs.	pkg.
28126	T6 T8	.10	1
28127	T7 T9	.10	1
28128	T10 T15	.10	1
28129	T20 T25	.10	1
28130	T30 T40	.10	1



281 Security TORX® Drive-Loc VI Interchangeable Blade

OAL 150mm/5.9"

Item	Size + Size	lbs.	pkg.
28132	T6s T8s	.10	1
28133	T7s T9s	.10	1
28134	T10s T15s	.10	1
28135	T20s T25s	.10	1
28136	T30s T40s	.10	1

Wiha Drive-Loc VI Blades



281 Hex Metric Drive-Loc VI Interchangeable Blade OAL 150mm/5.9"

Item	Hex	Hex	↔	↔
No.	mm + mm	lbs.	pkg.	
28149	2.0 2.5	.09	1	
28150	3.0 4.0	.10	1	
28151	5.0 6.0	.10	1	



281 Hex Inch Drive-Loc VI Interchangeable Blade OAL 150mm/5.9"

Item	Hex	Hex	↔	↔
No.	Inch + Inch	lbs.	pkg.	
28122	3/32 7/64	.10	1	
28123	1/8 9/64	.10	1	
28124	5/32 3/16	.10	1	



281 Ball End Hex & Hex Metric Drive-Loc VI Interchangeable Blade Ball end enables the user to work at angles up to 25°. OAL 150mm/5.9". Fits all Drive-Loc VI handles.

Item	Hex	Hex	↔	↔
No.	mm + mm	lbs.	pkg.	
28116	2.5 2.5	.10	1	
28117	3 3	.10	1	
28118	4 4	.10	1	
28119	5 5	.10	1	
28120	6 6	.10	1	

Drive-Loc VI Interchangeable Blade Sets



28187 32pc ESD Safe Drive-Loc VI Interchangeable Blade Set, In Folding Wallet Set includes Drive-Loc VI handle & 31 interchangeable blades.

Item No. 28187	↔ lbs.	3.66
Slotted:	3.5+4.5, 5.5+6.5mm	Square: 1+2
Slotted/Phillips:	3.0+0, 4.0+1, 6.0+2	
Security TORX®:	T6s+T8s, T7s+T9s, T10s+T15s, T20s+T25s, T30s+T40s	
Hex Inch:	3/32+7/64, 1/8+9/64, 5/32+3/16	
Hex Metric:	2.0+2.5, 3.0+4.0, 5.0+6.0	
Nut Drivers In:	1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2"	
Nut Drivers MM:	5.5, 6.0, 7.0, 8.0, 9.0, 10.0, 11.0mm	
Wiha ESD Safe SoftFinish® Cushion Grip		



28483 5 Pack Drive-Loc VI Interchangeable Blade Set OAL 150mm/5.9"

Item	↔ lbs.	
No. 28483	.35	
Slotted/Phillips:	3.0+#0, 4.0+#1, 6.0+#2	
Square:	#1+#2 & Pozidriv®: #1+#2	



28479 5 Pack Drive-Loc VI Interchangeable Blade Set OAL 150mm/5.9"

Item	↔ lbs.	
No. 28479	.35	
Tri-Wing:	#0+#1, #2+#3, #4+#5	
Torq Set:	#2+#4, #6+#8	



28477 5 Pack Drive-Loc VI Interchangeable Blade Set OAL 150mm/5.9"

Item	↔ lbs.	
No. 28477	.35	
Security TORX®:	T6s+T8s, T7s+T9s, T10s+T15s, T20s+T25s, T30s+T40s	

Wiha Drive-Loc VI Blade 5 Pack Sets



28474 5 Pack Drive-Loc VI Interchangeable Blade Set OAL 150mm/5.9"

Item	↔ lbs.	
No. 28474	.36	
Hex Metric:	3.0+4.0, 5.0+6.0mm	
Hex Inch:	3/32+7/64, 1/8+9/64, 5/32+3/16"	



28476 5 Pack Drive-Loc VI Interchangeable Blade Set OAL 150mm/5.9"

Item	↔ lbs.	
No. 28476	.36	
Hex Metric:	2.5, 3.0, 4.0, 5.0, 6.0mm	



28485 5 Pack Drive-Loc VI Interchangeable Blade Set OAL 150mm/5.9"

Item No. 28485	↔ lbs.	
TORX®:	.35	
T6+T8, T7+T9, T10+T15, T20+T25, T30+T40		

Drive-Loc VI Interchangeable Blade Set In Tool Box Tray



Tool box set in blow molded tray



28191 33pc Drive-Loc VI Interchangeable Blade Set, In Tool Box Tray Set includes Drive-Loc VI handles & 31 Drive-Loc VI blades.

Item No. 28191	↔ lbs.	3.48
Slotted:	3.5+4.5, 5.5+6.5mm	Square: 1+2
Slotted/Phillips:	3.0+0, 4.0+1, 6.0+2	
Security TORX®:	T6s+T8s, T7s+T9s, T10s+T15s, T20s+T25s, T30s+T40s	
Hex Inch:	3/32+7/64, 1/8+9/64, 5/32+3/16	
Hex Metric:	2.0+2.5, 3.0+4.0, 5.0+6.0	
Nut Drivers In:	1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2"	
Nut Drivers MM:	5.5, 6.0, 7.0, 8.0, 9.0, 10.0, 11.0mm	
Wiha SoftFinish® Cushion Grip & MicroFinish Non-Slip Grip Handles		



28194 5pc Drive-Loc VI Interchangeable Blade Set, In Durable Pouch Set includes Drive-Loc VI handle & 4 interchangeable blades.

Item No. 28194 ↔ lbs.

Slotted: 3.5+4.5, 5.5+6.5 .80

Phillips: 1+2 **Square:** 1+2

SoftFinish® Cushion Grip Blade Lock Handle



28197 6pc Drive-Loc VI Interchangeable Blade Set, In Durable Pouch Set includes Drive-Loc VI handle & 5 interchangeable blades.

Item ↔ lbs.

No. 28197 .83

Security TORX®: T6s+T8s, T7s+T9s, T10s+T15s, T20s+T25s, T30s+T40s

SoftFinish® Cushion Grip Blade Lock Handle



28199 10pc Drive-Loc VI Interchangeable Blade Set, In Durable Pouch Set includes Drive-Loc VI handle & 9 interchangeable blades.

Item No. 28199 ↔ lbs.

Slot/Ph: 4.0+1, 6.0+2 1.11

TORX®: T6+T8, T7+T9, T10+T15, T20+T25

Hex Inch: 3/32+7/64, 1/8+9/64, 5/32+3/16"

SoftFinish® Cushion Grip Blade Lock Handle



28189 15pc Drive-Loc VI Interchangeable Blade Set, In Folding Wallet Set includes Drive-Loc VI handle & 14 interchangeable blades.

Item No. 28189 ↔ lbs. 1.75

Slotted: 3.5+4.5, 5.5+6.5 **Phillips:** 1+2

Security TORX®: T6s+T8s, T7s+T9s, T10s+T15s, T20s+T25s, T30s+T40s

Hex Inch: 3/32+7/64, 1/8+9/64, 5/32+3/16

Hex Metric: 2.0+2.5, 3.0+4.0, 5.0+6.0mm

SoftFinish® Cushion Grip Blade Lock Handle

Wiha MicroFinish Handle - Non-Slip Grip

Wiha MicroFinish handle has a patented non-slip surface - It won't peel, crack or deteriorate when exposed to petroleum solvents. Oil and moisture flow away from the handle surface for a powerful, non-slip grip. Get maximum force & comfort with dry, oily or wet hands.

Safe, high density material, eliminates risk of sharp objects becoming embedded in the handle

Through hardened blades & hard chrome finish

Exact fit precision ground tips

CVM, hardened & tempered tool steel blade, gives exceptional tool life, wear resistance & high torque performance

Hex bolster & steel strike cap on 533 & 534 series



520 Slotted Screwdriver, With Wiha-MicroFinish Handle

Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant. Round blades.

Item No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
52005*	4.0	.157	100	3.9	0.8	.031	211	8.3	30	1.18	.16	10
52010*	4.0	.157	150	5.9	0.8	.031	261	10.3	30	1.18	.17	10
52020*	5.5	.216	125	5.0	1.0	.039	236	9.3	30	1.18	.20	10
52025*	5.5	.216	150	5.9	1.0	.039	261	10.3	30	1.18	.21	10
52035	6.5	.255	150	5.9	1.2	.047	268	10.6	36	1.42	.28	10
52040	8.0	.315	150	5.9	1.2	.047	274	10.8	41	1.61	.37	10
52050	10.0	.393	200	8.0	1.6	.063	324	12.8	41	1.61	.50	10

*Cabinet Tips



521 Phillips Screwdriver, With Wiha-MicroFinish Handle

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
52105	1	80	3.1	191	7.5	30	1.18	.15	10
52110	1	200	8.0	311	12.2	30	1.18	.21	10
52115	2	100	3.9	218	8.6	36	1.42	.26	10
52120	2	200	8.0	318	12.5	36	1.42	.34	10
52125	3	150	5.9	274	10.8	41	1.61	.41	10



52090 5pc Slotted & Phillips Screwdriver Set

Blade CVM steel, hardened, hard chromed.

Item No.	Slotted:	↔ lbs.
52090	4.0x100, 5.5x125, 8.0x150mm	1.23



52099 12pc MicroFinish® Slotted & Phillips Screwdriver Set

Item No.	Slotted:	↔ lbs.
52099	4.0x150, 5.5x125, 5.5x150, 6.5x150, 8.0x150, 10.0x200mm	4.20
	Phillips: 1x80, 1x200, 2x100, 2x200, 3x150mm	



52097 7pc Slotted/Phillips Screwdriver Set

Item No.	Slotted:	↔ lbs.
52097	4.0x100, 5.5x125, 8.0x150mm	1.35
	Phillips: #1x80, #1x200, #2x100, #2x200mm	



52098 8pc Slotted/Phillips Screwdriver Set

Item No.	Slotted:	↔ lbs.
52098	4.0x100, 5.5x125, 6.5, 8.0x150, 10.0x200mm	2.58
	Phillips: 1x80, 2x100, 3x150mm	

Wiha MicroFinish Extra Heavy Duty Non-Slip Grip Handle



533 Heavy Duty Slotted Screwdriver, Wiha-MicroFinish Handle & Steel Striking Cap
 Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Hex blade extending through handle with striking plate. Hex bolster for additional torque. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant.

Item	↓	↑	←	→	⊖	⊕	⊖	⊕	↶	↷	⊖	⊕
No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
53310*	4.5	.177	90	3.6	1.0	.039	201	7.9	30	1.18	.20	10
53315	5.5	.216	100	3.9	1.0	.039	213	8.4	36	1.42	.33	10
53320	6.5	.255	125	5.0	1.2	.047	238	9.4	36	1.42	.38	10
53325	8.0	.315	150	5.9	1.2	.047	271	10.7	41	1.61	.61	10
53330	10.0	.393	175	7.0	1.6	.063	296	11.7	41	1.61	.65	10

*No hex bolster



534 Heavy Duty Phillips Screwdriver, Wiha-MicroFinish Handle & Steel Striking Cap
 Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Hex blade extending through handle with striking plate. Hex bolster for additional torque. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant.

Item	⊕	←	→	⊖	⊕	⊖	⊕	↶	↷	⊖	⊕
No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.		
53405	1	80	3.1	186	7.3	30	1.18	.22	10		
53410	2	100	3.9	213	8.4	36	1.42	.37	10		
53425	3	150	5.9	268	10.6	41	1.61	.71	10		

Wiha TORX® MicroFinish Handle Non-Slip Grip



527 TORX® Screwdriver, With Wiha-MicroFinish Handle Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant. Round blades.

Item	⊕	←	→	⊖	⊕	⊖	⊕	↶	↷	⊖	⊕
No.	Size	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
52711	T9	60	2.4	4.0	.157	171	6.7	30	1.18	.15	10
52713	T10	80	3.1	4.0	.157	191	7.5	30	1.18	.15	10
52716	T15	80	3.1	4.0	.157	191	7.5	30	1.18	.15	10
52719	T20	100	3.9	4.0	.157	211	8.3	30	1.18	.15	10
52722	T25	100	3.9	4.5	.177	211	8.3	30	1.18	.16	10
52726	T27	115	4.5	5.5	.216	233	9.2	36	1.42	.25	10
52729	T30	115	4.5	6.0	.236	233	9.2	36	1.42	.27	10
52732	T40	130	5.1	7.0	.275	254	10.0	41	1.61	.40	10



52791 8pc TORX® Blade CVM steel, hardened, round blades hard chromed. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil & grease resistant.

Item	TORX®	↶	↷
No.	T9, T10, T15, T20, T25,	lbs.	
52791	T27, T30, T40	1.89	



53390 5pc Slotted/Phillips, Heavy Duty Set
 Blade CVM steel, hardened, hard chromed. Hex blade extending through handle with steel striking cap. Hex bolster for additional torque.

Item	Slotted:	↶	↷
No.	5.5, 6.5, 8.0mm	lbs.	
53390	Phillips: #1, 2	2.1	



53398 8pc Slotted/Phillips, Heavy Duty Set
 Blade CVM steel, hardened, hard chromed. Hex blade extending through handle with steel striking cap. Hex bolster for additional torque.

Item	Slotted:	↶	↷
No.	4.5*, 5.5, 6.5, 8.0, 10.0mm	lbs.	
53398	Phillips: #1, 2, 3	3.7	

*No hex bolster



52790 5pc TORX® Blade CVM steel, hardened, round blades hard chromed. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil & grease resistant.

Item	TORX®	↶	↷
No.	T10, T15, T20,	lbs.	
52790	T25, T30	1.0	

Wiha MicroFinish Non-Slip Grip Bit Holder



52650 1/4" Bit holding Screwdriver, With Wiha-MicroFinish Handle Magnetic, holds bit and screw. Retainer out of stainless steel. Shaft chrome-vanadium steel, nickel-plated.

Item	↶	↷	↶	↷	↶	↷	
No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
52650	1/4	125	5.0	244	9.6	.24	10

Wiha Power Blades

CentroFix quick release bit holder with magnet

Ergonomic SoftFinish® cushion grip handle



76000 CentroFix Cushion Grip Blade Holder

Wiha-SoftFinish® impact resistant, with roll off protection. Ergonomic cushion grip handle. Quick release bit holder with magnet.

Item						
No.	mm	mm	Inch	mm	Inch	lbs.
76000	6.0	149	5.9	34.6	1.36	.26

Blades high quality CVM steel, hard chrome finish



760 Slotted Power Blades

S2 modified tool steel. Hardened & tempered to HRC 60. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item					
No.	mm	lbs.	pkg.		
76035	2.5	.02	1		
76036	3.0	.02	1		
76037	4.5	.03	1		
76038	5.5	.03	1		
76039	6.0	.04	1		



76093 5pc Slotted Blade Set

Item					
No.	lbs.	Slotted:	2.5, 3.0, 4.5,		
76093	.16	5.5, 6.0mm	x 90mm		



760 Phillips Power Blades

S2 modified tool steel. Hardened & tempered to HRC 60. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item					
No.	Size	lbs.	pkg.		
76041	0	.01	1		
76042	1	.02	1		
76043	2	.03	1		
76044	3	.04	1		



76094 4pc Phillips Blade Set

Item					
No.	lbs.	Phillips:	#0, 1, 2,		
76094	.17	3 x 90mm			

90mm Power Blades



760 Square Power Blades

S2 modified tool steel. Hardened & tempered to HRC 60. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item					
No.	Size	lbs.	pkg.		
76056	1	.02	1		
76057	2	.03	1		
76058	3	.04	1		



76095 3pc Square Blade Set

Item					
No.	lbs.	Set includes:			
76095	.11	Square: #1, 2,	3 x 90mm		



760 Pozidriv® Power Blades

S2 modified tool steel. Hardened & tempered to HRC 60. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item					
No.	Size	lbs.	pkg.		
76011	1	.03	1		
76012	2	.04	1		
76013	3	.04	1		



76091 3pc Pozidriv® Blade Set

Item					
No.	lbs.	Set includes:			
76091	.12	Pozidriv®: #1, 2,	3 x 90mm		



760 Spanner Power Blades

S2 modified tool steel. Hardened & tempered to HRC 60. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item					
No.	Size	lbs.	pkg.		
76026	4	.03	1		
76022	6	.03	1		
76023	8	.04	1		
76024	10	.04	1		



76089 3pc Spanner Blade Set

Item					
No.	lbs.	Set includes:			
76089	.12	Spanner: #6, 8,	10 x 90mm		



760 Tri-Wing Power Blades

S2 modified tool steel. Hardened & tempered to HRC 60. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item					
No.	Size	lbs.	pkg.		
76031	1	.02	1		
76032	2	.02	1		
76033	3	.03	1		
76034	4	.04	1		



76088 4pc Tri-Wing Blade Set

Item					
No.	lbs.	Set includes:			
76088	.16	Tri-Wing: #1, 2,	3, 4 x 90mm		

76098 36pc Power Blade Set, In Folding Wallet

Set includes cushion grip CentroFix Blade Holder & 35 interchangeable blades.

Item No. 76098			lbs. 1.86
Slotted:	2.5, 3.0, 4.5, 5.5, 6.0mm		
Phillips:	#0, 1, 2, 3		
Security TORX:	T8s, T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s		
Security Hex Metric:	2.5, 3.0, 4.0, 5.0mm		
Pozidriv®:	#1, 2, 3 & Square: #1, 2, 3		
Spanner:	#6, 8, 10 & Tri-Wing: #1, 2, 3, 4		
Cushion Grip CentroFix Blade Holder			

Wiha 90mm Power Blades & Sets



760 Security Hex Metric Power Blades

S2 modified tool steel. Hardened & tempered to HRC 60. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item			
No.	mm	lbs.	pkg.
76001	2.5	.02	1
76002	3.0	.02	1
76003	4.0	.03	1
76004	5.0	.04	1



76090 4pc Security Hex Blade Set

Item		Set includes:
No.	lbs.	Metric: 2.5, 3.0,
76090	.12	4.0, 5.0 x 90mm



760 Security Hex Inch Power Blades

OAL 90mm/3.5".

Item			
No.	Inch	lbs.	pkg.
76046	5/64	.01	1
76047	3/32	.02	1
76048	7/64	.02	1
76049	1/8	.03	1
76050	9/64	.03	1
76051	5/32	.04	1
76052	3/16	.04	1
76053	7/32	.05	1
76054	1/4	.06	1



76096 10pc Security Hex Blade Set

Item		Set includes:
No.	lbs.	Inch: 1/16", 5/64,
76096	.32	3/32, 7/64, 1/8,
		9/64, 5/32, 3/16,
		7/32, 1/4" x 90mm

* 1/16" Standard Inch Hex Only



760 Security TORX® Power Blades

S2 modified tool steel. Hardened & tempered to HRC 60. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item			
No.	Size	lbs.	pkg.
76008	T8s	.02	1
76009	T9s	.02	1
76010	T10s	.02	1
76015	T15s	.02	1
76020	T20s	.02	1
76025	T25s	.03	1
76027	T27s	.03	1
76030	T30s	.04	1
76040	T40s	.04	1



76092 9pc Security TORX® Blade Set

Item		Set includes:
No.	lbs.	T8s, T9s, T10s, T15s,
76092	.30	T20s, T25s, T27s, T30s, T40s



760 Hex Inch Power Blades

S2 modified tool steel. Hardened & tempered to HRC 60. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item			
No.	Inch	lbs.	pkg.
76045	1/16	.01	1
76005	5/64	.01	1
76007	3/32	.02	1
76008	7/64	.02	1
76014	1/8	.03	1
76016	9/64	.03	1
76017	5/32	.04	1
76018	3/16	.04	1
76019	7/32	.05	1
76021	1/4	.06	1



76079 Canvas Folding Wallet

Holds 38 90mm power blades.

Item	
No.	Size
76079	7-1/8" x 6" x 2"



76099 37pc Power Blade Set, In Folding

Wallet Set includes cushion grip CentroFix Blade Holder & 36 interchangeable blades.

Item No. 76099		lbs. 2.06
Slotted:	2.5, 3.0, 4.5, 5.5, 6.0mm	
Phillips:	#0, 1, 2, 3	
Security TORX®:	T8s, T9s, T10s, T15s, T20s, T25s, T27s, T30s	
Security Hex Inch:	1/16", 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	
Pozidriv®:	#1, 2, 3 & Square: #1, 2, 3	
4" Nut Setters:	1/4, 5/16, 3/8"	
Cushion Grip CentroFix Blade Holder		
* 1/16" Standard Inch Hex Only		



76087 61pc Power Blade Service Kit

Set includes Bit Holding Handle, MicroBit Storage Handle, 4mm to 1/4" Magnetic Adapter, 9 power blades, 46 bits & 3 nut setters.

Item No. 76087		lbs. 1.34
90mm Power Blades:	Slotted: 4.5, 5.5, 6.0mm	
Phillips:	#1, 2, 3 & Square: #1, 2, 3	
75mm Security TORX® Bits:	T10s, T15s, T20s, T25s, T27s, T30s	
MicroBits:	Phillips: #000, 00, 0, 1, 2,	
Slotted:	.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm	
Hex Inch:	.028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"	
Hex Metric:	1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm	
TORX®:	T1, T2, T3, T4, T5, T6, T7, T8, T9, T10	
Magnetic Nut Setters:	1/4, 5/16, 3/8"	

Rotating cap
for precise turning and control with fingertip

Precision handle
high quality plastic, cadmium free

Molded on tapered handle
allows rapid rotation

High performance blades
CVM steel,
Hard chrome finished

Tip
precision ground for exact fit,
hard chromed non-slip surface

Wiha Precision Chip Lifter & Accessories



26810 Precision Chip Lifter
Blade CVM steel, hardened, chrome-plated. Precision handle high quality plastic, impact resistant. Standard handle

Item	Icon	Icon	Icon	Icon	Icon	Icon	Icon
No.	mm	mm	mm	mm	Inch	lbs.	Pkg.
26810	1	3.5	50	145	5.7	.07	1

*Metric dimensions actual - Inch dimensions approximate



26001 Pocket Clip for Precision Screwdrivers Tool clips turn Precision Screwdrivers into Pocket Screwdrivers.

Item No.	Fits all	lbs.	pkg.
26001	Precision handles	.01	1



26000 Plastic Precision Tool Rack
Rack holds 6 precision screwdrivers, can be set on workbench. Also has holes for hanging. Made from high quality plastic.

Item No.	Rack for 6	lbs.	Pkg.
26000	Precision screwdrivers	.08	1

Wiha Precision Slotted/Phillips Drivers



260 Slotted Screwdriver, With Precision Handle Blade high alloy chrome-vanadium-molybdenum steel. Pkg. 10

Item No.	Blade	mm	Inch	mm	Inch	mm	Inch	lbs.
26008	Slotted	.80	1/32	40	1.6	0.16	120	4.7 .02
26010	Slotted	1.0	.039	40	1.6	0.18	120	4.7 .02
26012	Slotted	1.2	3/64	40	1.6	0.20	120	4.7 .02
26015	Slotted	1.5	1/16	40	1.6	0.25	120	4.7 .02
26018	Slotted	1.8	.070	40	1.6	0.30	120	4.7 .02
26020	Slotted	2.0	5/64	40	1.6	0.40	120	4.7 .02
26022	Slotted	2.0	5/64	50	2.0	0.40	145	5.7 .02
26023	Slotted	2.0	5/64	100	3.9	0.40	180	7.1 .03
26025	Slotted	2.5	3/32	50	2.0	0.40	145	5.7 .03
26027	Slotted	2.5	3/32	100	3.9	0.40	195	7.7 .03
26028	Slotted	2.5	3/32	150	6.0	0.40	245	9.6 .04
26030	Slotted	3.0	1/8	50	2.0	0.50	145	5.7 .03
26032	Slotted	3.0	1/8	60	2.4	0.50	170	6.7 .04
26033	Slotted	3.0	1/8	100	3.9	0.50	210	8.3 .04
26034	Slotted	3.0	1/8	150	5.9	0.50	260	10.2 .05
26035	Slotted	3.5	9/64	60	2.4	0.60	170	6.7 .05
26040	Slotted	4.0	5/32	60	2.4	0.80	170	6.7 .05
26041	Slotted	4.0	5/32	100	3.9	0.80	210	8.3 .06
26042	Slotted	4.0	5/32	150	5.9	0.80	260	10.2 .07

*Metric dimensions actual - Inch dimensions approximate



261 Phillips Screwdriver, With Precision Handle Blade high alloy chrome-vanadium-molybdenum steel. Pkg. 10

Item No.	Blade	mm	Inch	mm	Inch	mm	Inch	lbs.
26102	Phillips	000	40	1.6	2.0	.08	120	4.7 .02
26100	Phillips	00	40	1.6	2.0	.08	120	4.7 .02
26101	Phillips	00	75	3.0	2.0	.08	155	6.1 .02
26105	Phillips	0	50	2.0	3.0	.12	145	5.7 .02
26108	Phillips	0	75	3.0	3.0	.12	170	6.7 .03
26107	Phillips	0	100	3.9	3.0	.12	195	7.6 .05
26109	Phillips	0	150	5.9	3.0	.12	245	9.6 .06
26110	Phillips	1	60	2.4	4.0	.16	170	6.7 .05
26113	Phillips	1	80	3.1	4.0	.16	190	7.5 .05
26114	Phillips	1	100	3.9	4.0	.16	210	8.2 .06
26115	Phillips	1	150	5.9	4.0	.16	260	10.2 .07

*Metric dimensions actual - Inch dimensions approximate



26190 8pc Precision Slotted & Phillips Screwdrivers and Industrial Long Nose Pliers Set

Item No.	Slotted:	lbs.
26190	1.5, 2.0 x 40mm, 2.5, 3.0 x 50mm, 3.0 x 60mm	.72
	Phillips: 00 x 40mm, 0 x 50mm, 1 x 60mm	
	Industrial Long Nose Pliers	
	6.3"/160mm OAL	



26190.MC/26197 7pc Precision Slotted & Phillips Set

Item No.	Slotted:	lbs.
26197	2.0, 2.5 x 50mm, 3.0 x 60mm	.31
	Phillips: 00 x 40mm, 0 x 50mm, 1 x 60mm	



26199 8pc Precision Slotted/Phillips Set

Item No.	Slotted:	lbs.
26199	1.0, 1.2, 1.5, 2.0 x 40mm, 3.0 x 50mm, 4.0 x 60mm	.55
	Phillips: 000, 00 x 40mm, 0 x 50mm, 1 x 60mm	

Wiha Precision Slotted/Phillips Drivers



26092 7pc Precision Slotted & Phillips

Set Blade high alloy chrome-vanadium-molybdenum steel.

Item No.		
26092	Slotted:	lbs.
	2.5 x 50mm,	.30
	2.5, 3.0, 4.0 x 100mm	
	3.0, 4.0 x 150mm	
	Phillips:	
	0 x 75mm	



26194 4pc Precision Phillips Set

Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished.

Item No.	Phillips:	
No.	000, 00 x 40mm	lbs.
26194	0 x 50mm, 1 x 60mm	.18



26192 5pc Precision Slotted & Phillips

Set Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	Slotted:	
No.	2.5, 3.0, 4.0 x 150mm	lbs. .44
26192	Phillips:	
	0, 1 x 150mm	

Wiha Pozidriv® Precision Series



262 Pozidriv® Screwdriver, With

Precision Handle Blade high alloy chrome-vanadium-molybdenum steel. Pkg. 10

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.
26205	0	50	2.0	3.0	.12	145	5.7	.03
26210	1	60	2.4	4.0	.16	170	6.7	.05

*Metric dimensions actual - Inch dimensions approximate

Wiha Hex Inch & Metric Precision Series



263 Inch **Inch Hex Driver, With Precision Handle** Inch sizes. Blade high alloy chrome-vanadium-molybdenum steel. Pkg. 10

Item No.	Inch	mm	mm	Inch	mm	Inch	lbs.
26307	0.028	0.7	40	1.6	120	4.7	.02
26309	0.035	0.9	40	1.6	120	4.7	.02
26313	0.05	1.3	40	1.6	120	4.7	.02
26316	1/16	-	50	2.0	145	5.7	.03
26320	5/64	2.0	50	2.0	145	5.7	.03
26323	3/32	-	60	2.4	170	6.7	.04
26327	7/64	-	60	2.4	170	6.7	.04
26331	1/8	-	60	2.4	170	6.7	.04
26333	9/64	60	2.4	170	6.7	6.7	.05
26336	5/32	60	2.4	170	6.7	6.7	.05

*Metric dimensions actual - Inch dimensions approximate



26391 8pc Precision Hex Driver Set - Inch Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	Hex Inch:	
26391	.028, .035, .050 x 1.6"	lbs. .32
	1/16, 5/64 x 2.0"	
	3/32, 7/64, 1/8 x 2.4"	



26399 8pc Precision Hex Driver Set - Inch Blade high alloy CVM steel. Hard chrome finished. In canvas storage pouch

Item No.	Hex Inch:	
26399	.028, .035, .050 x 1.6"	lbs. .55
	1/16, 5/64 x 2.0", 3/32, 7/64, 1/8 x 2.4"	



263 Metric **Metric Hex Driver, With Precision Handle** Metric sizes. Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26307	.7	.028	40	1.6	120	4.7	.02	10
26309	.9	.035	40	1.6	120	4.7	.02	10
26313	1.3	.050	40	1.6	120	4.7	.02	10
26315	1.5	-	50	2.0	145	5.7	.03	10
26320	2.0	5/64	50	2.0	145	5.7	.03	10
26325	2.5	-	60	2.4	170	6.7	.04	10
26330	3.0	-	60	2.4	170	6.7	.04	10
26340	4.0	-	60	2.4	170	6.7	.05	10

*Metric dimensions actual - Inch dimensions approximate



26390 7pc Precision Hex Driver Set - Metric Blade high alloy chrome-vanadium-molybdenum steel.


Item No.	Hex Metric:	
26390	.7, .9, 1.3 x 40mm	lbs. .28
	1.5, 2.0 x 50mm	
	2.5, 3.0 x 60mm	



91118 Rugged Polyester Canvas Storage Pouch Holds 8 Precision Tools up to 170mm in length. Folding pouch. Has security flaps and velcro closer.

Item No.	Size	lbs.	pkg.
91118	14 1/2" W x 7 3/4" L	.13	1

Wiha Ball End Precision Series



264 Inch Ball End Hex Inch Screwdriver
With Precision Handle Angle entry up to 30°. Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finish.

Item	No.	Inch	mm	Inch	mm	Inch	lbs.	Pkg.
	26413	.050	40	1.6	120	4.7	.02	10
	26416	1/16	50	2.0	145	5.7	.03	10
	26419	5/64	50	2.0	145	5.7	.03	10
	26423	3/32	50	2.0	145	5.7	.03	10
	26427	7/64	60	2.4	170	6.7	.03	10
	26431	1/8	60	2.4	170	6.7	.05	10
	26436	9/64	60	2.4	170	6.7	.05	10
	26439	5/32	60	2.4	170	6.7	.05	10

*Metric dimensions actual - Inch dimensions approximate



264 Metric Ball End Hex Metric Screwdriver
With Precision Handle Angle entry up to 30°. Blade high alloy CVM steel.

Item	No.	mm	Inch	mm	Inch	mm	Inch	lbs.	Pkg.
	26413	1.3	.050	40	1.6	120	4.7	.02	10
	26415	1.5	-	50	2.0	145	5.7	.03	10
	26420	2.0	-	50	2.0	145	5.7	.03	10
	26425	2.5	-	60	2.4	170	6.7	.04	10
	26430	3.0	-	60	2.4	170	6.7	.05	10
	26440	4.0	-	60	2.4	170	6.7	.05	10

*Metric dimensions actual - Inch dimensions approximate



26490 8pc Ball End Hex Driver Set - Inch
 Angle entry up to 30°. Blade high alloy chrome-vanadium-molybdenum steel.

Item	No.	Hex Inch:	lbs.
	26490	1/16, 5/64, 3/32 x 2.0, 7/64, 1/8, 9/64, 5/32 x 2.4"	.40



26499 8pc Ball End Hex Driver Set - Inch
 Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished.

Item	No.	Ball End Hex Inch:	lbs.
	26499	1/16, 5/64, 3/32 x 2.0" 7/64, 1/8, 9/64, 5/32 x 2.4"	.62

Wiha TORX® Precision Series



26491 5 Piece Ball End Hex Driver Set - Metric
 Angle entry up to 30°. Blade high alloy chrome-vanadium-molybdenum-steel.

Item	No.	Ball End Hex Metric:	lbs.
	26491	1.3 x 40mm 1.5, 2.0 x 50mm 2.5, 3.0 x 60mm	.31



26792 7pc TORX® Screwdriver Set
 Blade high alloy chrome-vanadium-molybdenum steel.

Item	No.	TORX®:	lbs.
	26792	T5, T6, T7, T8 x 40mm T9, T10 x 50mm T15 x 60mm	.33

Wiha TORX® Precision Series



267 TORX® Screwdriver, With Precision Handle
 Blade high alloy chrome-vanadium-molybdenum steel.

Item	No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
	26701	T1	40	1.6	120	4.7	.01	10
	26702	T2	40	1.6	120	4.7	.02	10
	26703	T3	40	1.6	120	4.7	.02	10
	26704	T4	40	1.6	120	4.7	.02	10
	26705	T5	40	1.6	120	4.7	.02	10
	26706	T6	40	1.6	120	4.7	.02	10
	26707	T7	40	1.6	120	4.7	.02	10
	26708	T8	40	1.6	120	4.7	.03	10
	26709	T9	50	2.0	145	5.7	.03	10
	26710	T10	50	2.0	145	5.7	.03	10
	26715	T15	60	2.4	170	6.7	.05	10
	26720	T20	60	2.4	170	6.7	.05	10

*Metric dimensions actual - Inch dimensions approximate



26790 6pc TORX® Screwdriver Set
 Blade high alloy chrome-vanadium-molybdenum steel.

Item	No.	TORX®:	lbs.
	26790	T6, T7, T8 x 40mm T9, T10 x 50mm T15 x 60mm	.30

26791 Set 8pc TORX® Screwdriver Set

Item No.	T1, T2, T3, T4,
26791	T5, T6, T7, T8



26799 8pc TORX® Screwdriver Set
 Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished. In canvas storage pouch

Item	No.	TORX®:	lbs.
	26799	T3, T4, T5, T6, T7, T8 x 40mm T9 x T10 x 50mm	.50

Wiha Pentalobe Precision Series

Wiha Pentalobe drivers will fit fasteners used in "Apple" brand products including iPhone, Mac Book & Mac Air

- Exact fit precision machined tips
- High performance CRM72 tool steel
- Hard chromed finish blades & tips
- Tapered ergonomic handle
- Easy spin finger tip control cap



267 Pentalobe Screwdrivers, With Precision Handle Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
26761	PL1	40	1.6	120	4.7	.01	1
26762	PL2	40	1.6	120	4.7	.02	1
26763	PL3	40	1.6	120	4.7	.02	1
26764	PL4	40	1.6	120	4.7	.02	1
26765	PL5	40	1.6	120	4.7	.02	1
26766	PL6	40	1.6	120	4.7	.02	1

*Metric dimensions actual - Inch dimensions approximate (PL4 is used for Mac Book Pro)



26794 6 Pc. Precision Pentalobe Screwdriver Set Blade high alloy CVM steel. Hard chrome finished.

Item No.	Pentalobe Drivers:	lbs.
26794	PL1, PL2, PL3, PL4, PL5, PL6	.35



92191 51pc Precision Tool Tray Set Tool box tray. Equipped with 51 precision drivers.

Item No.	Slotted:	lbs.
92191	.8, 1.0, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0	4.63
	Phillips: #000, #00, #0, #1	
	Torx®: T1, T2, T3, T4, T5, T6, T7, T8, T9, T10	
	Metric Hex: 1.27, 1.5, 2.0, 2.5, 3.0, 4.0	
	Inch Hex: .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"	
	Metric Nut Drivers: 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5	
	26810 Chip Lifter	

Wiha Precision Screwdriver Sets



92189 Master Technicians Bench Top Set Metal frame. Equipped with 50 precision drivers.

Item No.	Slotted:	lbs.
92189	1.5, 2.0, 2.5, 3.0, 3.5, 4.0	3.67
	Phillips: #000, #00, #0, #1	
	Pentalobe: PL1, PL2, PL3, PL4	
	TORX®: T1, T2, T3, T4, T5, T6, T7, T8, T9, T10	
	Metric Hex: 1.27, 1.5, 2.0, 2.5, 3.0	
	Inch Hex: .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"	
	Metric Nut Drivers: 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5	
	26810 Chip Lifter	



92190 Master Technicians Bench Top Set Metal frame. Equipped with 50 precision drivers.

Item No.	Slotted:	lbs.
92190	.8, 1.0, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0	3.67
	Phillips: #000, #00, #0, #1	
	TORX®: T1, T2, T3, T4, T5, T6, T7, T8, T9, T10	
	Metric Hex: 1.27, 1.5, 2.0, 2.5, 3.0	
	Inch Hex: .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"	
	Metric Nut Drivers: 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5	
	26810 Chip Lifter	

Wiha Magnetizer/Demagnetizer

Magnetize or Demagnetize tools and small parts instantly

Shatterproof Box is made from high quality plastic

Uses 2 C8 industrial permanent magnets



(+) to Magnetize
(-) to Demagnetize

40010 Magnetizer and Demagnetizer

To magnetize and demagnetize steel screwdriver blades, tweezers and similar tools. Box high quality plastic, shock-resistant, green, cadmium free.

Application:

To magnetize, lead tool slowly through the (+) opening, to demagnetize guide tool slowly through the (-) opening.

Item No.	Dimensions	lbs.
40010	2.1" x 2.0" x 1.1"	.30

(Parts under 1" Length or 1/8" Diameter may not demagnetize)

NOTES:

Wiha Soft Grip PicoFinish Precision Screwdrivers

The Comfortable Precision Screwdriver

Soft Grip Handle

CVM tool steel blade, hardened, hard chrome finish

Ergonomic multi-component handle with rotating cap for maximum user comfort and precise control

Sets In Roll-Up Pouch



26195 5pc Precision Screwdrivers With Precision Soft PicoFinish Handle

Item No.	Slotted:	lbs.
26195	1.5, 2.5, 3.5mm	.25
26195	Phillips: #0, #1	.25

* No Pouch - In clamshell



260 Slotted Precision Screwdriver, With PicoFinish Handle

Blade CVM steel, hardened, hard chromed.

Item No.	mm	Inch	mm	Inch	mm	Inch	Pkg.
26050	0.8	.03	40	1.6	134	5.3	Pkg.
26051	1.0	.04	40	1.6	134	5.3	10
26052	1.2	.05	40	1.6	134	5.3	10
26053	1.5	.06	40	1.6	134	5.3	10
26055	1.8	.07	40	1.6	134	5.3	10
26056	1.8	.07	60	2.4	154	6.1	10
26060	2.0	.08	40	1.6	140	5.5	10
26061	2.0	.08	60	2.4	160	6.3	10
26065	2.5	.09	50	2.0	150	5.9	10
26066	2.5	.09	75	3.0	175	6.9	10
26068	2.5	.09	100	3.9	200	7.9	10
26070	3.0	.13	50	2.0	150	5.9	10
26072	3.0	.13	100	3.9	200	7.9	10
26073	3.0	.13	150	5.9	250	9.8	10
26074	3.5	.14	60	2.4	160	6.3	10
26076	4.0	.16	60	2.4	160	6.3	10
26079	4.0	.16	100	3.9	200	7.9	10
26080	4.0	.16	150	5.9	250	9.8	10

*Metric dimensions actual - Inch dimensions approximate



261 Phillips Precision Screwdriver, With Soft PicoFinish Precision Handle

Blade high alloy CVM steel. Hard chrome finished.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	Pkg.
26130	000	40	1.6	2.0	.08	134	5.3	10
26132	00	40	1.6	2.0	.08	134	5.3	10
26135	0	50	2.0	3.0	.12	150	5.9	10
26136	0	75	3.0	3.0	.12	175	6.9	10
26140	1	60	2.4	4.0	.16	160	6.3	10
26142	1	80	3.1	4.0	.16	180	7.1	10
26145	1	150	5.9	4.0	.16	250	9.8	10

*Metric dimensions actual - Inch dimensions approximate



26193 8pc Slotted & Phillips Precision Driver Set, With Soft PicoFinish Handle

Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit. In storage pouch

Item No.	Slotted:	lbs.
26193	1.0, 1.5, 2.0 x 40mm	.55
	2.5 x 50mm, 3.5 x 60mm	
	Phillips: 00 x 40mm	
	0 x 50mm, 1 x 60mm	



26093 8pc Slotted Precision Screwdriver Set, With Soft PicoFinish Handle

In storage pouch

Item No.	Slotted:	lbs.
26093	.8, 1.2, 1.5, 2.0 x 40mm	.54
	2.5, 3.0 x 50mm, 3.5, 4.0 x 60mm	



Ergonomic multi-component handle with rotating cap for maximum user comfort and precise control



267 MagicSpring Screw Holding TORX® Screwdriver, With Wiha-Precision Soft PicoFinish Handle

Blade high alloy CVM steel, hardened, hard chromed. Molded on ergonomic Wiha-PicoFinish precision handle, molded on, soft grips.

Item No.	Size	mm	Inch	mm	Inch	lbs.	Pkg.
26721	T6	40	1.6	140	5.5	.03	10
26723	T7	40	1.6	140	5.5	.03	10
26725	T8	40	1.6	140	5.5	.03	10
26727	T9	50	2.0	150	5.9	.04	10
26731	T15	60	2.4	160	6.3	.04	10

*Metric dimensions actual - Inch dimensions approximate



26798 6pc MagicSpring Screw Holding TORX® Screwdriver Set, With Wiha-Precision Soft PicoFinish Handle

Blade high alloy CVM steel, hardened, hard chromed. Molded on ergonomic Wiha-PicoFinish precision handle, molded on, soft grips. In storage pouch

Item No.	MagicSpring TORX®:	lbs.
26798	T6, T7, T8 x 40mm	.50
	T9, T10, T15 x 50mm	



Wiha Pico Soft Grip TORX®



267 TORX® Screwdriver, With Precision Soft PicoFinish Handle Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item	No.	Size	mm	Inch	mm	Inch	Pkg.
26732	T1	40	1.6	134	5.3	10	
26733	T2	40	1.6	134	5.3	10	
26735	T3	40	1.6	134	5.3	10	
26736	T4	40	1.6	134	5.3	10	
26737	T5	40	1.6	134	5.3	10	
26739	T6	40	1.6	140	5.5	10	
26741	T7	40	1.6	140	5.5	10	
26743	T8	40	1.6	140	5.5	10	
26745	T9	50	2.0	150	5.9	10	
26747	T10	50	2.0	150	5.9	10	
26749	T15	60	2.4	160	6.3	10	
26751	T20	60	2.4	160	6.3	10	

*Metric dimensions actual - Inch dimensions approximate

In storage pouch



26793 8pc TORX® Precision Driver Set, With Soft PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit.

Item	TORX®:	lbs.
No.	T1, T2, T3, T4,	
26793	T5, T6, T7, T8	.50

In storage pouch



26796 8pc TORX® Precision Driver Set, Soft PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit.

Item	TORX®:	lbs.
No.	T5, T6, T7, T8 x 40mm	.57
26796	T9, T10 x 50mm, T15, T20 x 60mm	

Pico Soft Grip Hex Inch & Metric



263 Hex Inch Screwdriver, With Precision Soft PicoFinish Handle Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item	No.	Inch	mm	Inch	mm	Inch	Pkg.
26341		.028(0.7)	40	1.6	134	5.3	10
26343		.035(0.9)	40	1.6	134	5.3	10
26345		.050(1.3)	40	1.6	134	5.3	10
26349		5/64(2.0)	50	2.0	150	5.9	10
26363		1/16	50	2.0	144	5.7	10
26367		3/32	60	2.4	160	6.3	10
26369		7/64	60	2.4	160	6.3	10
26371		1/8	60	2.4	160	6.3	10

*Metric dimensions actual - Inch dimensions approximate



26392 8pc Hex Inch Precision Driver Set, Soft PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed.

Item	Hex Inch:	lbs.
No.	.028, .035, .050 x 1.6"	.24
26392	5/64, 1/16 x 2.0", 3/32, 7/64, 1/8 x 2.4"	



263 Hex Metric Driver, With Precision Soft PicoFinish Handle

Item	No.	mm	mm	Inch	mm	Inch	Pkg.
26341		.7(.028)	40	1.6	134	5.3	10
26343		.9(.035)	40	1.6	134	5.3	10
26345		1.3(.050)	40	1.6	134	5.3	10
26347		1.5	50	2.0	144	5.7	10
26349		2.0(5/64)	50	2.0	150	5.9	10
26351		2.5	60	2.4	160	6.3	10
26353		3.0	60	2.4	160	6.3	10

*Metric dimensions actual - Inch dimensions approximate



26393 7pc Hex Metric Precision Driver Set, Soft PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed.

Item No.	Hex Metric:	lbs.
26393	.71, .89, 1.27 x 40mm	.22
	1.5, 2.0 x 50mm, 2.5, 3.0 x 60mm	

Pico Soft Grip Ball End Inch & Metric



264 Ball End Hex Inch Screwdriver, With Precision Soft PicoFinish Handle Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item	No.	Inch	Inch	mm	Inch	mm	pkg.
26455		1/16	2.0	50	5.9	150	10
26457		5/64	2.0	50	5.9	150	10
26459		3/32	2.0	50	5.9	150	10
26461		7/64	2.4	60	6.3	160	10
26463		1/8	2.4	60	6.3	160	10
26465		9/64	2.4	60	6.3	160	10
26467		5/32	2.4	60	6.3	160	10

*Metric dimensions actual - Inch dimensions approximate



26493 7pc Inch Ball End Hex Precision Driver Set, With Soft PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit. In storage pouch

Item	Ball End Hex Inch:	lbs.
No.	.27	
26493	1/16, 5/64, 3/32 x 2.0"	
	7/64, 1/8, 9/64, 5/32 x 2.4"	



264 Ball End Hex Metric Screwdriver, With Precision Soft PicoFinish Handle. Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item	No.	mm	mm	Inch	mm	Inch	pkg.
26441		1.3	40	1.6	134	5.3	10
26443		1.5	50	2.0	150	5.9	10
26445		2.0	50	2.0	150	5.9	10
26447		2.5	60	2.4	160	6.3	10
26449		3.0	60	2.4	160	6.3	10

*Metric dimensions actual - Inch dimensions approximate

Pico Soft Grip Tri-Wing

Tri-Wing

(Used in iPhone 7 or higher series)



266 Tri-Wing Precision Screwdriver, With Soft PicoFinish Precision Handle Blade high alloy CVM steel. Hard chrome finished.

Item	Size	mm	Inch	mm	Inch	mm	Inch
26631	000	40	1.6	2.0	.08	140	5.5

PicoFinish® Soft Grip Set



26196 5pc Precision Screwdrivers With Precision Soft PicoFinish Handle

Item	Phillips: #0, #1	lbs.
No.	Pentalobe: PL1	.25
26196 Tri-Wing: #000		
Tweezers: 2a SA ESD Flat Round Tip		

* No Pouch - In clamshell

PicoFinish Soft Grip Nut Drivers



265 Inch Nut Drivers, With Precision Soft PicoFinish Handle Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item	Inch	Inch	Inch	Inch	pkg.
26571	3/32	2.4	6.3	.71	10
26572	7/64	2.4	6.3	.71	10
26573	1/8	2.4	6.3	.71	10
26574	9/64	2.4	6.3	.71	10
26575	5/32	2.4	6.3	.71	10
26576	3/16	2.4	6.3	.71	10
26577	7/32	2.4	6.3	.71	10
26578	1/4	2.4	6.3	.71	10

*Metric dimensions actual - Inch dimensions approximate

Pico Soft Grip Pentalobe



267 Pentalobe Screwdriver, With Precision Soft PicoFinish Handle Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item	Size	Inch	mm	Inch	mm	pkg.
26771	PL1	1.6	40	5.5	140	10
26772	PL2	1.6	40	5.5	140	10
26773	PL3	1.6	40	5.5	140	10
26774	PL4	1.6	40	5.5	140	10
26775	PL5	1.6	40	5.5	140	10
26776	PL6	1.6	40	5.5	140	10

*Metric dimensions actual - Inch dimensions approximate

Pico Soft Grip Precision Chip Lifter



26815 Soft PicoFinish Precision Chip Lifter Blade CVM steel, hardened, hard chromed.

Item	mm	mm	mm	mm	Inch
No.	1	3.5	50	150	5.9
26815	Standard Soft PicoFinish handle				

NOTES:



26795 6pc Precision Pentalobe Driver Set, Soft PicoFinish Handle Blade high alloy CVM steel. Hard chrome finished.

Item No.	Pentalobe Drivers:	lbs.
26795	PL1, PL2, PL3, PL4, PL5, PL6	.40



265 Metric Nut Drivers, With Precision PicoFinish Handle Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item	mm	mm	mm	mm	mm	mm	pkg.
26579	1.5	60	160	2.5	3.0	18	10
26581	2.0	60	160	3.2	4.0	18	10
26582	2.5	60	160	4.0	4.0	18	10
26583	3.0	60	160	5.0	5.0	18	10
26584	3.5	60	160	5.3	6.0	18	10
26585	4.0	60	160	5.5	6.0	18	10
26586	4.5	60	160	6.2	7.0	18	10
26587	5.0	60	160	6.8	7.0	18	10
26588	5.5	60	160	7.6	8.0	18	10
26589	6.0	60	160	8.2	9.0	18	10

*Metric dimensions actual - Inch dimensions approximate



26593 8 Piece Inch Nut Driver Set, With Precision Soft PicoFinish Handle

Item	Inch Nut Drivers:	lbs.
No.	3/32, 7/64, 1/8, 9/64,	lbs.
26593	5/32, 3/16, 7/32, 1/4" x 2.4"	.72






26596 8pc Metric Nut Driver Set, With Precision Soft PicoFinish Handle

Item	Metric Nut Drivers:	lbs.
No.	2.0, 2.5, 3.0, 3.5, 4.0,	lbs.
26596	4.5, 5.0, 5.5 x 60mm	.66

Wiha SYSTEM 4 Precision Handles and Blades








26900 SYS 4 Standard Precision Handle, with rotating control cap. Accepts all SYSTEM 4 interchangeable blades. Wiha Precision handle, tapered, impact resistant. Ball retainer hold. 110mm/4.3" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
26900	4.0	.1574	14.0	.55	.04



28000 ESD Safe Dissipative Precision Handle with rotating control cap. Surface resistant 10⁶-10⁹ Ohms. 4 mm hex retainer for all SYSTEM 4 interchangeable blades. Tapered handle, high quality plastic, impact resistant. Ball retainer hold. 110mm/4.3" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
28000	4.0	.1574	14.0	.55	.04

Rotating Cap for precise turning and control




Tapered Handle allows rapid rotation, requires less clearance

Precision Handle high quality plastic. ESD Safe or Standard styles






Tips Exact fit, precision machined


Blades CVM steel, hardened, hard chromed. On 4mm Hex shafts



269 SYSTEM 4 Metric Ball End & Standard Hex, Reversible Blade






CVM steel, hardened, hard chromed. Wiha vapor Chrome-Top finish on tips. One side hex, other side ballpoint hex.


Item					
No.	mm	mm	mm	Inch	lbs.
26932	1.3 + 1.3	120	4.7	.05	
26935	2.5 + 2.5	120	4.7	.06	
26936	3.0 + 3.0	120	4.7	.06	
26937	4.0 + 4.0	120	4.7	.06	



280 SYSTEM 4 Metric Ball End Hex Interchangeable Blade





High alloy tool steel, hardened, corrosion protected. Ball end works at 30° angle entry for easy access to fasteners.

Item					
No.	mm	mm	Inch	lbs.	pkg.
28033	1.5	120	4.7	.06	1
28034	2.0	120	4.7	.06	1
28035	2.5	120	4.7	.06	1
28036	3.0	120	4.7	.06	1
28037	4.0	120	4.7	.06	1








280 SYSTEM 4 Inch Ball End Hex Interchangeable Blade

High alloy tool steel, hardened, corrosion protected. Ball end works at 30° angle entry for easy access to fasteners.

Item				
No.	Inch	mm	Inch	lbs.
28021	.050	120	4.7	.06
28023	1/16	120	4.7	.06
28024	5/64	120	4.7	.06
28026	7/64	120	4.7	.06
28027	1/8	120	4.7	.06
28028	9/64	120	4.7	.06
28029	5/32	120	4.7	.06








269 SYSTEM 4 Slotted Reversible Blade High alloy CVM steel, hardened, hard chromed. Wiha vapor Chrome-Top finish on tips.

Item					
No.	mm	mm	mm	Inch	lbs.
26903	1.5 + 3.0	120	4.7	.05	
26904	2.0 + 3.5	120	4.7	.05	
26905	2.5 + 4.0	120	4.7	.06	








269 SYSTEM 4 Combined Slotted/Phillips Reversible Blade

Item					
No.	mm	Size	mm	Inch	lbs.
26971	1.5 + 000	120	4.7	.05	
26972	2.0 + 00	120	4.7	.05	
26973	3.0 + 0	120	4.7	.05	
26974	4.0 + 1	120	4.7	.06	








269 SYSTEM 4 Phillips Reversible Blade High alloy CVM steel, hardened, hard chromed. Wiha vapor Chrome-Top finish on tips.

Item					
No.	Size	Size	mm	Inch	lbs.
26911	000 + 00	120	4.7	.03	
26912	0 + 1	120	4.7	.03	



269 SYSTEM 4 Pozidriv® Reversible Blade High alloy CVM steel, hardened, hard chromed. Wiha vapor Chrome-Top finish on tips.

Item					
No.	Size	Size	mm	Inch	lbs.
26922	0 + 1	120	4.7	.03	

Wiha SYSTEM 4 Precision Blades



269 SYSTEM 4 Metric Hex Sizes, Interchangeable Blade High alloy CVM steel, hardened, corrosion protected.

Item				
No.	mm	mm	Inch	lbs.
26914	0.9	120	4.7	.06
26916	1.5	120	4.7	.06
26917	2.0	120	4.7	.06
26918	2.5	120	4.7	.06
26919	3.0	120	4.7	.06
26920	4.0	120	4.7	.06



269 SYSTEM 4 Inch Hex Sizes, Interchangeable Blade High alloy CVM steel, hardened, corrosion protected.

Item				
No.	Inch	mm	Inch	lbs.
26921	.050	120	4.7	.06
26923	1/16	120	4.7	.06
26924	5/64	120	4.7	.06
26925	3/32	120	4.7	.06
26926	7/64	120	4.7	.06
26927	1/8	120	4.7	.06
26928	9/64	120	4.7	.06
26929	5/32	120	4.7	.06



269 SYSTEM 4 TORX® Reversible Blade High alloy CVM steel, hardened, vapor chrome protected, Wiha vapor Chrome-Top finish on tips. 120mm/4.7" OAL.

Item			
No.	Size	Size	lbs.
26951	T6 + T8		.03
26952	T7 + T9		.03
26953	T10 + T15		.03
26954	T15 + T20		.03



269 SYSTEM 4 TORX® Interchangeable Blade High alloy CVM steel, hardened, Wiha vapor Chrome-Top finish on tips. 120mm/4.7" OAL

Item		
No.	Size	lbs.
26955	T3	.03
26956	T4	.03
26957	T5	.03

Wiha SYSTEM 4 Drive-Loc Precision Locking Tools

Blade lengths can be adjusted from 18mm (.7") to 90mm (3.5") Max. In 3mm increments



26906 SoftFinish® Cushion Grip Drive-Loc Handle 4 mm hex retainer for all SYSTEM 4 interchangeable blades. Ball retainer hold. 105mm/4.13" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
26906	4.0	.1574	23	.91	.08



26961 ESD Safe Dissipative Precision Drive-Loc Handle Surface resistant 10⁶-10⁹ Ohms. 4 mm hex retainer for all SYSTEM 4 interchangeable blades. Ball retainer hold. 105mm/4.13" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
26961	4.0	.1574	23	.91	.08



269 SYSTEM 4 Slotted Drive-Loc Reversible Locking Blades On 4mm Hex

Item			
No.	mm	mm	lbs.
26958	1.5 + 3.0		.02
26959	2.0 + 3.5		.02
26960	2.5 + 4.0		.02



269 SYSTEM 4 Phillips Drive-Loc Reversible Locking Blades On 4mm Hex

Item			
No.	Size	Size	lbs.
26975	000 + 00		.02
26976	0 + 1		.02



269 SYSTEM 4 TORX® Drive-Loc Reversible Locking Blades On 4mm Hex

Item			
No.	Size	Size	lbs.
26977	T1 + T2		.02
26978	T3 + T4		.02
26979	T5 + T6		.02
26980	T6 + T8		.02
26981	T7 + T9		.02
26982	T10 + T15		.02
26983	T15 + T20		.02



280 SYSTEM 4 Pozidriv® Drive-Loc Reversible Locking Blades On 4mm Hex

Item			
No.	Size	Size	lbs.
28002	0 + 1		.02



280 SYSTEM 4 Metric Ball End Hex & Hex Metric Drive-Loc Reversible Locking Blades On 4mm Hex blades

Item			
No.	mm	mm	lbs.
28003	1.3 + 1.3		.02
28004	1.5 + 1.5		.02
28005	2.0 + 2.0		.02
28006	2.5 + 2.5		.02
28007	3.0 + 3.0		.02
28008	4.0 + 4.0		.02



280 SYSTEM 4 Metric Nut Drivers Drive-Loc Locking Blades On 4mm Hex blades

Item			
No.	mm	mm	lbs.
28012	3.2 + -		.02
28015	4.5 + -		.02
28016	5.0 + -		.02

Wiha Drive-Loc IV Precision Locking Tools



26985 12pc Precision ESD Safe Drive-Loc IV Set In storage pouch

Item No. **26985 ESD Safe Drive-Loc Handle**

Slotted: 1.5x3.0, 2.0x3.5, 2.5x4.0

lbs. .44 **Phillips:** 000x00, 0x1

TORX®: T1xT2, T3xT4, T5xT6, T6xT8, T7xT9, T10xT15



26930 7pc Drive-Loc IV TORX® Precision ESD Safe Set In storage pouch

Item No. **26930 ESD Safe Drive-Loc Handle**

TORX®: T3xT4, T5xT6, T6xT8, T7xT9, T10xT15, T15xT20

lbs. .56

Rotating Cap
for precise turning and control

Tapered Handle
allows rapid rotation, requires less clearance

Precision Handle
high quality plastic, cadmium free. ESD Safe or Standard styles

Blades
CVM steel, hardened, hard chromed

Tips
Exact fit, precision machined

15mm
Collet Lock Handle adjustable blade length from 15 to 95mm/.6" to 3.75"
95mm



26970 12pc Precision ESD Safe Drive-Loc IV and Tweezers Set

Item No. **26970 ESD Safe Drive-Loc Handle**

Slotted: 2.0x3.5, 2.5x4.0

lbs. .59 **Phillips:** 000x00, 0x1

TORX®: T6xT8, T7xT9, T10xT15

44501 Fine Point - AA SA

44509 Extra Fine Point - 5 SA

44505 Flat and Blunt - 2a SA

44510 Curved Fine Point - 7a SA



26984 9pc Precision Drive-Loc IV Interchangeable Blade Set

Item No. **26984 SoftFinish® Drive-Loc Handle**

Slotted: 1.5x3.0, 2.0x3.5, 2.5x4.0

lbs. .47 **Phillips:** 000x00, 0x1

TORX®: T6xT8, T7xT9, T10xT15

269 SYSTEM 4 Nut Driver Inch, Interchangeable Blade High alloy CVM steel, hardened, corrosion protected. On 4mm Hex shaft. 120mm/4.7" OAL

Item No.	Inch	Inch	Inch	lbs.
26962	3/32	.16	.16	.04
26963	7/64	.20	.20	.04
26964	1/8	.20	.20	.04
26965	9/64	.21	.24	.04
26966	5/32	.22	.24	.04
26968	7/32	.30	.32	.04
26969	1/4	1.34	.36	.04



26994 9pc Precision ESD Safe Drive-Loc IV Interchangeable Blade Set

Item No. **26994 ESD Safe Drive-Loc Handle**

Slotted: 1.5x3.0, 2.0x3.5, 2.5x4.0

lbs. .47 **Phillips:** 000x00, 0x1

TORX®: T6xT8, T7xT9, T10xT15

Precision Interchangeable Blade Sets In Metal Box



26987 8pc TORX® Precision Blade Set
Wiha ESD Safe precision collet lock handle and 7 interchangeable blades.

26987 Set includes the following blades:

- TORX® standard blades:** T3, T4, T5
- TORX® reversible blades:** T6, T7, T8, T9, T10, T15, T20

lbs. .62

269 SYSTEM 4 Nut Driver Metric, Interchangeable Blade High alloy CVM steel, hardened, corrosion protected. On 4mm Hex Shaft. 120mm/4.7" OAL

Item No.	mm	mm	Inch	Inch	lbs.
26940	1.5 + 1.8	.12	.12	.03	
26941	2.0 + 2.5	.16	.16	.03	
26938	1.5 -	.11	.11	.04	
26939	1.8 -	.12	.12	.04	
26949	2.0 -	.13	.13	.06	
26950	2.5 -	.16	.16	.06	
26942	3.0 -	.20	.20	.06	
26943	3.2 -	.20	.20	.06	
26944	3.5 -	.22	.24	.06	
26945	4.0 -	.22	.24	.06	
26946	4.5 -	.25	.28	.06	
26947	5.0 -	.27	.28	.06	
26948	5.5 -	.30	.32	.06	

Wiha SoftFinish® Handle - Ergonomic Cushion Grip

Handle is molded directly onto the blade for a permanent bond



Wiha SoftFinish® Handle: Featuring advanced technology dual material molding. A remarkable improvement in handle design, comfort and performance. The SoftFinish® ergonomic shape allows maximum torque and user comfort.

Wiha Nut Drivers are precision formed to exact tolerances for a perfect fit every time

All blades are made of Wiha's exclusive formula chrome-vanadium-molybdenum tool steel, super hardened plated for unmatched durability



341 Nut Driver, With Wiha-SoftFinish® Handle Inch sizes. Blade CVM steel, hardened. Deep drawn 1" socket. Solid shafts. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item No.	⊙	⊞	⊞	⊞	⊞	⊞	⊞	⊞	⊞	⊞
No.	Inch	Inch	mm	mm	Inch	Inch	mm	lbs.	pkg.	
34134	9/64	5.0	125	238	9.4	1.18	30	.18	10	
34135	5/32	5.0	125	238	9.4	1.18	30	.24	10	
34136	3/16	5.0	125	238	9.4	1.18	30	.25	10	
34137	7/32	5.0	125	238	9.4	1.18	30	.26	10	
34138	1/4	5.0	125	246	9.7	1.42	36	.38	10	
34139	5/16	5.0	125	246	9.7	1.42	36	.40	10	
34140	11/32	5.0	125	246	9.7	1.42	36	.40	10	
34141	3/8	5.0	125	246	9.7	1.42	36	.40	10	
34142	7/16	5.0	125	246	9.7	1.61	41	.40	10	
34143	1/2	5.0	125	246	9.7	1.61	41	.40	10	
34144	9/16	5.0	125	246	9.7	1.61	41	.40	10	
34145	5/8	5.0	125	246	9.7	1.61	41	.40	10	

341 Nut Driver, With Wiha-SoftFinish® Handle Metric sizes

Item No.	⊙	⊞	⊞	⊞	⊞	⊞	⊞	⊞	⊞
No.	mm	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
34120	5.0	125	5.0	238	9.4	30	1.18	.14	10
34121	5.5	125	5.0	238	9.4	30	1.18	.14	10
34122	6.0	125	5.0	238	9.4	30	1.18	.15	10
34123	7.0	125	5.0	238	9.4	36	1.42	.25	10
34124	8.0	125	5.0	238	9.4	36	1.42	.25	10
34126	10.0	125	5.0	238	9.4	36	1.42	.27	10
34127	11.0	125	5.0	247	9.7	41	1.61	.37	10
34128	12.0	125	5.0	247	9.7	41	1.61	.40	10
34129	13.0	125	5.0	247	9.7	41	1.61	.40	10
34130	14.0	125	5.0	247	9.7	41	1.61	.40	10
34131	15.0	125	5.0	247	9.7	41	1.61	.40	10
34132	16.0	125	5.0	249	9.8	41	1.61	.42	10
34133	17.0	125	5.0	249	9.8	41	1.61	.42	10

341 Magnetic Nut Driver, With Wiha-SoftFinish® Handle

Item No.	⊙	⊞	⊞	⊞	⊞	⊞	⊞
No.	mm	mm	Inch	mm	Inch	lbs.	pkg.
34152	5.5	125	5.0	238	9.4	.14	10
34154	5.5	250	9.8	361	14.2	.21	10



34193 7pc Nut Driver Set Inch sizes.

Blade CVM steel, hardened. Deep drawn 1" socket.

Item No.	⊙	⊞	⊞	⊞	⊞
No.	Inch	Inch	Inch	Inch	lbs.
34193	3/16	5.0	3/8	5.0	1.89
	1/4	5.0	7/16	5.0	
	5/16	5.0	1/2	5.0	
	11/32	5.0			



34195 10pc Nut Driver Set Inch sizes

Blade CVM steel, hardened. Deep drawn 1" socket.

Item No.	⊙	⊞	⊞	⊞	⊞
No.	Inch	Inch	Inch	Inch	lbs.
34195	3/16	5.0	3/8	5.0	3.12
	7/32	5.0	7/16	5.0	
	1/4	5.0	1/2	5.0	
	5/16	5.0	9/16	5.0	
	11/32	5.0	5/8	5.0	



34194 7pc Nut Driver Set Metric sizes

Blade CVM steel, hardened. Deep drawn 1" socket.

Item No.	⊙	⊞	⊞	⊞	⊞
No.	mm	mm	mm	mm	lbs.
34194	5.0	125	8.0	125	1.93
	5.5	125	10.0	125	
	6.0	125	13.0	125	
	7.0	125			

Wiha SoftFinish® Heavy Duty Nut Drivers



347 Nut Driver, With Hex Bolster & Wiha-SoftFinish® Handle

Blade CVM steel, hardened. Deep drawn 1" socket. Hex bolster for additional torque, Solid shafts. Wiha-SoftFinish® cushion grip handle.

Item No.	mm	mm	Inch	mm	mm	Inch	mm	Inch	lbs.	pkg.
34712	7.0	125	5.0	10.0	238	9.4	36	1.42	.25	10
34715	8.0	125	5.0	10.0	238	9.4	36	1.42	.25	10
34718	9.0	125	5.0	10.0	238	9.4	36	1.42	.26	10
34721	10.0	125	5.0	10.0	238	9.4	36	1.42	.27	10
34724	11.0	125	5.0	13.0	247	9.7	41	1.61	.37	10
34727	12.0	125	5.0	13.0	247	9.7	41	1.61	.40	10
34730	13.0	125	5.0	13.0	247	9.7	41	1.61	.40	10



34791 5pc Nut Driver Set Metric sizes

Item No.	mm	mm	mm	mm	lbs.
34791	5.0*	125	10.0	125	1.42
	6.0*	125	11.0	125	
	8.0	125			

*Standard blade - no hex bolster



34792 6pc Nut Driver Set Inch sizes

Item No.	Inch	Inch	Inch	Inch	lbs.
34792	3/16	5.0	3/8	5.0	1.94
	1/4	5.0	7/16	5.0	
	5/16	5.0	1/2	5.0	



347 Nut Driver, Hex Bolster & Wiha-SoftFinish® Handle Inch sizes

Item No.	Inch	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
34753	3/16	5.0	125	5/16	231	9.1	36	1.42	.18	10
34759	1/4	5.0	125	3/8	238	9.4	36	1.42	.24	10
34765	5/16	5.0	125	3/8	238	9.4	36	1.42	.25	10
34771	3/8	5.0	125	3/8	238	9.4	36	1.42	.26	10
34774	7/16	5.0	125	1/2	246	9.7	41	1.61	.38	10
34777	1/2	5.0	125	1/2	246	9.7	41	1.61	.40	10

Wiha SoftFinish® Metric Nut Drivers - Hollow Shaft

- Hollow shafts allow for fit over extended bolts
- Finally a handle that makes Nut Drivers useful
- Get 40% more power with SoftFinish cushion grip
- Soft ergonomic molded shape for maximum comfort
- Hardened for maximum torque and wear resistance
- Heavy duty hollow shaft - 3.7" depth
- Chrome plated anti corrosion finish



343 Hollow Shaft Nut Driver With Wiha-SoftFinish® Handle Metric

Item No.	mm	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
34302	5.0	70	2.75	175	7.0	36	1.42	.14	10
34304	5.5	70	2.75	175	7.0	36	1.42	.14	10
34306	6.0	70	2.75	175	7.0	36	1.42	.15	10
34308	7.0	70	2.75	182	7.5	41	1.61	.25	10
34310	8.0	70	2.75	182	7.5	41	1.61	.25	10
34312	10.0	70	2.75	187	7.6	41	1.61	.27	10
34314	13.0	70	2.75	187	7.6	41	1.61	.40	10



34391 7pc Hollow Shaft Nut Driver Set

Item No.	mm	mm	mm	mm	lbs.
34391	5.0	70	8.0	70	1.41
	5.5	70	10.0	70	
	6.0	70	13.0	70	
	7.0	70			

Long Flexible Shaft Nut Drivers, SoftFinish® Handle - Ergonomic Cushion Grip



372 Long Flexible Shaft Nut Driver, With Wiha-SoftFinish® Handle Inch sizes. Heavy Duty flexible shaft of braided steel with protective sleeve. Hardened mounted socket for optimal torque. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item No.	⊙	⊖	⊖	⊖	⊖	⊖	⊖	⊖	⊖
	Inch	Inch	mm	mm	Inch	mm	Inch	lbs.	pkg.
37220	3/16	5.9	150	261	10.2	30	1.18	.30	1
37222	1/4	5.9	150	261	10.2	36	1.42	.42	1
37226	3/8	6.9	175	261	10.2	36	1.42	.44	1
37228	7/16	6.9	175	261	10.2	41	1.61	.44	1
37230	1/2	6.9	175	261	10.2	41	1.61	.44	1



372 Long Flexible Shaft Nut Driver, With Wiha-SoftFinish® Handle Metric sizes. Heavy Duty flexible shaft of braided steel with protective sleeve. Hardened mounted socket for optimal torque. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item No.	⊙	⊖	⊖	⊖	⊖	⊖	⊖	⊖	⊖
	mm	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
37235	5.0	150	5.9	261	10.2	30	1.18	.16	1
37236	5.5	150	5.9	261	10.2	30	1.18	.16	1
37237	6.0	150	5.9	261	10.2	30	1.18	.17	1
37238	7.0	150	5.9	261	10.2	36	1.42	.28	1
37239	8.0	150	5.9	261	10.2	36	1.42	.28	1
37241	10.0	175	6.9	261	10.2	41	1.61	.44	1
37244	13.0	175	6.9	261	10.2	41	1.61	.44	1



37291 7pc Flexible Shaft Nut Driver Set, Metric Sizes

Item No.	⊙	⊖	⊖	⊖	⊖
	mm	mm	mm	mm	lbs.
37291	5.0	150	8.0	150	1.93
	5.5	150	10.0	175	
	6.0	150	13.0	175	
	7.0	150			

Wiha SoftFinish® Inch Nut Drivers - Hollow Shaft



343 Hollow Shaft Nut Driver-Wiha-SoftFinish® Handle Inch sizes

Item No.	⊙	⊖	⊖	⊖	⊖	⊖	⊖	⊖	⊖
	Inch	Inch	mm	mm	Inch	mm	Inch	lbs.	pkg.
34336	3/16	2.75	70	175	7.0	30	1.18	.18	10
34338	1/4	2.75	70	175	7.0	30	1.18	.24	10
34339	5/16	2.75	70	175	7.0	36	1.42	.25	10
34340	11/32	2.75	70	182	7.5	36	1.42	.25	10
34341	3/8	2.75	70	182	7.5	36	1.42	.26	10
34342	7/16	2.75	70	187	7.6	41	1.61	.38	10
34343	1/2	2.75	70	187	7.6	41	1.61	.40	10



34390 7pc Hollow Shaft Nut Driver Set Inch Sizes

Item No.	⊙	⊖	⊖	⊖	⊖
	Inch	Inch	Inch	Inch	lbs.
34390	3/16	2.75	3/8	2.75	1.55
	1/4	2.75	7/16	2.75	
	5/16	2.75	1/2	2.75	
	11/32	2.75			















Inch Color Coded To Size


Wiha SoftFinish® Triangle Nut Drivers



344 Triangle Nut Driver, With Wiha-SoftFinish® Handle

Blade Chrome-vanadium-molybdenum steel, hardened. Wiha-SoftFinish® cushion grip handle.

Item												
No.	Size	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.	
34474	M4	6.8	.267	125	5"	236	9.3	30	1.18	.17	10	
34475	M5	8.3	.326	125	5"	236	9.3	30	1.18	.19	10	
34476	M6	10.1	.413	125	5"	236	9.3	30	1.18	.21	10	
34478	M8	12.1	.474	125	5"	243	9.6	36	1.42	.23	10	
34482	M12	16.1	.651	125	5"	243	9.6	41	1.61	.27	10	














Wiha T-Handle Nut Drivers



336 Nut Driver, With Wiha T-handle Blade CVM steel, hardened, nickel-plated.






Wiha T-handle high quality plastic, impact resistant. Deep drawn 1" socket, solid shaft.

Item											
No.	Inch	Inch	mm	Inch	mm	Inch	mm	lbs.	pkg.		
33653	3/16	6.0	150	7.2	182	4.0	100	.16	10		
33659	1/4	6.0	150	7.2	182	4.0	100	.18	10		
33665	5/16	6.0	150	7.2	182	4.0	100	.19	10		
33671	3/8	6.0	150	7.2	182	4.0	100	.20	10		
33674	7/16	6.0	150	7.2	182	4.0	100	.26	10		
33677	1/2	6.0	150	7.2	182	4.0	100	.30	10		



33690 6pc Nut Driver T-handle Set






Inch Sizes. Blade CVM steel, hardened, nickel-plated. Wiha T-handle high quality plastic, impact resistant. Deep drawn 1" socket, solid shaft.

Item					
No.	Inch	Inch	Inch	Inch	lbs.
33690	3/16	6.0	3/8	6.0	1.61
	1/4	6.0	7/16	6.0	
	5/16	6.0	1/2	6.0	



33691 5pc Nut Driver T-handle Set












Metric Sizes. Blade CVM steel, hardened, nickel-plated. Wiha T-handle high quality plastic, impact resistant. Deep drawn 1" socket, solid shaft.

Item					
No.	mm	mm	mm	mm	lbs.
33691	6.0	125	10.0	125	1.57
	8.0	125	13.0	125	
	9.0	125			



336 Nut Driver, With Wiha T-handle Blade CVM steel, hardened, nickel-plated. Wiha

T-handle high quality plastic, impact resistant. Deep drawn 1" socket, solid shaft.

Item											
No.	mm	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.		
33603	6.0	125	4.9	157	6.2	100	4.0	.16	10		
33606	8.0	125	4.9	157	6.2	100	4.0	.18	10		
33607	8.0	200	7.9	232	9.1	100	4.0	.22	10		
33609	9.0	125	4.9	157	6.2	100	4.0	.23	10		
33612	10.0	125	4.9	157	6.2	100	4.0	.24	10		
33614	10.0	230	9.0	262	10.3	100	4.0	.26	10		
33620	12.0	125	4.9	157	6.2	100	4.0	.26	10		
33622	13.0	125	4.9	157	6.2	100	4.0	.27	10		
33623	13.0	230	9.0	262	10.3	100	4.0	.30	10		

Wiha Drive-Loc VI Nut Drivers




Locking mechanism in Wiha SoftFinish® cushion grip ergonomic handle. Blade length can be adjusted from 40mm-120mm. (1.7 to 4.7" In 1/8" increments)

See Drive-Loc VI Handles & Screwdrivers on pages 17-18

Drive-Loc VI

For Adjustable Length Locking Blades



The blade length can be adjusted from 40mm-120mm. (1.7 to 4.7")



281 Drive-Loc VI Inch Nut Driver Blades

High alloy CVM steel, through hardened, hard chrome finish. OAL blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item No.	Inch	OAL	lbs.	pkg.
28156	3/16	5.9"	.11	1
28157	7/32	5.9"	.11	1
28158	1/4	5.9"	.11	1
28159	9/32	5.9"	.12	1
28160	5/16	5.9"	.13	1
28161	11/32	5.9"	.14	1
28162	3/8	5.9"	.15	1
28163	7/16	5.9"	.17	1
28164	1/2	5.9"	.18	1



281 Drive-Loc VI Metric Nut Driver Blades

High alloy CVM steel, through hardened, hard chrome finish. OAL blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item No.	mm	OAL	lbs.	pkg.
28168	4.0	150mm	.10	1
28169	4.5	150mm	.10	1
28170	5.0	150mm	.11	1
28171	5.5	150mm	.11	1
28172	6.0	150mm	.12	1
28173	7.0	150mm	.13	1
28174	8.0	150mm	.13	1
28177	9.0	150mm	.14	1
28175	10.0	150mm	.15	1
28176	11.0	150mm	.20	1



28196 8pc Drive-Loc VI Interchangeable Blade Set, In Durable Pouch

Set includes Drive-Loc VI handle & 7 Inch Nut Driver blades.

Item No.	lbs.
28196	1.22

Inch: 3/16, 1/4, 5/16, 11/32, 3/8, 7/16, 1/2"
SoftFinish® Cushion Grip Blade Lock Handle



28198 8pc Drive-Loc VI Interchangeable Blade Set, In Durable Pouch

Set includes Drive-Loc VI handle & 7 Metric Nut Driver blades.

Item No.	lbs.
28198	1.00

Metric: 5.0, 5.5, 6.0, 7.0, 8.0, 9.0, 10.0mm
SoftFinish® Cushion Grip Blade Lock Handle



28144 Extension Blade For Drive-Loc VI Blades High alloy CVM steel, through hardened, hard chrome finish. OAL blade length 6.5". Blades fit all Drive-Loc VI handles.

Item No.	mm	OAL	lbs.	pkg.
28144	6.0	150mm	.14	1

Wiha Power Blade Nut Drivers - 100mm



76000 CentroFix Cushion Grip Blade Holder

Wiha-SoftFinish® impact resistant, with roll off protection. Ergonomic cushion grip handle. Quick release bit holder with magnet.

Item No.	mm	mm	Inch	mm	Inch	lbs.
76000	6.0	149	5.9	34.6	1.36	.26



76085 9pc Power Blade Nut Driver Set

30mm deep drilled Nut drivers. Use with #76000 CentroFix Blade Holder. 100mm OAL

Item No.	lbs.
76085	.96

Inch: 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2"



76086 12pc Power Blade Nut Driver Set

30mm deep drilled Nut drivers. Use with #76000 CentroFix Blade Holder. 100mm OAL

Item No.	lbs.
76086	1.22

Metric: 4.0, 4.5, 5.0, 5.5, 6.0, 7.0, 8.0, 9.0, 10.0, 11.0, 12.0, 13.0mm



76084 12pc Power Blade Inch & Metric Nut Driver Set

30mm deep drilled Nut drivers. Use with #76000 CentroFix Blade Holder. 100mm OAL

Item No.	lbs.
76084	2.97

Inch: 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2"
Metric: 4.0, 4.5, 5.0, 5.5, 6.0, 7.0, 8.0, 9.0, 10.0, 11.0, 12.0, 13.0mm
Cushion Grip CentroFix Blade Holder

Wiha Power Blade Nut Drivers - 100mm



760 Power Blade Inch Nut Drivers

High alloy CVM steel, hardened, hard chromed.

Item No.	Blade	mm	Inch	lbs.
76059	3/16	100	3.9	.12
76060	7/32	100	3.9	.14
76061	1/4	100	3.9	.14
76062	9/32	100	3.9	.14
76063	5/16	100	3.9	.14
76064	11/32	100	3.9	.15
76065	3/8	100	3.9	.15
76066	7/16	100	3.9	.15
76067	1/2	100	3.9	.18



760 Power Blade Metric Nut Drivers

High alloy CVM steel, hardened, hard chromed.

Item No.	Blade	mm	Inch	lbs.
76068	4.0	100	3.9	.12
76069	4.5	100	3.9	.12
76070	5.0	100	3.9	.12
76071	5.5	100	3.9	.14
76072	6.0	100	3.9	.14
76073	7.0	100	3.9	.14
76074	8.0	100	3.9	.14
76075	9.0	100	3.9	.14
76076	10.0	100	3.9	.14
76077	11.0	100	3.9	.15
76078	12.0	100	3.9	.18
76080	13.0	100	3.9	.19

Wiha Nut Driver Sets Precision Series



26590 8pc Precision Nut Driver Set - Metric

Blade CVM steel. Hard chrome finish.

Item No.	Metric Nut Drivers:	lbs.
26590	2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5, 6.0mm x 60mm	.48

26592 7pc Nut Driver Set - Metric

Item No.	Metric Nut Drivers:	lbs.
26592	1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm	

Wiha Nut Driver Precision Series



265 Metric Metric Nut Driver With Precision Handle Metric sizes.

Blade Chrome-Vanadium-Molybdenum steel. Hard chrome finished.

Item No.	Blade	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26510	1.5	60	2.4	140	5.5	2.5	3.0	.03	10
26515	1.8	60	2.4	140	5.5	2.9	3.5	.03	10
26520	2.0	60	2.4	140	5.5	3.2	4.0	.04	10
26525	2.5	60	2.4	155	6.1	4.0	4.0	.04	10
26530	3.0	60	2.4	155	6.1	5.0	5.0	.05	10
26532	3.2	60	2.4	155	6.1	5.0	5.0	.05	10
26535	3.5	60	2.4	155	6.1	5.3	6.0	.05	10
26540	4.0	60	2.4	155	6.1	5.5	6.0	.05	10
26545	4.5	60	2.4	155	6.1	6.2	7.0	.05	10
26550	5.0	60	2.4	155	6.1	6.8	7.0	.05	10
26555	5.5	60	2.4	170	6.7	7.6	8.0	.06	10
26560	6.0	60	2.4	170	6.7	8.2	9.0	.06	10
26570	7.0	60	2.4	170	6.7	9.6	10.0	.06	10

*Metric dimensions actual - Inch dimensions approximate



265 Inch Inch Nut Driver With Precision Handle Inch sizes.

Blade Chrome-Vanadium-Molybdenum steel. Hard chrome finished.

Item No.	Blade	Inch	mm	Inch	mm	Inch	Inch	lbs.	pkg.
26523	3/32	60	2.4	155	6.1	.16	.16	.04	10
26527	7/64	60	2.4	155	6.1	.20	.20	.05	10
26531	1/8	60	2.4	155	6.1	.20	.20	.05	10
26536	9/64	60	2.4	155	6.1	.21	.24	.05	10
26539	5/32	60	2.4	155	6.1	.22	.24	.05	10
26547	3/16	60	2.4	155	6.1	.25	.28	.05	10
26556	7/32	60	2.4	170	6.7	.30	.32	.06	10
26563	1/4	60	2.4	170	6.7	.34	.36	.06	10

*Metric dimensions actual - Inch dimensions approximate



In canvas storage pouch

26598 8pc Precision Nut Driver Set - Metric

Blade CVM steel. Hard chrome finished.

Item No.	Metric Nut Drivers:	lbs.
26598	2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5, 6.0mm x 60mm	.70



26591 8pc Precision Nut Driver Set - Inch

Blade CVM steel. Hard chrome finished.

Item No.	Inch Nut Drivers:	lbs.
26591	3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4" x 2.4"	.47



In canvas storage pouch

26599 8pc Precision Nut Driver Set - Inch

Blade CVM steel. Hard chrome finished.

Item No.	Inch Nut Drivers:	lbs.
26599	3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4" x 2.4"	.72

Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page
10810	16	26193	26	26531	37	26766	25	26968	31	28143	16
16112	15	26194	23	26532	37	26771	28	26969	31	28144	36
20715	15	26195	26	26535	37	26772	28	26970	31	28149	17
20756	15	26196	28	26536	37	26773	28	26971	29	28150	17
20757	15	26197	22	26539	37	26774	28	26972	29	28151	17
20758	15	26199	22	26540	37	26775	28	26973	29	28156	36
20759	15	26205	23	26545	37	26776	28	26974	29	28157	36
20760	15	26210	23	26547	37	26790	24	26975	30	28158	36
20799	15	26307	23	26550	37	26791	24	26976	30	28159	36
21103	13	26309	23	26555	37	26792	24	26977	30	28160	36
21105	13	26313	23	26556	37	26793	27	26978	30	28161	36
26000	22	26315	23	26560	37	26794	25	26979	30	28162	36
26001	22	26316	23	26563	37	26795	28	26980	30	28163	36
26008	22	26320	23	26570	37	26796	27	26981	30	28164	36
26010	22	26323	23	26571	28	26798	26	26982	30	28168	36
26012	22	26325	23	26572	28	26799	24	26983	30	28169	36
26015	22	26327	23	26573	28	26810	22	26984	31	28170	36
26018	22	26330	23	26574	28	26815	28	26985	31	28171	36
26020	22	26331	23	26575	28	26900	29	26987	31	28172	36
26022	22	26333	23	26576	28	26903	29	26994	31	28173	36
26023	22	26336	23	26577	28	26904	29	28000	29	28174	36
26025	22	26340	23	26578	28	26905	29	28002	30	28175	36
26027	22	26341	27	26579	28	26906	30	28003	30	28176	36
26028	22	26343	27	26581	28	26911	29	28004	30	28177	36
26030	22	26345	27	26582	28	26912	29	28005	30	28187	17
26032	22	26347	27	26583	28	26914	30	28006	30	28188	17
26033	22	26349	27	26584	28	26916	30	28007	30	28189	18
26034	22	26351	27	26585	28	26917	30	28008	30	28191	17
26035	22	26353	27	26586	28	26918	30	28012	30	28194	18
26040	22	26363	27	26587	28	26919	30	28015	30	28196	36
26041	22	26367	27	26588	28	26920	30	28016	30	28197	18
26042	22	26369	27	26589	28	26921	30	28021	29	28198	36
26050	26	26371	27	26590	37	26922	29	28023	29	28199	18
26051	26	26390	23	26591	37	26923	30	28024	29	28474	17
26052	26	26391	23	26592	37	26924	30	28026	29	28476	17
26053	26	26392	27	26593	28	26925	30	28027	29	28477	17
26055	26	26393	27	26596	28	26926	30	28028	29	28479	17
26056	26	26399	23	26598	37	26927	30	28029	29	28483	17
26060	26	26413	24	26599	37	26928	30	28033	29	28485	17
26061	26	26415	24	26631	28	26929	30	28034	29	28486	16
26065	26	26416	24	26701	24	26930	31	28035	29	28487	16
26066	26	26419	24	26702	24	26932	29	28036	29	28488	16
26068	26	26420	24	26703	24	26935	29	28037	29	28489	14
26070	26	26423	24	26704	24	26936	29	28103	14	30202	6
26072	26	26425	24	26705	24	26937	29	28106	16	30203	6
26073	26	26427	24	26706	24	26938	31	28107	16	30204	6
26074	26	26430	24	26707	24	26939	31	28108	16	30205	6
26076	26	26431	24	26708	24	26940	31	28109	16	30206	6
26079	26	26436	24	26709	24	26941	31	28110	16	30208	6
26080	26	26439	24	26710	24	26942	31	28112	16	30210	6
26090	22	26440	24	26715	24	26943	31	28114	16	30211	6
26092	23	26441	27	26720	24	26944	31	28116	17	30212	6
26093	26	26443	27	26721	26	26945	31	28117	17	30215	6
26099	22	26445	27	26723	26	26946	31	28118	17	30216	6
26100	22	26447	27	26725	26	26947	31	28119	17	30217	6
26101	22	26449	27	26727	26	26948	31	28120	17	30218	6
26102	22	26455	27	26731	26	26949	31	28122	17	30219	6
26105	22	26457	27	26732	27	26950	31	28123	17	30220	6
26107	22	26459	27	26733	27	26951	30	28124	17	30221	6
26108	22	26461	27	26735	27	26952	30	28126	16	30222	6
26109	22	26463	27	26736	27	26953	30	28127	16	30223	6
26110	22	26465	27	26737	27	26954	30	28128	16	30225	6
26113	22	26467	27	26739	27	26955	30	28129	16	30226	6
26114	22	26490	24	26741	27	26956	30	28130	16	30227	6
26115	22	26491	24	26743	27	26957	30	28132	16	30230	6
26130	26	26493	27	26745	27	26958	30	28133	16	30232	6
26132	26	26499	24	26747	27	26959	30	28134	16	30235	6
26135	26	26510	37	26749	27	26960	30	28135	16	30236	6
26136	26	26515	37	26751	27	26961	30	28136	16	30237	9
26140	26	26520	37	26761	25	26962	31	28137	16	30238	6
26142	26	26523	37	26762	25	26963	31	28138	16	30239	7
26145	26	26525	37	26763	25	26964	31	28139	16	30255	7
26190	22	26527	37	26764	25	26965	31	28140	16	30265	7
26192	23	26530	37	26765	25	26966	31	28142	16	30276	5

Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page
30289	7	34124	32	36228	11	36738	12	52097	18	76033	20
30290	7	34126	32	36229	11	36740	13	52098	18	76034	20
30291	7	34127	32	36231	11	36742	12	52099	18	76035	20
30294	6	34128	32	36232	11	36744	12	52105	18	76036	20
30295	8	34129	32	36233	11	36750	13	52110	18	76037	20
30297	6	34130	32	36234	9	36760	13	52115	18	76038	20
30298	6	34131	32	36238	11	36780	13	52120	18	76039	20
30299	8	34132	32	36239	11	36786	13	52125	18	76040	21
30520	8	34133	32	36240	15	36790	13	52650	19	76041	20
30523	8	34134	32	36241	11	36791	12	52711	19	76042	20
30526	8	34135	32	36242	11	36792	13	52713	19	76043	20
30535	8	34136	32	36243	11	36793	12	52716	19	76044	20
30540	8	34137	32	36244	9	36794	12	52719	19	76045	21
30580	8	34138	32	36246	11	37220	34	52722	19	76046	21
30813	5	34139	32	36247	11	37222	34	52726	19	76047	21
30814	5	34140	32	36248	11	37226	34	52729	19	76048	21
30815	5	34141	32	36249	9	37228	34	52732	19	76049	21
30816	5	34142	32	36250	15	37230	34	52790	19	76050	21
30817	5	34143	32	36252	11	37235	34	52791	19	76051	21
30820	5	34144	32	36253	11	37236	34	53010	4	76052	21
30825	5	34145	32	36254	9	37237	34	53015	4	76053	21
30830	5	34152	32	36255	11	37238	34	53020	4	76054	21
30835	5	34154	32	36256	9	37239	34	53025	4	76056	20
30892	5	34193	32	36257	9	37241	34	53027	4	76057	20
30896	5	34194	32	36258	9	37244	34	53035	4	76058	20
30898	5	34195	32	36259	10	37291	34	53040	4	76059	37
30942	8	34302	33	36262	11	38450	14	53075	4	76060	37
31105	6	34304	33	36263	11	38460	14	53090	4	76061	37
31110	6	34306	33	36264	10	38600	14	53096	4	76062	37
31112	6	34308	33	36265	11	40010	25	53097	5	76063	37
31114	6	34310	33	36266	10	45056	14	53099	5	76064	37
31115	6	34312	33	36267	10	45057	14	53110	4	76065	37
31117	6	34314	33	36268	10	45060	14	53115	4	76066	37
31118	6	34336	34	36269	10	45062	14	53120	4	76067	37
31120	6	34338	34	36270	10	45065	14	53310	19	76068	37
31125	6	34339	34	36271	10	45067	14	53315	19	76069	37
31135	7	34340	34	36272	10	45147	14	53320	19	76070	37
31137	9	34341	34	36273	10	45152	14	53325	19	76071	37
31140	7	34342	34	36274	10	45205	14	53330	19	76072	37
31190	7	34343	34	36275	10	45225	14	53390	19	76073	37
31191	7	34390	34	36276	10	45505	15	53398	19	76074	37
31192	7	34391	33	36277	10	45521	15	53405	19	76075	37
31193	7	34474	35	36278	10	45525	14	53410	19	76076	37
31194	9	34475	35	36279	10	45527	14	53425	19	76077	37
31201	5	34476	35	36280	10	45540	14	76000	20,36	76078	37
31202	5	34478	35	36281	10	45545	14	76001	21	76079	21
31203	5	34482	35	36282	10	45546	15	76002	21	76080	37
31305	8	34712	33	36283	10	45550	14	76003	21	76084	36
31310	8	34715	33	36284	10	45551	15	76004	21	76085	36
31312	8	34718	33	36285	10	45831	14	76005	21	76086	36
31315	8	34721	33	36286	10	45832	14	76007	21	76087	21
31320	8	34724	33	36287	10	45833	14	76008	21	76088	20
32644	8	34727	33	36288	10	45891	14	76009	21	76089	20
33603	35	34730	33	36290	9	46702	15	76010	21	76090	21
33606	35	34753	33	36291	10	46704	15	76011	20	76091	20
33607	35	34759	33	36294	10	46706	15	76012	20	76092	21
33609	35	34765	33	36296	11	46712	15	76013	20	76093	20
33612	35	34771	33	36297	11	46715	15	76014	21	76094	20
33614	35	34774	33	36298	10	46716	15	76015	21	76095	20
33620	35	34777	33	36299	11	46720	15	76016	21	76096	21
33622	35	34791	33	36710	12	46722	15	76017	21	76098	20
33623	35	34792	33	36713	12	46725	15	76018	21	76099	21
33653	35	35800	7	36715	13	46740	15	76019	21	91118	23
33659	35	35801	7	36716	12	46750	15	76020	21	92189	25
33665	35	35802	7	36719	12	46760	15	76021	21	92190	25
33671	35	35803	7	36720	13	46786	15	76022	20	92191	25
33674	35	35894	7	36723	12	52005	18	76023	20		
33677	35	36201	10	36725	13	52010	18	76024	20		
33690	35	36202	9	36726	12	52020	18	76025	21		
33691	35	36203	9	36728	12	52025	18	76026	20		
34120	32	36207	9	36730	13	52035	18	76027	21		
34121	32	36211	11	36732	12	52040	18	76030	21		
34122	32	36214	11	36734	12	52050	18	76031	20		
34123	32	36223	11	36736	12	52090	18	76032	20		



PROFESSIONAL SCREWDRIVERS & NUT DRIVERS



(800) 494-6104
 fax: (800) 494-7456
 cservice@wihatools.com
 www.wihatools.com



Wiha Quality Tools
 1348 Dundas Circle
 Monticello, MN 55362
 tel: 763.295.6591
 fax: 763.295.6598

Wiha Tools Canada Ltd.
 www.wihatools.ca
 Brampton, ONT L6T 4X4
 tel: 866.494.0096 or 763.295.6591
 fax: 763.295.6598



To:

Catalog Item No. 99002
 version - 2/1/20

Subject to change without notice

©2020 Willi Hahn Corporation

@Torx is a registered trademark of
 Acument Intellectual Properties LLC.



99934 - Hex Tools Catalog




99914 - TORX Catalog



99001 - TorqueControl Catalog




99951 - Bits Catalog



99919 - Insulated Catalog



99977.w - Pliers/Crimpers Catalog



99004 - Shop Tools Catalog



99945 - ESD Catalog



99007 - Merchandise Catalog

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Wiha:

<u>28103</u>	<u>52791</u>	<u>21103</u>	<u>92189</u>	<u>22240</u>	<u>30226</u>	<u>30232</u>	<u>30202</u>	<u>33623</u>	<u>30216</u>	<u>30203</u>	<u>30212</u>	<u>30204</u>	<u>33614</u>	<u>30206</u>
<u>30208</u>	<u>30221</u>	<u>30813</u>	<u>30814</u>	<u>28105</u>	<u>36249</u>	<u>36256</u>	<u>36258</u>	<u>45561</u>	<u>45589</u>	<u>31192</u>	<u>30520</u>	<u>92191</u>	<u>34474</u>	<u>34475</u>
<u>34154</u>	<u>28187</u>	<u>28188</u>	<u>76087</u>	<u>76089</u>	<u>76090</u>	<u>76091</u>	<u>76092</u>	<u>76093</u>	<u>76094</u>	<u>76095</u>	<u>76096</u>	<u>28483</u>	<u>45833</u>	<u>76060</u>
<u>76061</u>	<u>76062</u>	<u>76070</u>	<u>76072</u>	<u>76073</u>	<u>15310</u>	<u>30298</u>	<u>36244</u>	<u>36254</u>	<u>36259</u>	<u>45556</u>	<u>45598</u>	<u>52098</u>	<u>38600</u>	<u>65090</u>
<u>28194</u>	<u>35894</u>	<u>52099</u>	<u>53096</u>	<u>30237</u>	<u>31137</u>	<u>31190</u>	<u>31191</u>	<u>31193</u>	<u>30517</u>	<u>30526</u>	<u>30530</u>	<u>30540</u>	<u>34132</u>	<u>34133</u>
<u>30535</u>	<u>30550</u>	<u>28191</u>	<u>30560</u>	<u>30523</u>	<u>52097</u>	<u>30580</u>	<u>34476</u>	<u>34478</u>	<u>34480</u>	<u>28189</u>	<u>34482</u>	<u>21105</u>	<u>30896</u>	<u>34152</u>
<u>34158</u>	<u>76088</u>	<u>76098</u>	<u>76099</u>	<u>45831</u>	<u>76000</u>	<u>76079</u>	<u>30289</u>	<u>76059</u>	<u>76063</u>					