

# Product Information



## 1470POO050P30-11

EAN 4031582338508

Swivel castor, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, bolt hole. Wheel centre made of Polypropylene, plain bearing

Technical Data	
Wheel diameter	50 mm
Width of Tread	18 mm
Centre hole	11 mm
Offset	25 mm
Swivel Interference	100 mm
Overall height	70 mm
Temperature	- 20 / + 60 °C
Standard	EN 12530
Weight	0.14 kg
Swivel Radius	50 mm
Hardness of tread	Shore D 65
Load capacity	40 kg
Load capacity (static)	80 kg



Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

# Product Information



**1470POO050P30-11**

EAN 4031582338508

