



# SPECIFICATION

1. Rated Voltage ..... 12VDC
2. Operating Voltage ..... 7~15VDC
3. Max. Rated Current ..... 200mA at 12VDC
4. Min. Sound Pressure Level ..... 108dB at 12VDC/30cm
5. Tone Nature ..... Siren
6. Case Material ..... PC/ABS
7. Color ..... Red
8. Flashes/Min ..... 150 times
9. Operating Temperature ..... -20.~+60°C
10. Store Temperature ..... -30.~+70°C
11. Weight ..... 115g

Compliance with ROHS

**KEPO** NINGBO KEPO ELECTRONIC CO.,LTD  
<http://www.chinaacoustic.com>

Piezo Siren  
**KP-120R**

UNIT mm DWG NO. KP2.840.045  
 SCALE NOT TO SCALE SHEET 7 OF 8  
 VER 1.0

No.	DESCRIPTION	APPROVED	DATE
	DRAWN		
	CHECKED		
	APPROVED		07.12.21

