


Stamped crimp contacts




Identification	Wire gauge (mm <sup>2</sup> )	Part No.		
----------------	-------------------------------	----------	--	--

D-Sub

Performance levels Explanations see page 05.04 Other performance levels on request	Wire gauge (mm <sup>2</sup> )	stamped female contacts		
		Performance level 3	Performance level 2	Performance level 1
Individual contacts	AWG 28-24 0.09-0.25 stranded	09 67 000 7277 <sup>1)</sup>	09 67 000 7278 <sup>1)</sup>	09 67 000 7276 <sup>1)</sup>
500 pieces/reel Unrolling left		09 67 000 7267	09 67 000 7268	09 67 000 7266
10 000 pieces/reel Unrolling left Unrolling left reversed Unrolling right reversed		09 67 000 7257 09 67 000 7247 09 67 000 7237	09 67 000 7258 09 67 000 7248 09 67 000 7238	09 67 000 7256 09 67 000 7246 09 67 000 7236
Individual contacts	AWG 24-20 0.25-0.56 stranded	09 67 000 8277 <sup>1)</sup>	09 67 000 8278 <sup>1)</sup>	09 67 000 8276 <sup>1)</sup>
500 pieces/reel Unrolling left		09 67 000 8267	09 67 000 8268	09 67 000 8266
10 000 pieces/reel Unrolling left Unrolling left reversed Unrolling right reversed		09 67 000 8257 09 67 000 8247 09 67 000 8237	09 67 000 8258 09 67 000 8248 09 67 000 8238	09 67 000 8256 09 67 000 8246 09 67 000 8236

Unrolling direction



<sup>1)</sup> Minimum order 500 pieces or multiples of 500  
Insertion and removal tool see chapter 20  
Contact dimensions see page 05.31