

Medium Toggle Switch


Q-1311

TYPE: **KN3-3**

SPECIFICATIONS



Rating: 5A 125V AC; 3A 250V AC
 Contact R: 50mΩ max
 Insulation R: 500V DC 100MΩ min
 Dielectric Strength: 1 Minute 1500V AC
 Operating Temperature: -25°C ~ +85°C
 Electrical Life: 10, 000 Cycles

Outline Drawing



Mounting

Circuitry



ON - ON