

KERN HCN50K100IP

Die Handliche für erhöhte Lasten

KERN[®]



Functions

Data hold function: yes

Environmental conditions

Maximum humidity: 80 %

Maximum operating temperature: 35 °C

Minimum ambient temperature: 5 °C

Power supply

Operating time: 200 h

Service

Adjustment at the location of installation: 961-248

DAkkS Certificate: 963-128H

Category

Brand: KERN

Category: Balances

Product Group: Hanging scale

Packaging & shipping

Delivery: 24 h

Dimensions packaging (WxDxH): 155 x 220 x 75 mm

Gross weight: 1,145 kg

Net weight: 800 g

Shipping method: Parcel service

Construction

Casing material: stainless steel

Dimensions housing (WxDxH): 95 x 180 x 50 mm

Measuring system

Adjustment options: External calibration

Linearity: 200 g

Precision (of [Max]): 0,005

Readout [d]: 100 g

Recommended adjusting weight: 50 kg (M2)

Reproducibility: 100 g

Resolution: 500

Stabilisation time: 2 s

Warm up time: 10 min

Weighing range [Max]: 50 kg

Weighing system: Strain gauge

Weighing units: kg lb N

Display

Display digit height: 1,200 cm