



Rollover image to zoom



DWE7485

8-1/4 IN. COMPACT JOBSITE TABLE SAW



(0) **WRITE A REVIEW**

Maximized for accuracy and capacity, this 8-1/4 in. Table Saw includes on-board storage for the blade guard assembly, non-through cut riving knife, anti-kickback pawls, blade-change wrenches, miter gauge, and push stick. The powerful 15 Amp, 5800 rpm motor allows users to complete a majority of applications. The rack & pinion fence allows for fast, easy adjustments and provides the capacity to rip 4x8 sheet goods.

FEATURES & SPECS

FEATURES

- Compact size for easy transportation and storage
- Rack & pinion telescoping fence rails make fence adjustments fast, smooth, and accurate
- 24.5 in. of rip capacity for ripping 4x8 plywood or OSB sheets
- Power-loss reset prevents accidental restarts following a power disruption when the tool is left in the on position
- Blade brake
- On-board storage for guard, fence, wrenches, and miter gauge
- Metal roll cage base for jobsite durability
- Site-Pro Modular Guarding System allows for tool-free adjustments of the guarding

SPECIFICATIONS

AMPS	15 AMPS
ARBOR SIZE	5/8 IN
BLADE DIAMETER	8-1/4"
DEPTH OF CUT AT 45°	1-3/4 IN
DEPTH OF CUT AT 90°	2-9/16 IN
DUST PORT DIAMETER	2.5 IN
FOR WOOD CUTTING	TRUE
MAX RIP TO LEFT OF BLADE	12 IN
MAX RIP TO RIGHT OF BLADE	24.5 IN
NO LOAD SPEED	5800 RPM
TOOL HEIGHT	13 IN
TOOL LENGTH	22.75 IN
TOOL WEIGHT	46 LBS

INCLUDES

- (1) DWE7485 8-1/4 in. Table Saw
- (1) Anti-Kickback Pawls
- (1) Push Stick
- (1) Non-Through Cut Riving Knife
- (1) Modular Guard System
- (1) Fence
- (1) Miter Gauge
- (1) 8-1/4 in. Blade
- (2) Blade-Change Wrenches

WARRANTY & SERVICE INFORMATION

WARRANTY INFORMATION

