

MILAN S.r.l. a socio unico

Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it



Firestop® Technical Datasheet



**tasker® C2075 CPR – 2x0,75 mm²
 Braided Shielded Cable**



A	B	C	D
---	---	---	---

NOTE
CATEGORY
APPLICATIONS

The picture does not represent the real number of conductors
 Braided Conductor Shielded Cable (See Data Network Catalogue)
 Data transmission and Electronics

- A:** Black **Flame Retardant PVC** sheath.
Outer cable diam. Ø 6,80 (±0,20) mm.
- B:** Braided Shielding O.F.C. Red Copper covering 85%.
- C:** Cores Insulation with **Flame Retardant PVC**.
Core color code: Brown, Blue. Diam. Ø 2,50 (±0,20) mm.
- D:** Stranded O.F.C. Red Copper formation 24x0,20 mm.
Nom. Cross section 2x0,75 mm².

MARKING

**tasker® C2075 CPR 2x0,75 mm² O.F.C. - IMQ 0051-CPR-0966 – 2017 – Eca –
 BRAIDED SHIELDED CABLE - Firestop® - Made Italy**

Cable Properties

Conductor Resistance	21,93 Ω/Km
Capacity Core/Core	170 pF/mt
Capacity Core/Shield	300 pF/mt
Max Rated Voltage	49 V
Operative Temperature	-20/+70°C

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS2 Compliant
Impiego	X	Outdoor Limited	Esterno Limitato	Posa	X	Restricted Mobile	Mobile Limitata	Informazioni	X	Ver. A / 26.05.17
		Outdoor	Esterno			Mobile	Mobile			
		Outdoor Direct Burial	Esterno Interrato			Mobile in Drag Chain	Mobile in Catena			