

Automotive Rocker Switch

Q-10232

TYPE: **R13-247BR**
Rocker



SPECIFICATIONS

Rating: 20A 12V DC
Contact R: 50mΩ max
Insulation R: 500V DC 100MΩ min
Dielectric Strength: 1 Minute 1500V AC
Operating Temperature: -25°C ~ +85°C
Electrical Life: 10,000 Cycles

