



- For solid and stranded conductors
AWG 27 up to AWG 22
- Max. wire diameter 1.5mm
- Cable diameter 6 - 12mm
- Degree of protection IP65/IP67
- Cat. 6 performance class EA
suitable for 1/10 Gigabit Ethernet
- Temperature range -40°C up to +70°C
- 750 mating cycles

Data contact plating: Au 1.27µm (50µ") over nickel

	All Dimensions in mm Original Size DIN A4		Scale 1:1	Free size tol.		Ref.		
						Sub.		
	All rights reserved		Created by TAMAS	Inspected by AVRAM	Standardisation HOFFMANN	Date 2016-07-05	State Final Release	
	Department EC PD - RO		Title Han 3A RJ45 Hybrid 10G metal connector				Doc-Key / ECM-Nr. 100190447/UGD/002/B 500000106140	
HARTING Electronics GmbH D-32339 Espelkamp			Type TB	Number 09451151760			Rev. B	Page 1/1