

# Tact Switch



**Q-1457**

TYPE: **TS-2201**


## SPECIFICATIONS

Contact Type	SPST
Rating	DC 12V, 50mA
Travel	0,5±0,10mm
Contacts Resistance	100mΩ Max
Insulation Resistance	100MΩ Min
Minimum Load	DC 100V
Dielectric Strengths	AC 250V / 1 minute
Life Test	100 000 Cycles Min
Operating temperature range	-30°C to +85°C
Operating Force	130 ± 50gf


Outline Drawing



Mounting



PP=4,3; 5,0; 6,0; 8,0; 9,0; 18,0mm  
Circuitry



OFF - (ON)