

# Tact Switch

**Q-2718**

TYPE: **SKEYAHA010**




## SPECIFICATIONS



Contact Type	SPST
Rating	DC 12V, 50mA
Contacts Resistance	500mΩ Max
Insulation Resistance	50MΩ Min
Minimum Load	DC 100V
Dielectric Strengths	AC 100V / 1 minute
Life Test	500 000 cycles/ minute
Operating temperature range	-40°C to +90°C

Outline Drawing

Unit: mm





h
5



Mounting

Circuitry



**OFF - (ON)**