

Tact Switch


Q-886

TYPE: **12X12X10**


SPECIFICATIONS

Contact Type	SPST-NO
Rating	DC 12V, 50mA
Contacts Resistance	100mΩ Max
Insulation Resistance	100MΩ Min
Minimum Load	DC 500V
Dielectric Strengths	AC 500V / 1 minute
Life Test	300 000 Cycles Min
Operating temperature range	-25°C to +70°C
Operating Force	130 ± 50gf

Outline Drawing



Mounting



Circuitry

