

**CARDMASTER ABS 36/31-3**



Sample photo

**Order symbol:** ABS 36/31-3  
**Product nbr:** 7585020  
**Description:** Enclosure, ABS  
**Remarks:** Smoked transparent hinged cover

**EAN:** 6418074056801  
**EI. number:**  
 Finland: 3438246  
 Electric No. 8212016787  
 Denmark:  
 Electric No. Sweden: 7585020

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Dimensions:	Length	Width	Height	Accessories:
mm:	390	316	167	FP 36/31 Front plate (aluminium)
inch:	15.4	12.4	6.6	
Materials:	<b>Material:</b> ABS <b>Base colour:</b> RAL 7035 -light grey <b>Cover colour:</b> Smoked grey <b>Gasket material:</b> EPDM & PUR			
Temperatures:	<b>Temperature °C (short term):</b> -40 ... 80 °C <b>Temperature °C (continuous):</b> -40 ... 60 °C <b>Temperature °F (short term):</b> -40 ... 175 °F <b>Temperature °F (continuous):</b> -40 ... 140 °F			
Accessories:	Ingress Protection (EN 60529): IP65 Impact Resistance (EN 62262): IK07 Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): 1 Flammability Rating: UL 94 HB Glow Wire Test (IEC 695-2-1) °C: 650 NEMA Class: NEMA 1, 3, 3R, 12, 13			
MP 36/31	Mounting plate			

