

PushPull V4, compact housing w. clip



Part number	09 45 545 0042
Specification	PushPull V4, compact housing w. clip
HARTING eCatalogue	https://b2b.harting.com/09455450042

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Connectors
Series	HARTING PushPull (V4)
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Compact With board looks
	With board locks With integrated seal

Version

Locking type PushPull	
-----------------------	--

Technical characteristics

11. 98. 1	40 70.00
Limiting temperature	-40 +70 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65
	IP67
Vibration resistance	10-500 Hz, 5 g, 0.35 mm, 2h/axis
	5.72 m/s² acc. to IEC 61373 Category 1 Class B
Shock resistance	25 g / 11 ms, 3 shocks / axis and direction
	5 g / 30 ms, 5 shocks / axis and direction acc. to IEC 61373 Category 1 Class B

Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0



Material properties

RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4) EN 45545-2 R26: HL1, HL2, HL3
UL / CSA	UL 1977 ECBT2.E102079
	CSA-C22.2 No. 182.3 ECBT8.E102079

Commercial data

Packaging size	100
Net weight	3.8 g
Country of origin	Romania
European customs tariff number	85366990
eCl@ss	27440202 Shell for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING: 09455450042