

Detector Switch


Q-9021

TYPE: IT-1189U


SPECIFICATIONS

Contact Type	SPST
Rating	DC 12V, 50mA
Contacts Resistance	100mΩ Max
Insulation Resistance	100MΩ Min
Minimum Load	DC 100V
Dielectric Strengths	AC 100V / 1 minute
Life Test	100 000 cycles/ minute
Operating temperature range	-30°C to +85°C


Outline Drawing



Mounting



Circuitry



OFF - (ON)