

# KERN EMB 600-2

Einsteiger-Laborwaage mit enormen Wägeleistungen



## Measuring system

|                               |                      |
|-------------------------------|----------------------|
| Adjustment options:           | External calibration |
| Linearity:                    | 30 mg                |
| Readout [d]:                  | 10 mg                |
| Recommended adjusting weight: | 500 g (F2)           |
| Reproducibility:              | 10 mg                |
| Resolution:                   | 60000                |
| Stabilisation time:           | 2,500 s              |
| Warm up time:                 | 2 h                  |
| Weighing range [Max]:         | 600 g                |
| Weighing system:              | Strain gauge         |
| Weighing units:               | dwt g oz oz          |

## Display

|                       |          |
|-----------------------|----------|
| Display digit height: | 1,500 cm |
|-----------------------|----------|

## Functions

|                     |      |
|---------------------|------|
| Suspended weighing: | Hook |
|---------------------|------|

## Environmental conditions

|                                |       |
|--------------------------------|-------|
| Maximum humidity:              | 80 %  |
| Maximum operating temperature: | 35 °C |
| Minimum ambient temperature:   | 5 °C  |

## Power supply

|                |      |
|----------------|------|
| Charging time: | 10 h |
|----------------|------|

|      |                        |
|------|------------------------|
| n/a: | Mains adapter external |
|------|------------------------|

## Power supply

|                                 |                         |
|---------------------------------|-------------------------|
| Operating time:                 | 12 h                    |
| Operating time (Backlight off): | 50 h                    |
| Rechargeable battery:           | Rchrg. battery optional |

## Service

Adjustment at the location of installation: 961-247

|                    |         |
|--------------------|---------|
| DAkkS Certificate: | 963-127 |
|--------------------|---------|

## Category

|                |                |
|----------------|----------------|
| Brand:         | KERN           |
| Category:      | Balances       |
| Product Group: | School balance |

## Packaging & shipping

|                               |                   |
|-------------------------------|-------------------|
| Delivery:                     | 24 h              |
| Dimensions packaging (WxDxH): | 210 x 265 x 90 mm |
| Gross weight:                 | 655 g             |
| Net weight:                   | 500 g             |
| Shipping method:              | Parcel service    |

## Construction

|                             |                   |
|-----------------------------|-------------------|
| Casing material:            | Plastic           |
| Dimensions housing (WxDxH): | 170 x 240 x 39 mm |
| Material weighing plate:    | Plastic           |
| Weighing surface (d):       | 105               |