

KERN HDB5K5N

Praktisch, preiswert und stets griffbereit



Functions

Data hold function: yes

Environmental conditions

Maximum humidity: 90 %
Maximum operating temperature: 35 °C
Minimum ambient temperature: 5 °C

Power supply

Operating time: 180 h

Service

Adjustment at the location of installation: 961-247

DAkkS Certificate: 963-127H

Category

Brand: KERN
Category: Balances
Product Group: Hanging scale

Packaging & shipping

Delivery: 24 h
Dimensions packaging (WxDxH): 225 x 150 x 70 mm
Gross weight: 383,860 g
Net weight: 200 g
Shipping method: Parcel service

Construction

Casing material: Plastic
Dimensions housing (WxDxH): 70 x 25 x 105 mm
Overall dimensions mounted (WxDxH): 195 x 70 x 25 mm

Measuring system

Adjustment options: External calibration
Linearity: 15 g
Precision (of [Max]): 0,005
Readout [d]: 5 g
Recommended adjusting weight: 5 kg (M1)
Reproducibility: 5 g
Resolution: 1000
Stabilisation time: 2 s
Warm up time: 10 min
Weighing range [Max]: 5 kg
Weighing system: Strain gauge
Weighing units: kg lb N

Display

Display digit height: 1,200 cm