
Item no.: 282-681
Product description: 3-CONDUCTOR THROUGH TERMINAL BLOCK



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm ²]	0.2 - 6 mm ²
Cross section [AWG]	24 - 10 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	41 A
Weight	21.29 g
Color	gray
Wiring type	Front-entry
No. of connection Points	3
No. of potentials	1
Height	32.5 mm
Height	1.28 in
Width	8 mm
Width	0.315 in
Depth	93 mm
Depth	3.66 in

Strip length from	12 mm
Strip length to	13 mm
Strip length	0.49 in
Mounting	TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
282-681	ABS	05-HG476175/3-PDA	800	41	6,0
282-681	BV	07436/Co	800	41	6,0
282-681	CCA	NL5448	800	30	6
282-681	CSA	154112-1505033	600	40	24-10
282-681	DNV	E-10423	800	41	6,0
282-681	GL	17295-00HH	800	41	6
282-681	KEMA	2036290.01	800		6
282-681	KR	HMB05880-EL001	500/800	10/46	6
282-681	LR	91/20112(E6)	800	41	6,0
282-681	PRS	TE/1718/880590/08	800	30	6
282-681	RMR	11130002	800	41	6,0
282-681	UR	E45172	600	30	24-10

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected